




Magnetic properties	Conditions	Min	Typ	Max	Unit
Pull-In	at 20°C	51		75	AT
Test equipment		KMS048-001 + PH45			

Special Product Data	Conditions	Min	Typ	Max	Unit
Contact - No.		90F			
Contact - form		Form C - Changeover			
Contact rating	Any DC combination of V & A not to exceed their individual max.'s			10	W
Switching voltage	DC or Peak AC			175	V
Carry current	DC or Peak AC			1	A
Switching current	DC or Peak AC			0,5	A
Sensor-resistance	measured with 40% overdrive			300	mOhm
Housing material		PBT GF30			
Case color		black			
Sealing compound		Polyurethan			

Environmental data	Conditions	Min	Typ	Max	Unit
Operating temperature		-5		80	°C
Storage temperature		-20		80	°C
Remark (RoHS)		Yes			

Data to reed-contact modifica	Conditions	Min	Typ	Max	Unit
Overall length cable	Tolerance according to drawing		500		mm

Cable specification	Conditions	Min	Typ	Max	Unit
Cable type		round cable			
Cable material		PVC			
Cross section		0,14 sq-mm			

General data	Conditions	Min	Typ	Max	Unit
Mounting advice		Decreased switching distances by mounting on iron.			
Mounting advice		Magnetically conductive screws must not be used.			
Mounting advice		over 5m cable, a resistor is recommended.			
Tightening torque	Screw M3 ISO 1207 Disk ISO 7089			0,5	Nm