

● Part Numbering

High Voltage Ceramic Capacitors (250V-6.3kV)

(Part Number)

DE	B	B3	3A	102	K	N2	A	
①	②	③	④	⑤	⑥	⑦	⑧	⑨

① Product ID

Product ID	
DE	High Voltage Ceramic Capacitors (250V-6.3kV) / Safety Standard Certified Ceramic Capacitors

② Series Category

Code	Outline	Contents
A	High Voltage	Class 1 (Char. SL) DC1-3.15kV Rated
B		Class 2 DC1-3.15kV Rated
C		Class 1, 2 DC6.3kV Rated
H		High Temperature Guaranteed, Low-dissipation Factor (Char. R, C)
S		High Temperature Guaranteed, Low-dissipation Factor (Char. D)
F		LCD Backlight Inverter Circuit

First three digits (①Product ID and ②Series Category) express "Series Name".

③ Temperature Characteristics

Code	Temperature Characteristics	Cap. Change or Temp. Coeff.	Temperature Range
B3	B	±10%	-25 to +85°C
E3	E	+20%, -55%	
F3	F	+30%, -80%	
C3	C	±20%	-25 to +85°C
		+15%, -30%	+85 to +125°C
R3	R	±15%	-25 to +85°C
		+15%, -30%	+85 to +125°C
D3	D	+20%, -30%	-25 to +125°C
1X	SL	+350 to -1000ppm/°C	+20 to +85°C
2C	CH	0±60ppm/°C	+20 to +85°C

④ Rated Voltage

Code	Rated Voltage
2E	DC250V
2H	DC500V
3A	DC1kV
3D	DC2kV
3F	DC3.15kV
3J	DC6.3kV
LH	6.3kVp-p

⑤ Capacitance

Expressed by three figures. The unit is pico-farad (pF). The first and second figures are significant digits, and the third figure expresses the number of zeros which follow the two numbers.

⑥ Capacitance Tolerance

Code	Capacitance Tolerance
C	±0.25pF
D	±0.5pF
J	±5%
K	±10%
Z	+80%, -20%

⑦ Lead Style

Code	Lead Style	Dimensions (mm)		
		Lead Spacing	Lead Diameter	Pitch of Components
A2	Vertical Crimp Long	5	ø0.6±0.05	—
A3		7.5		
A4		10		
B2/J2	Vertical Crimp Short	5	ø0.6±0.05	—
B3/J3		7.5		
B4		10		
C1	Straight Long	5	ø0.5±0.05	—
C3		7.5	ø0.6±0.05	
C4		10		
CD	Straight Short	7.5	ø0.5±0.05	—
D1		5	ø0.5±0.05	
D3		7.5	ø0.6±0.05	
DD	Vertical Crimp Taping	7.5	ø0.5±0.05	12.7
N2		5	ø0.6±0.05	15
N3		7.5		30
N7	Straight Taping	7.5	ø0.6±0.05	30
P2		5		12.7
P3		7.5		15

⑧ Packaging

Code	Packaging
A	Ammo Pack Taping Type
B	Bulk Type

⑨ Individual Specification Code

In case part number cannot be identified without "Individual Specification", it is added at the end of part number. Expressed by three-digit alphanumerics.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Murata:

[DEA1X3D150JA1B](#) [DEA1X3A150JA1B](#) [DEA1X3A100JA1B](#) [DEA1X3D100JA1B](#) [DEBE33A102ZA1B](#)
[DE0705F472Z1K](#) [DEA1X3D120J1AB](#) [DEA1X3A120JA1B](#) [DEA1X3A220JA1B](#) [DEA1X3D220JA1B](#)
[DEBB33A471KA1B](#) [DEBB33A102KQ1A](#) [DEHR33A222KA4B](#) [DE1007E222Z3K](#) [DEBB33A221KA1B](#)
[DELR33J471KCGB](#) [DEBB33D221KA1B](#) [DEBB33D101KA1B](#) [DEBB33A101KA1B](#) [DEBB33A472KA2B](#)
[DEA1X3D330JA1B](#) [DEA1X3A330JA1B](#) [DEHR33A102KEAB](#) [DEA1X3D270JA1B](#) [DEA1X3A270JA1B](#)
[DEA1X3A470JA1B](#) [DEA1X3F470JA3B](#) [DEBB33A331KA1B](#) [DEBB33D331KA1B](#) [DEHR33D221KA3B](#)
[DEA1X3D331JA2B](#) [DEBB33D151KA1B](#) [DEBB33A151KA1B](#) [DEA1X3A561JA2B](#) [DEHR33A472KECB](#)
[DEBF33D103ZA2B](#) [DE1005-979F103Z1K](#) [DE0905B222K1K](#) [DEBF33D102ZA1B](#) [DEA1X3A560JA1B](#)
[DEHR33D681KEBB](#) [DEA1X3D180JA1B](#) [DEA1X3A180JA1B](#) [DEA1X3A680JA1B](#) [DEHR33F271KA3B](#)