


ZXTC2045E6

Dual 40V complementary transistors in SOT23-6

Summary

$BV_{CEV} = 40V$

$BV_{CEO} = 30V$




Features

- 40V complementary device
- Up to 5 amps peak current
- High h_{FE}
- SOT236 package

Applications

- MOSFET and IGBT gate driving




Ordering information

Device	Reel size	Tape width	Quantity per reel
ZXTC2045E6TA	7"	8mm embossed	3,000
ZXTC2045E6TC	13"	8mm embossed	10,000

Device marking

2045

Pin out - top view



Absolute maximum ratings (each transistor)

Parameter	Symbol	Limit		Unit
		NPN	PNP	
Collector-base voltage	BV_{CBO}	40	-40	V
Collector-emitter voltage	BV_{CEV}	40	-40	V
Collector-emitter voltage	BV_{CEO}	30	-30	V
Emitter-base voltage	BV_{EBO}	7	-7	V
Peak pulse current	I_{CM}	5	-5	A
Continuous collector current ^(a)	I_C	1.5	-1.5	A
Base current	I_B	1	-1	A
Power dissipation at $T_A = 25^\circ\text{C}$ ^{(a) (c)} Linear derating factor	P_D	0.9 7.2		W mW/°C
Power dissipation at $T_A = 25^\circ\text{C}$ ^{(a) (d)} Linear derating factor	P_D	1.1 8.8		W mW/°C
Power dissipation at $T_A = 25^\circ\text{C}$ ^{(b) (c)} Linear derating factor	P_D	1.7 13.6		W mW/°C
Operating and storage temperature range	T_j, T_{stg}	-55 to +150		°C

Thermal resistance

Parameter	Symbol	Value	Unit
Junction to ambient ^{(a) (c)}	$R_{\theta JA}$	139	°C/W
Junction to ambient ^{(b) (c)}	$R_{\theta JA}$	73	°C/W
Junction to ambient ^{(a) (d)}	$R_{\theta JC}$	113	°C/W

NOTES:

- (a) For a device surface mounted on 25mm x 25mm x 0.6mm FR4 PCB with high coverage of single sided 1oz copper, in still air conditions.
 (b) As above measured at $t < 5$ seconds.
 (c) For device with one active die.
 (d) For device with two active dice running at equal power.

ZXTC2045E6

Electrical characteristics (at $T_{AMB} = 25^{\circ}\text{C}$ unless otherwise stated)


Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions
Collector-base breakdown voltage	BV_{CBO}	$(-)40^{(*)}$			V	$I_C = (-)100\mu\text{A}$
Collector-emitter breakdown voltage	BV_{CEV}	$(-)40^{(*)}$			V	$I_C = (-)1\mu\text{A}$ $0.25\text{V} > V_{BE} > 1.0\text{V}$ ($0.25\text{V} < V_{BE} < 1.0\text{V}$)
Collector-emitter breakdown voltage	BV_{CEO}	$(-)30^{(*)}$			V	$I_C = (-)10\text{mA}$ ^(†)
Emitter-base breakdown voltage	BV_{EBO}	$(-)7^{(*)}$	$(-)8.5^{(*)}$		V	$I_E = (-)100\mu\text{A}$
Collector cut-off current	I_{CBO}		$(-) < 1^{(*)}$	$(-)20^{(*)}$	nA	$V_{CB} = (-)32\text{V}$
Collector cut-off current	$I_{CES/R}$		$(-) < 1^{(*)}$	$(-)20^{(*)}$	nA	$V_{CE} = (-)16\text{V}$, $R \leq 1\text{k}\Omega$
Emitter cut-off current	I_{EBO}		$(-) < 1^{(*)}$	$(-)20^{(*)}$	nA	$V_{EB} = (-)6\text{V}$
Collector-emitter saturation voltage	$V_{CE(SAT)}$			$(-)375^{(*)}$	mV	$I_C = (-)0.75\text{A}$, $I_B = (-)15\text{mA}$ ^(†)
Base-emitter saturation voltage	$V_{BE(SAT)}$			$(-)1.2^{(*)}$	V	$I_C = (-)0.75\text{A}$, $I_B = (-)15\text{mA}$ ^(†)
Static forward current transfer ratio	h_{FE}	180	300	500		$I_C = (-)100\text{mA}$, $V_{CE} = (-)2\text{V}$ ^(†)

NOTES:

(*) () applies to PNP

(†) Measured under pulsed conditions. Pulse width ≤ 300 s; duty cycle $\leq 2\%$.

Package details - SOT23-6



DIM	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	0.90	1.45	0.354	0.0570
A1	0.00	0.15	0.00	0.0059
A2	0.90	1.30	0.0354	0.0511
b	0.35	0.50	0.0078	0.0196
C	0.09	0.26	0.0035	0.0102
D	2.70	3.10	0.1062	0.1220
E	2.20	3.20	0.0866	0.1181
E1	1.30	1.80	0.0511	0.0708
L	0.10	0.60	0.0039	0.0236
e	0.95 REF		0.0374 REF	
e1	1.90 REF		0.0748 REF	
L	0°	30°	0°	30°

Note: Controlling dimensions are in millimeters. Approximate dimensions are provided in inches

Europe

Zetex GmbH
Streitfeldstraße 19
D-81673 München
Germany

Telefon: (49) 89 45 49 49 0
Fax: (49) 89 45 49 49 49
europe.sales@zetex.com

Americas

Zetex Inc
700 Veterans Memorial Highway
Hauppauge, NY 11788
USA

Telephone: (1) 631 360 2222
Fax: (1) 631 360 8222
usa.sales@zetex.com

Asia Pacific

Zetex (Asia Ltd)
3701-04 Metroplaza Tower 1
Hing Fong Road, Kwai Fong
Hong Kong

Telephone: (852) 26100 611
Fax: (852) 24250 494
asia.sales@zetex.com

Corporate Headquarters

Zetex Semiconductors plc
Zetex Technology Park, Chadderton
Oldham, OL9 9LL
United Kingdom

Telephone: (44) 161 622 4444
Fax: (44) 161 622 4446
hq@zetex.com

For international sales offices, agents and distributors please go to www.zetex.com/salesnetwork

This publication is issued to provide outline information only which (unless agreed by the company in writing) may not be used, applied or reproduced for any purpose or form part of any order or contact or be regarded as a representation relating to the products or services concerned. The company reserves the right to alter without notice the specification, design, price or conditions of supply of any product or service.