

| PART NAME              |             | NON-METALLIC ENCLOSURE (STYLE E) |                 |                 |                                                                       |                 |                 |                 |                 |                                                                                                                                                             |                 | PART No.        |                 | NBE-10553 AND NBE-10573 |                                                                       |                 |                 |                 |                 |                                                                                                                                             |                 |                 |                 |  |  |  |  |  |  |
|------------------------|-------------|----------------------------------|-----------------|-----------------|-----------------------------------------------------------------------|-----------------|-----------------|-----------------|-----------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|-----------------|-----------------|-------------------------|-----------------------------------------------------------------------|-----------------|-----------------|-----------------|-----------------|---------------------------------------------------------------------------------------------------------------------------------------------|-----------------|-----------------|-----------------|--|--|--|--|--|--|
| MATERIAL:              |             |                                  |                 |                 |                                                                       |                 |                 |                 |                 | FINISH:                                                                                                                                                     |                 |                 |                 |                         |                                                                       |                 |                 |                 |                 | INDUSTRY STANDARDS:                                                                                                                         |                 |                 |                 |  |  |  |  |  |  |
| SOLID BODY & COVER     |             |                                  |                 |                 | ABS/PC BLENDED PLASTIC<br>UL94-5VB FLAMMABILITY RATING                |                 |                 |                 |                 | BODY                                                                                                                                                        |                 |                 |                 |                         | LIGHT GRAY                                                            |                 |                 |                 |                 | UL508 TYPE 1, 2, 4, 4X INDOOR, 12 & 13<br>NEMA TYPE 1, 2, 4, 4X, 12 & 13<br>IEC529-IP65                                                     |                 |                 |                 |  |  |  |  |  |  |
| CLEAR COVER            |             |                                  |                 |                 | POLYCARBONATE PLASTIC<br>UL94V-0 FLAMMABILITY RATING<br>UV STABILIZED |                 |                 |                 |                 | COVER                                                                                                                                                       |                 |                 |                 |                         | LIGHT GRAY OR CLEAR                                                   |                 |                 |                 |                 | AIR AND MOISTURE VENTS, GALVANIZED STEEL INTERNAL PANEL AND STAINLESS STEEL LOCKING HASP ARE NOT INCLUDED, BUT CAN BE PURCHASED SEPARATELY. |                 |                 |                 |  |  |  |  |  |  |
| PANEL                  |             |                                  |                 |                 | 0.078 THICK ALUMINUM                                                  |                 |                 |                 |                 | PANEL                                                                                                                                                       |                 |                 |                 |                         | ANODIZED                                                              |                 |                 |                 |                 |                                                                                                                                             |                 |                 |                 |  |  |  |  |  |  |
| LATCHES & HINGES       |             |                                  |                 |                 | NON-METALLIC                                                          |                 |                 |                 |                 | COVER INCLUDES GRAY POLY-URETHANE GASKET.<br><br>UNIT COMES COMPLETE WITH (4) WALL MOUNTING BRKTS. & (4) M5 x 10mm LG. TRUSS HD. MACHINE SCREWS (NOT SHOWN) |                 |                 |                 |                         | 0.570 [14] DIA. BOSS WITH M5 x 0.8mm THREADED BRASS INSERT (4) PLACES |                 |                 |                 |                 |                                                                                                                                             |                 |                 |                 |  |  |  |  |  |  |
| WALL MOUNTING BRACKETS |             |                                  |                 |                 | STAINLESS STEEL                                                       |                 |                 |                 |                 |                                                                                                                                                             |                 |                 |                 |                         |                                                                       |                 |                 |                 |                 |                                                                                                                                             |                 |                 |                 |  |  |  |  |  |  |
|                        |             |                                  |                 |                 |                                                                       |                 |                 |                 |                 |                                                                                                                                                             |                 |                 |                 |                         |                                                                       |                 |                 |                 |                 |                                                                                                                                             |                 |                 |                 |  |  |  |  |  |  |
| VIEW LESS COVER        |             |                                  |                 |                 |                                                                       |                 |                 |                 |                 | VIEW LESS COVER AND SWINGFRAME PANEL                                                                                                                        |                 |                 |                 |                         |                                                                       |                 |                 |                 |                 |                                                                                                                                             |                 |                 |                 |  |  |  |  |  |  |
|                        |             |                                  |                 |                 |                                                                       |                 |                 |                 |                 |                                                                                                                                                             |                 |                 |                 |                         |                                                                       |                 |                 |                 |                 | 0.984 [25] TYP.                                                                                                                             |                 |                 |                 |  |  |  |  |  |  |
|                        |             |                                  |                 |                 |                                                                       |                 |                 |                 |                 |                                                                                                                                                             |                 |                 |                 |                         |                                                                       |                 |                 |                 |                 | 0.984 [25] TYP.                                                                                                                             |                 |                 |                 |  |  |  |  |  |  |
|                        |             |                                  |                 |                 |                                                                       |                 |                 |                 |                 |                                                                                                                                                             |                 |                 |                 |                         |                                                                       |                 |                 |                 |                 | 0.126 [3]                                                                                                                                   |                 |                 |                 |  |  |  |  |  |  |
|                        |             |                                  |                 |                 |                                                                       |                 |                 |                 |                 |                                                                                                                                                             |                 |                 |                 |                         |                                                                       |                 |                 |                 |                 | 0.078 [2]                                                                                                                                   |                 |                 |                 |  |  |  |  |  |  |
|                        |             |                                  |                 |                 |                                                                       |                 |                 |                 |                 |                                                                                                                                                             |                 |                 |                 |                         |                                                                       |                 |                 |                 |                 | 0.276 [7] (INSIDE)                                                                                                                          |                 |                 |                 |  |  |  |  |  |  |
|                        |             |                                  |                 |                 |                                                                       |                 |                 |                 |                 |                                                                                                                                                             |                 |                 |                 |                         |                                                                       |                 |                 |                 |                 | 0.380 [10] (INSIDE)                                                                                                                         |                 |                 |                 |  |  |  |  |  |  |
|                        |             |                                  |                 |                 |                                                                       |                 |                 |                 |                 |                                                                                                                                                             |                 |                 |                 |                         |                                                                       |                 |                 |                 |                 | DIMENSIONS = INCHES [MILLIMETERS]                                                                                                           |                 |                 |                 |  |  |  |  |  |  |
|                        |             |                                  |                 |                 |                                                                       |                 |                 |                 |                 |                                                                                                                                                             |                 |                 |                 |                         |                                                                       |                 |                 |                 |                 | NOTE: ALL DIMENSIONS HAVE ±0.039 [±1] TOLERANCE UNLESS OTHERWISE SPECIFIED                                                                  |                 |                 |                 |  |  |  |  |  |  |
| PART NO.               |             | DIMENSIONS                       |                 |                 |                                                                       |                 |                 |                 |                 |                                                                                                                                                             |                 |                 |                 |                         |                                                                       |                 |                 |                 |                 |                                                                                                                                             |                 |                 |                 |  |  |  |  |  |  |
| SOLID COVER            | CLEAR COVER | A                                | B               | C               | D                                                                     | E               | F               | G               | H               | J                                                                                                                                                           | K               | L               | M               | N                       | P                                                                     | R               | S               | T               | U               | V                                                                                                                                           | W               | X               | Y               |  |  |  |  |  |  |
| NBE-10553              | NBE-10573   | 14.640<br>[372]                  | 13.750<br>[349] | 12.768<br>[324] | 12.158<br>[309]                                                       | 11.643<br>[296] | 10.824<br>[275] | 19.170<br>[487] | 18.330<br>[466] | 17.392<br>[442]                                                                                                                                             | 16.690<br>[424] | 16.138<br>[410] | 14.760<br>[375] | 6.666<br>[169]          | 1.185<br>[30]                                                         | 18.500<br>[470] | 18.335<br>[466] | 13.980<br>[355] | 13.810<br>[337] | 13.271<br>[470]                                                                                                                             | 12.516<br>[318] | 18.110<br>[460] | 17.088<br>[434] |  |  |  |  |  |  |