


RPC-1.85

Attenuator
RPC-1.85 Plug - RPC-1.85 Jack

08AS102-K10S3



All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

According to
Mechanically compatible with

IEC 60169-32
RPC-2.40

Documents

N/A

Material and plating

Connector parts

Center conductor - plug
Center conductor - jack
Outer conductor
Coupling nut
Dielectric
Substrate

Material

CuBe
CuBe
Stainless steel
Stainless steel
PS
Al₂O₃

Plating

Gold, min. 1.27 µm, over nickel
Gold, min. 1.27 µm, over nickel
Passivated
Passivated

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG
RF_35/05.10/6.0

Technical Data Sheet				Rosenberger			
RPC-1.85		Attenuator RPC-1.85 Plug - RPC-1.85 Jack		08AS102-K10S3			
Electrical data Impedance50 Ω Frequency rangeDC to 67 GHz Return loss≥ 32 dB, DC to 4 GHz ≥ 25 dB, 4 GHz to 26.5 GHz ≥ 18 dB, 26.5 GHz to 37 GHz ≥ 12 dB, 37 GHz to 67 GHz Attenuation10 dB ± 0.5 dB, DC to 26.5 GHz 10 dB ± 1.0 dB, 26.5 GHz to 50 GHz 10 dB ± 1.5 dB, 50 GHz to 67 GHz Power handling0.5 W at 25°C							
Mechanical data Mating cycles≥ 500 Maximum torque1.65 Nm Recommended torque0.90 Nm Gauge0.00 mm to 0.03 mm							
Environmental data Operating temperature range¹+20 °C to +26 °C Storage temperature range0 °C to +50 °C RoHScompliant							
¹ Temperature range over which these specifications are valid.							
Packing Standard1 pce in box Weight6.9 g/pce							
While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.							
Draft		Date		Approved		Date	
Marcel Panicke		17.01.08		Lars Ramtke		18.06.15	
Rev.		Engineering change number		Name		Date	
c00		15-0783		Marion Striegler		18.06.15	
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de				Tel. : +49 8684 18-0 Email : info@rosenberger.de			Page 2 / 2