

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		L4	REVISED PER ECR 09-025791	02DEC09	JR	GS

1. FINISH— SILVER PLATE 500 uINCHES THICK MINIMUM.
2. FINISH— SILVER PLATE 200 uINCHES THICK MINIMUM.
3. FINISH— NICKEL PLATE 40 uINCHES THICK MINIMUM.
4. FINISH— GOLD PLATE 50 uIN MIN THICK MINIMUM.
5. FINISH—
6. PLATING NOTES ARE TO BE INTERPRETED AS FOLLOWS: 1-2 AS 1 OVER 2.
- △



 PRODUCT IS SOLD BY THE FOOT.
- △8

 PRELIMINARY PART NUMBER.
9. FINISH— GOLD PLATE 40 uIN THICK MINIMUM.
10. FINISH— NICKEL PLATE 100 uIN THICK MINIMUM.
- △1

 OBSOLETE
- △2

 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- △3

 10 LOUVERS, NOT TO EXCEED 1.000 INCHES.



△12 OBSOLETE		△8	2.67[.105]	2.00[5.08] MAX	1-3	20 MIN	0.25[.010]	-	2-192002-0
	.100	△8	2.75[.110]		4-3	△7	0.25[.010]	-	1-192002-9
	.100	△8	2.75[.110]	1.00 ^{±.01} _{-.00}	1-3	10-11	0.25[.010]	-	1-192002-8
	.090		2.79[.110]		9-10	△7	0.25[.010]	-	1-192002-7
	.100		2.67[.105]		4-3	△7	0.15[.006]	-	1-192002-6
		△8	2.67[.105]	-	4-3	3	0.15[.006]	-	1-192002-5
	.090	△8	2.67[.105]		4-3	△7	0.15[.006]	-	1-192002-4
		△8	2.67[.105]	-	1-3	3	0.15[.006]	-	1-192002-3
		△8	2.67[.105]		1-3	△7	0.15[.006]	-	1-192002-2
		△8	2.67[.105]		4-3	△7	0.15[.006]	-	1-192002-1
△12 OBSOLETE		△8	2.79[.110]	-	UNPL	6	0.25[.010]	-	1-192002-0
			2.79[.110]	203.2 [8.00]	1-3	--	0.25[.010]	00517	192002-9
			2.79[.110]	--	1-3	4	0.25[.010]	00513	192002-8
△12 OBSOLETE	.100	△11	2.79[.110]	--	1-3	9	0.25[.010]	00515	192002-7
			2.79[.110]	--	1-3	5	0.25[.010]	00514	192002-6
			2.79[.110]	152.4 [6.00]	1-3	--	0.25[.010]	00516	192002-5
			2.79[.110]	△13	1-3	△7	0.25[.010]	00502	192002-4
			2.79[.110]		UNPL	△7	0.25[.010]	00503	192002-3
			2.67[.105]		1-3	△7	0.15[.006]	00501	192002-2
			2.67[.105]		UNPL	△7	0.15[.006]	00500	192002-1
A	LOUVER HT		LENGTH		PLATING (NOTE)	NUM LOUV	MAT'L THK	WAS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm[inches]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.5 [.02]

3 PLC ± 0.25 [.010]

4 PLC ± -

ANGLES ± -

FINISH SEE TABLE

MATERIAL

BeCu

DWN -

CHK S.SIEGRIST 12-16-92

APVD -

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

Tyco Electronics

Tyco Electronics Corporation

Harrisburg, PA 17105-3608

NAME

CONTACT BAND, STRIP

SIZE A2

CAGE CODE 00779

DRAWING NO C=192002

RESTRICTED TO -

SCALE 1:1

SHEET 1 OF 1

REV L4