





TABLE 1

DASH No.	Dim.	Amount of Pins	Dim.A	Dim.B	Dim.C
-000 06 XX LF	6		2.54	18.31	8.46
-000 10 XX LF	10		5.08	20.85	11.00
-000 12 XX LF	12		6.35	22.12	12.27
-000 14 XX LF	14		7.62	23.39	13.54
-000 16 XX LF	16		8.89	24.66	14.81
-000 20 XX LF	20		11.43	27.20	17.35
-000 26 XX LF	26		15.24	31.01	21.16
-000 30 XX LF	30		17.78	33.55	23.70
-000 34 XX LF	34		20.32	36.09	26.24
-000 40 XX LF	40		24.13	39.90	30.05
-000 44 XX LF	44		26.67	42.44	32.59
-000 50 XX LF	50		30.48	46.25	36.40
-000 60 XX LF	60		36.83	52.60	42.75
-000 64 XX LF	64		39.37	55.14	45.29
-000 66 XX LF	66		40.64	56.41	46.56
-000 68 XX LF	68		41.91	57.68	47.83



NOTE:

1. MATERIAL:
HOUSING: HIGH TEMP PLASTIC, UL94-V0, BLACK
TERMINAL: COPPER ALLOY, SQ=0.40±0.03MM
2. FINISH:
TERMINAL: GOLD AT CONTACT,
G/F OVER 1um(40u") MIN Ni OVER ALL
3. SPEC.:
PRODUCT SPEC: GS-12-629
PACKING SPEC: GS-14-1420
4. THE HSG. WILL WITHSTAND EXPOSURE TO 260C
PEAK TEMP. FOR 10 SEC. IN A CONVECTION INFRA-RED
OR VAPOR PHASE REFLOW OVEN.
5. PRODUCT NUMBERING:
20021621 - 0 0 0 XX X X LF

LEAD FREE

PLATING:

1:GOLD FLASH ALL OVER
4:0.25um(10u")GOLD AT CONTACT
8:0.76um(30u")GOLD AT CONTACT
9:1u" GOLD OVER 30u" PdNi AT CONTACT

PACKING

T: TUBE
D: TUBE + CAP
C: T&R + CAP (30 POS)

PIN COUNT

SEE TABLE 1

mat'l. code				surface	tolerance	projection	product family		
				ISO1302	ISO1101 ISO406		MINITEK		
litr	ecr no	dr	date	tolerances	unless otherwise specified	specified	title		
A	T09-1117	S.LIN	09/15/09	angles	0.X±0.38	MM	1.27X1.27MM BTB EJECT HEADER		
B	T10-0027	S.LIN	01/20/10	0°±2°	0.XX±0.25	scale 2:1	SMT		
C	T-005600	S.LIN	01/16/12	0°±2°	0.XXX±0.10		dwg no		
D	EX-N-010367	ZK	01/16/12	dr	STERLING LIN	09/15/09	sheet 1 of 1 size		
E	EX-N-010623	ZK	02/12/12	engr	STERLING LIN	09/15/09	20021621		
F	EX-N-1727	TIM	03/20/14	chr	GRAY HSEH	09/15/09	A4		
				appd	JOSEPH	09/15/09	type Product Customer Drawing		
sheet index		revision	F						
		sheet	1						