

ADVANCE DATA SHEET

SKY77189 Power Amplifier Module for WCDMA / HSDPA Band VIII (880–915 MHz)

Applications

- WCDMA handsets
- HSDPA

Features

- Low voltage positive bias supply
3.2 V to 4.2 V
- Good linearity
- High efficiency
- 40% @ 28.75 dBm
- Large dynamic range
- Small, low profile package
- 3 mm x 3 mm x 0.85 mm
- 10-pad configuration
- Power down control
- InGaP
- Supports low collector voltage operation
- Digital Enable
- No V_{REF} required
- CMOS compatible control signals
- Integrated Directional Coupler

The SKY77189 Power Amplifier Module (PAM) is a fully matched 10-pad surface mount module developed for Wideband Code Division Multiple Access (WCDMA) applications. This small and efficient module packs full 880–915 MHz bandwidth coverage into a single compact package. Because of high efficiencies attained throughout the entire power range, the SKY77189 delivers unsurpassed talk-time advantages. The SKY77189 meets the stringent spectral linearity requirements of High Speed Downlink Packet Access (HSDPA) data transmission with high power added efficiency. A directional coupler is integrated into the module thus eliminating the need for any external coupler.

The single Gallium Arsenide (GaAs) Microwave Monolithic Integrated Circuit (MMIC) contains all active circuitry in the module. The MMIC contains on-board bias circuitry, as well as input and interstage matching circuits. Output match into a 50-ohm load is realized off-chip within the module package to optimize efficiency and power performance.

The SKY77189 PAM is manufactured with Skyworks' InGaP GaAs Heterojunction Bipolar Transistor (HBT) BiFET process that provides for all positive voltage DC supply operation while maintaining high efficiency and good linearity. Primary bias to the SKY77189 is supplied directly from any three-cell Ni-Cd, a single-cell Li-Ion, or other suitable battery with an output in the 3.2 to 4.2 volt range. No V_{REF} voltage is required. Power down is accomplished by setting the voltage on VENABLE to zero volts. No external supply side switch is needed as typical "off" leakage is a few microamperes with full primary voltage supplied from the battery.

NEW Skyworks Green™ products are RoHS (Restriction of Hazardous Substances)-compliant, conform to the EIA/EICTA/JEITA Joint Industry Guide (JIG) Level A guidelines, are halogen free according to IEC-61249-2-21, and contain < 1,000 ppm antimony trioxide in polymeric materials.





Figure 1. Functional Block Diagram

Electrical Specifications

The following tables list the electrical characteristics of the SKY77189 Power Amplifier. Table 1 lists the absolute maximum ratings, while Table 2 shows the recommended operating conditions to achieve WCDMA and HSDPA performance

characteristics listed in Table 4. Table 3 presents a truth table for the power settings. Table 5 and Table 6 provide the standard test configurations for WCDMA (STC1) and HSDPA (STC2), respectively.

Table 1. Absolute Maximum Ratings¹

Parameter	Symbol	Minimum	Nominal	Maximum	Unit
RF Input Power	P _{IN}	—	0	10	dBm
Supply Voltage	V _{CC1} , V _{CC2}	—	3.4	6.0	Volts
Enable Control Voltage	V _{EN}	—	1.8	4.2	Volts
Mode Control Voltage	V _{MODE_0}	—	1.8	4.2	Volts
	V _{MODE_1}	—	1.8	4.2	
Case Temperature ²	Operating	T _{CASE}	-30	25	°C
	Storage	T _{STG}	-55	—	

¹ No damage assuming only one parameter is set at limit at a time with all other parameters set at nominal value.

² Case Operating Temperature (T_{CASE}) refers to the temperature of the GROUND PAD at the underside of the package.

Table 2. Recommended Operating Conditions

Parameter	Symbol	Minimum	Nominal	Maximum	Unit	
RF Output Power ¹	WCDMA	P _{O_MAX}	—	28.75	dBm	
	HSDPA	P _{O_MAX}	—	27.75		
Operating Frequency	F ₀	880.0	897.5	915.0	MHz	
Supply Voltage	V _{CC1} , V _{CC2}	3.2 ²	3.4	4.2	Volts	
Enable Control Voltage	Low	V _{EN_L}	0.0	0.0	Volts	
	High	V _{EN_H}	1.35	1.8		3.1
Mode Control Voltage	Low	V _{MODE_0}	1.35	1.8	Volts	
		V _{MODE_1}	1.35	1.8		3.1
	Medium	V _{MODE_0}	1.35	1.8		3.1
		V _{MODE_1}	0.0	0.0		
	High	V _{MODE_0}	0.0	0.0		0.5
		V _{MODE_1}	0.0	0.0		
Case Operating Temperature	T _{CASE}	-20	+25	+85	°C	

¹ For V_{CC} < 3.4 V, output power back-off = 0.5 dB.

² Recommended minimum V_{CC} for maximum power output is indicated. V_{CC2} down to 0.5 V may be used for backed-off power when using DC/DC converter to conserve battery current.

Table 3. Modes of Operation

Power Setting	ENABLE	V _{MODE_0}	V _{MODE_1}	V _{CC}
Power Down Mode	Low	Low	Low	On
Standby Mode	Low	—	—	On
High Power Mode (17.0 dBm ≤ P _{OUT} ≤ 28.75 dBm)	High	Low	Low	On
Medium Power Mode (7.0 dBm ≤ P _{OUT} ≤ 17.0 dBm)	High	High	Low	On
Low Power Mode (P _{OUT} ≤ 7.0 dBm)	High	High	High	On
Optional Lower V _{CC} Mode (P _{OUT} ≤ 7.0 dBm)	High	Low	Low	1.5 V

Table 4. Electrical Specifications for Nominal Operating Conditions ¹

Characteristics	Symbol	Condition	Minimum	Typical	Maximum	Unit	
Gain	GLOW	P ₀ = 7.0 dBm	8.0	12.0	16.0	dB	
	GMID	P ₀ = 17.0 dBm	13.0	18.0	24.0		
	GHIGH	P ₀ = 28.75 dBm	24.5	27.0	29.5		
Rx Band Gain	RxG	—	—	—	-0.5	dB	
	RxG_GPS	—	—	-14.0	-3.0		
	RxG_ISM	—	—	-20.0	-6.0		
Power Added Efficiency	PAELOW	P ₀ = 7.0 dBm	—	9.0	—	%	
	PAEMID	P ₀ = 17.0 dBm	—	16.5	—		
	PAEHIGH	P ₀ = 28.75 dBm	40.0	—	—		
Total Supply Current	I _{CC_LOW}	P ₀ = 7.0 dBm	—	7.5	—	mA	
	I _{CC_MID}	P ₀ = 17.0 dBm	—	40.0	—		
	I _{CC_HIGH}	P ₀ = 28.75 dBm	—	—	550		
Quiescent Current	I _{q_LOW}	Low Power Mode	—	2.5	—	mA	
	I _{q_MED}	Medium Power Mode	—	10.0	—		
Enable Control Current	I _{EN}	—	—	0.01	0.1	mA	
Mode Control Current	I _{MODE_0}	—	—	0.05	0.1	mA	
	I _{MODE_1}	—	—	0.05	0.1		
Total Supply Current in Power Down Mode	I _{PD}	V _{CC} = 3.4 V V _{EN} = Low V _{MODE_0} = Low V _{MODE_1} = Low	—	—	10	μA	
Adjacent Channel Leakage power Ratio ²	5 MHz offset	ACLR5	P ₀ = 7.0 dBm	—	-42	-36	dBc
			P ₀ = 17.0 dBm	—	-46	-36	
			P ₀ = 28.75 dBm	—	-40	-36	
	10 MHz offset	ACLR10	P ₀ = 7.0 dBm	—	-65	-46	
			P ₀ = 17.0 dBm	—	-60	-46	
			P ₀ = 28.75 dBm	—	-55	-46	
Harmonic Suppression	Second	f ₀₂	P ₀ ≤ 28.75 dBm	—	-45	-35	dBc
	Third	f ₀₃		—	-50	-35	
Tx Noise in Rx Bands	Rx		925 MHz–960 MHz	—	-138	-136	dBm/Hz
	GPS Rx		1574 MHz–1577 MHz	—	-142	-140	
	ISM Rx		2400 MHz–2483.5 MHz	—	-145	-143	
Input Voltage Standing Wave Ratio	VSWR	—	—	1.5:1	1.8:1	—	
EVM	EVM1	P ₀ = P _{MAX}	—	—	3.35	%	
	EVM2	P ₀ = P _{MAX} - 3	—	—	2.50		
Rise / Fall Time	DC	T _{ONDC}	—	—	20	μs	
		T _{OFFDC}	—	—	20		
	RF	T _{ONRF}	—	—	6		
		T _{OFFRF}	—	—	6		
Coupling Factor	CPL	P ₀ = 28.75 dBm	—	-18	—	dB	
Stability (Spurious output)	S	5:1 VSWR All phases	—	—	-70	dBc	
Ruggedness – no damage ³	Ru	P ₀ ≤ 28.75 dBm	10:1	—	—	VSWR	

¹ Per Table 2 over dynamic range up to 28.75 dBm output power, unless specified otherwise.

² ACLR is expressed as a ratio of total adjacent power to WCDMA modulated in-band, both measured in 3.84 MHz bandwidth at specified offsets.

³ All phases, time = 10 seconds.

Table 5. Standard Test Configuration – STC1 WCDMA Mode

Parameter	Level	Spread Code	Spread Factor	I/Q	β_c	β_d	β_{hs}	β_{ec}	β_{ed}	Relative Power (dB)
DPCCH	15 kbps	0	256	Q	8/15	—	—	—	—	-6.547
DPDCH	60 kbps	16	64	I	—	15/15	—	—	—	-1.087

Table 6. Standard Test Configuration – STC2 HSDPA Mode

Parameter	Level	Spread Code	Spread Factor	I/Q	β_c	β_d	β_{hs}	β_{ec}	β_{ed}	Relative Power (dB)
DPCCH	15 kbps	0	256	Q	12/15	—	—	—	—	-7.095
DPDCH	60 kbps	16	64	I	—	15/15	—	—	—	-5.157
HS-DPCCH	15 kbps	64	256	Q	—	—	24/15	—	—	-3.012

Evaluation Board Description

The evaluation board is a platform for testing and interfacing design circuitry. To accommodate the interface testing of the SKY77189, the evaluation board schematic and assembly

diagrams are included for preliminary analysis and design. Figure 2 shows the basic schematic of the board for the 880 MHz to 915MHz range.




Figure 2. Evaluation Board Schematic





Figure 3. Evaluation Board Assembly Diagram

Package Dimensions

The SKY77189 is a multi-layer laminate base, overmold encapsulated modular package designed for surface mount solder attachment to a printed circuit board. Figure 4 is a mechanical drawing of the pad layout for this package. Figure 5 provides a

recommended phone board layout footprint for the PAM to help the designer attain optimum thermal conductivity, good grounding, and minimum RF discontinuity for the 50-ohm terminals.



NOTES: Unless otherwise specified.

1. DIMENSIONING AND TOLERANCING IN ACCORDANCE WITH ASME Y14.5 – 1994
2. SEE APPLICABLE DIAGRAM AND DEVICE ASSEMBLY DRAWING FOR DIE AND COMPONENT PLACEMENT.
3. PAD DEFINITIONS PER DETAILS ON DRAWING.
4. PCB TYPE 4L PPG TEV MCM (100).

Figure 4. Dimensional Diagram for 3 mm x 3 mm x 0.85 mm, 10-Pad Package (All Views) – SKY77189

200887_004







Figure 5. Phone PCB Layout Footprint for 3 mm x 3 mm, 10-Pad Package – SKY77189

Package Description

Figure 6 shows the pad functions and the pad numbering convention, which starts with pad 1 in the upper left and increments counter-clockwise around the package. Typical case markings are illustrated in Figure 7.



Pad layout as seen from Top View looking through the package. GROUND PAD is package underside.

200887_006

Figure 6. SKY77189 Pad Names and Configuration (Top View)

Package Handling Information

Because of its sensitivity to moisture absorption, this device package is baked and vacuum-packed prior to shipment. Instructions on the shipping container label must be followed regarding exposure to moisture after the container seal is broken, otherwise, problems related to moisture absorption may occur when the part is subjected to high temperature during solder assembly.


The SKY77189 is capable of withstanding an MSL3/260 °C solder reflow. Care must be taken when attaching this product, whether it is done manually or in a production solder reflow environment. If the part is attached in a reflow oven, the temperature ramp rate should not exceed 3 °C per second; maximum temperature should not exceed 260 °C. If the part is manually attached, precaution should be taken to insure that the part is not subjected to temperatures exceeding 260 °C for more than 10 seconds. For details on attachment techniques, precautions, and handling procedures recommended by Skyworks, please refer to Skyworks Application Note: *PCB Design and SMT Assembly/Rework*, Document Number 101752. Additional information on standard SMT reflow profiles can also be found in the JEDEC Standard J-STD-020.

Production quantities of this product are shipped in the standard tape-and-reel format (Figure 8).

Electrostatic Discharge Sensitivity (ESD)

To avoid ESD damage, both latent and visible, it is very important that the product assembly and test areas follow the Class 1 ESD handling precautions listed below.


- Personnel Grounding
 - Wrist Straps
 - Conductive Smocks, Gloves and Finger Cots
 - Antistatic ID Badges
- Protective Workstation
 - Dissipative Table Top
 - Protective Test Equipment (Properly Grounded)
 - Grounded Tip Soldering Irons
 - Solder Conductive Suckers
 - Static Sensors
- Facility
 - Relative Humidity Control and Air Ionizers
 - Dissipative Floors (less than 10⁹ Ω to GND)
- Protective Packaging and Transportation
 - Bags and Pouches (Faraday Shield)
 - Protective Tote Boxes (Conductive Static Shielding)
 - Protective Trays
 - Grounded Carts
 - Protective Work Order Holders



NOTE: Lines 1, 2, 3 have a maximum of 7 characters
Line 1 = Part Number and Version
Line 2 = Lot Number
Line 3 = Year–Week–Country Code (MX)

200887_007

Figure 7. Typical Case Markings



NOTES:

1. CARRIER TAPES MUST MEET ALL REQUIREMENTS OF SKYWORKS GP01–D232 PROCUREMENT SPEC FOR TAPE AND REEL SHIPPING.
- ② CARRIER TAPE SHALL BE BLACK CONDUCTIVE POLYCARBONATE OR POLYSTYRENE.
3. COVER TAPE SHALL BE TRANSPARENT CONDUCTIVE PRESSURE-SENSITIVE ADHESIVE (PSA) MATERIAL W/ 9.3 mm WIDTH.
4. ESD-SURFACE RESISTIVITY SHALL BE $\leq 1 \times 10^{10}$ OHMS/SQUARE PER EIA, JEDEC TNR SPECIFICATION.
5. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE: ± 0.2 mm
6. Ao & Bo MEASURED ON PLANE 0.3 mm ABOVE THE BOTTOM OF THE POCKET.
7. ALL DIMENSIONS ARE IN MILLIMETERS.
8. PART NO.: KS-1208-332 REV. 00 (PLEASE INDICATE ON PURCHASE ORDER).
9. NUMBER OF PARTS per 13 inch (DIAMETER) x 12 mm REEL: 2500/4500.

KOSTAT CARRIER TAPE

CARRIER TAPE OVERMOLD MCM / RFLGA 3 x 3 x 1.4 mm BODY SIZE GP01-D232-187C
 101568_002

Figure 8. Dimensional Diagram for Carrier Tape Body Size 3 mm x 3 mm x 1.4 mm – MCM

Ordering Information

Model Number	Manufacturing Part Number	Product Revision	Package	Operating Temperature
SKY77189	SKY77189		MCM 3 x 3 x 0.85 mm	-20 °C to +85 °C

Revision History

Revision	Date	Description
A	April 4, 2008	Initial Release – Advance Information
B	April 23, 2008	Revise: Tables 1–4; Figures 1–3, 6; Tx freq. to 880–915; Rx freq. to 925–960
C	May 20, 2008	Revise: Features list (p1); Tables 1, 2, 4, 5; Figures 2–5; Add: Skyworks Green tag (p1)
D	November 13, 2008	Revise: Features list (p1); Figure 3; Tables 1–4; ESD section Add: Tables 5, 6
E	February 3, 2009	Revise: Order Information table, Package column
F	May 15, 2009	Revise: Figure 5 Add: Figure 8
G	February 2, 2010	Revise: Figure 1 Add: Figure 8

References

Skyworks Application Note: PCB Design and SMT Assembly/Rework, Document Number 101752.

Standard SMT Reflow Profiles: JEDEC Standard J–STD–020

Copyright © 2008, 2009, 2010, Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. (“Skyworks”) products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED “AS IS” WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of stated published specifications or parameters.

Skyworks, the Skyworks symbol, “Breakthrough Simplicity,” DCR, Helios, HIP3, Innovation to Go, Intera, iPAC, LIPA, Polar Loop, and System Smart are trademarks or registered trademarks of Skyworks Solutions, Inc., in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksin.com, are incorporated by reference.