



Contact data 06/2	Conditions	Min	Typ	Max	Unit
Contact - No.			06/2		
Contact rating	Any DC combination of V & A not to exceed their individual max.'s			10	W
Switching voltage	DC or Peak AC			200	V
Switching current	DC or Peak AC			0,5	A
Carry current	DC or Peak AC			1	A

Special Product Data	Conditions	Min	Typ	Max	Unit
Number of contacts			1		
Contact - form			A - NO		
Sensor-resistance				680	mOhm
Housing material LS			Polypropylene		
Material of float			Polypropylene		
Case colour			white		
Sealing compound			Polyurethan		
Reach / RoHS conformity			yes		

Environmental data	Conditions	Min	Typ	Max	Unit
Shock				50	g
Vibration	from 10 - 1200 Hz			20	g
Operating temperature		-30		80	°C
Operating temperature		-5		80	°C
Storage temperature		-30		80	°C
Safety class			IP68 until the thread		

Cable specification	Conditions	Min	Typ	Max	Unit
Cable type			round cable		
Cable material			PVC		
Cross section			0.14 sq-mm		

General data	Conditions	Min	Typ	Max	Unit
Mounting advice			over 5m cable, a resistor is recommended.		
Tightening torque				0,5	Nm

Modifications in the sense of technical progress are reserved

Designed at: 29.01.08 Designed by: BUELTZHOEFFER

Approval at: 29.02.08 Approval by: BUELTZHOEFFER

Last Change at: 31.03.15 Last Change by: WKOVACS

Approval at: 31.03.15 Approval by: DKUECHLER

Rev. No.: 05