

UCB

Chip Type, Long Life Assurance



For SMD



Long Life

Anti-Solvent
Feature

- Chip type with load life of 7000 hours at +105°C.
- Applicable to automatic mounting machine fed with carrier tape.
- Compliant to the RoHS directive (2011/65/EU).

UCB

Long Life UUL





UCW




■ Specifications

Item	Performance Characteristics															
Category Temperature Range	-25 to +105°C															
Rated Voltage Range	6.3 to 50V															
Rated Capacitance Range	1 to 1000μF															
Capacitance Tolerance	±20% at 120Hz, 20°C															
Leakage Current	After 2 minutes' application of rated voltage at 20°C, leakage current is not more than 0.03 CV or 4 (μA) , whichever is greater.															
Tangent of loss angle (tan δ)	Measurement frequency : 120Hz at 20°C															
	Rated voltage (V)		6.3	10	16	25	35	50								
	tan δ (MAX.)		0.32	0.28	0.26	0.16	0.14	0.14								
Stability at Low Temperature	Measurement frequency : 120Hz															
	Rated voltage (V)		6.3	10	16	25	35	50								
	Impedance ratio ZT / Z20 (MAX.)	Z-25°C / Z+20°C	4	3	2	2	2	2								
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 7000 hours at 105°C.															
									Capacitance change		Within ±30% of the initial capacitance value					
									tan δ		300% or less than the initial specified value					
									Leakage current		Less than or equal to the initial specified value					
Shelf Life	After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.															
Resistance to soldering heat	The capacitors are kept on a hot plate for 30 seconds, which is maintained at 250°C. The capacitors shall meet the characteristic requirements listed at right when they are removed from the plate and restored to 20°C.															
						Capacitance change		Within ±10% of the initial capacitance value								
						tan δ		Less than or equal to the initial specified value								
Marking	Black print on the case top.															
						Leakage current		Less than or equal to the initial specified value								

■ Chip Type



Type numbering system (Example : 16V 100μF)



Voltage

V	6.3	10	16	25	35	50
Code	j	A	C	E	V	H

●Dimension table in next page.

UCB

■ Dimensions

Cap.(μF)	V Code	6.3		10		16		25		35		50	
		0J		1A		1C		1E		1V		1H	
1	010									4 × 7	6.2		
2.2	2R2									4 × 7	11		
3.3	3R3									4 × 7	14		
4.7	4R7									4 × 7	15		
10	100					4 × 7	18			5 × 7	25		
22	220	4 × 7	22			5 × 7	30			6.3 × 7	42		
33	330			5 × 7	35			6.3 × 7	48	6.3 × 8.7	57	8 × 10	77
47	470	5 × 7	36			6.3 × 7	50	6.3 × 8.7	63			8 × 10	92
100	101	6.3 × 7	60			6.3 × 8.7	81	8 × 10	116			10 × 10	151
220	221	6.3 × 8.7	101	8 × 10	141					10 × 10	216		
330	331	8 × 10	160										
470	471					10 × 10	254					Case size	Rated
1000	102	10 × 10	313									φ D × L (mm)	ripple

Rated ripple current (mA_{rms}) at 105°C 120Hz

● Frequency coefficient of rated ripple current

Frequency	50 Hz	120 Hz	300 Hz	1 kHz	10 kHz or more
Coefficient	0.70	1.00	1.17	1.36	1.50

- Taping specifications are given in page 23.
- Recommended land size, soldering by reflow are given in page 18, 19.
- Please refer to page 3 for the minimum order quantity.