




NOTES:
 1. $\odot$ REPRESENTS A CRITICAL DIMENSION.
 2. PACKAGING IN TRAY.


DESIGNED & DIMENSIONED IN MILLIMETERS[INCHES]

USBR-A-D-X-O-TH

TYPE —
 -A
 ROW SPECIFICATION —
 -D: DOUBLE ROW
 PLATING SPECIFICATION —
 -F: 1 μ " FLASH GOLD ON CONTACT AREA,
 MATTE TIN ON TAIL
 -S: 30 μ " SELECTIVE GOLD ON CONTACT AREA,
 MATTE TIN ON TAIL
 OPTION —
 -TH: THROUGH HOLE
 COLOR —
 -O: ORANGE



RECOMMENDED PCB LAYOUT



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS[INCHES]. TOLERANCES ARE: DECIMALS ANGLES X.X: $\pm$ 0.25[.01] X.XX: $\pm$ 0.13[.005] X.XXX: $\pm$ 0.05[.002]	* PROPRIETARY NOTE * THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.	520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code: 55322	
MATERIAL: DO NOT SCALE DRAWING INSULATOR: PA9T, COLOR: ORANGE CONTACT: COPPER ALLOY SHELL: COPPER ALLOY	SHEET SCALE: 2:1 DESCRIPTION: HIGH RETENTION USB TYPE A DOUBLE ROW DWG. NO. USBR-A-D-X-O-TH	BY: TOM TANG 12/30/2008 SHEET 1 OF 1	