






This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

PRODUCT NUMBER
85674-XXX OR 85674-XXXX
85674-XXYLF OR 85674-XXYYLF



mat'l code				SEE NOTES				tolerances unless otherwise specified				CUSTOMER			FCI		
ltr	ecr no.	dr	date	linear	dr	date	linear	0.X ±0.3	projection	projection	projection	COPY			www.fciconnect.com		
CC	V06-0569	DCH	2006-06-12	linear	dr	date	linear	0.XX ±0.13	projection	projection	projection	title			METRAL SIGNAL HEADER		
CD	DG07-0409	Cenh	10/18/07	linear	dr	date	linear	.XXX ±.051	projection	projection	projection	product family			METRAL		
CE	DG07-0487	Cenh	12/04/07	angles	dr	date	angles	0° ±2°	projection	projection	projection	size			213		
CF	DG08-0246	Cenh	09/26/08	dr	dr	date	dr	T.BRUNGARD 11/19/99	projection	projection	projection	dwg no			85674		
CG	DG08-0303	Cenh	10/30/08	enrg	dr	date	enrg	M.STRAWER 11/19/99	projection	projection	projection	scale			2:1		
CH	DG09-0073	Cenh	03/05/09	chr	dr	date	chr	M.STRAWER 11/19/99	projection	projection	projection	sheet			1 of 10		
-	-	-	-	appd	dr	date	appd	M.STRAWER 02/29/00	projection	projection	projection	cage code			22526		
sheet index	revision sheet	CH	CH	CH	CH	CH	CH	CH	CH	CH	CH	CH	CH	CH	CH	CH	CH

Pro/E

PDM: Rev:CH


STATUS: Released

Printed: May 16, 2009



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18



3 | 4

KEY (SIGNAL PRESS-FIT)		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
1	5.00	4.30
2	5.75	4.30
3	6.50	4.30
4	7.25	4.30
5	5.00	13.60
6	5.75	13.60
7	6.50	13.60
8	7.25	13.60
11	6.50	17.00
19	8.00	4.30
20	8.00	13.60
21	8.00	17.00
22	5.00	12.10
29	8.00	14.60
30	5.00	12.90
31	5.75	12.90
40	5.00	15.60
41	6.50	15.60
49	5.75	15.10
52	8.00	15.10
59	5.00	11.80
61	6.50	11.80
64	5.75	14.90
65	5.00	16.30
67	7.25	16.30

mat'l code				- -		tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com				
ltr	ecn no.	dr	date	linear	0.X ±0.3		COPY			title METRAL SIGNAL HEADER 1 MOD, 5 ROW PRESS-FIT				
CH					0.XX ±0.13		projection							
					.XXX ±.051									
				angles	0° ±2°					product family METRAL				
				dr	T.BRUNGARD	11/19/99						size A	dwg no 85674	
				enr	M.STRAWER	11/19/99								
				chr	M.STRAWER	11/19/99								
				appd	M.STRAWER	02/29/00								
sheet index		revision sheet												

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X01	E	1	1	1	1	1	1
	D	1	1	1	1	1	1
-----	C	1	1	2	2	2	2
85674-X01LF	B	1	1	1	1	1	1
	A	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X07	E	5	5	5	5	5	5
	D	5	5	5	5	5	5
-----	C	8	8	8	8	8	8
85674-X07LF	B	5	5	5	5	5	5
	A	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X13	E	I	I	-	I	I	
	D	I	I	-	I	I	
-----	C	I	I	-	-	-	
85674-X13LF	B	I	I	-	I	I	
	A	I	I	-	I	I	

METRAL P/N	ROW	CONTACT MOD. I				
		1	2	3	4	5
85674-X17 ----- :85674-X17LF	E	22	22	22	22	22
	D	22	22	22	31	22
	C	22	22	22	22	22
	B	22	22	22	22	22
	A	22	22	22	22	7 2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X2I	E	1	2	4	4	2	4
	D	1	2	4	4	2	4
-----	C	1	2	4	4	2	4
85674-X2ILF	B	1	2	4	4	2	4
	A	1	2	4	4	2	4

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X02	E	5	5	5	5	5	5
	D	5	5	5	5	5	5
-----	C	5	5	6	6	6	6
85674-X02LF	B	5	5	5	5	5	5
	A	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X08	E	8	8	8	8	8	5
	D	8	8	8	8	8	5
-----	C	8	8	8	8	8	5
85674-X08LF	B	8	8	8	8	8	5
	A	8	8	8	8	8	5

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X14	E	2	2	4	49	49	4
	D	2	2	4	49	49	4
-----	C	2	2	4	49	49	4
85674-X14LF	B	2	2	4	49	49	4
	A	2	2	4	49	49	4

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X18	E	7	7	7	7	7	7
	D	7	7	7	7	7	7
-----	C	7	7	7	7	7	7
85674-X18LF	B	-	7	7	7	7	7
	A	-	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X22	E	7	7	7	7	7	7
	D	7	7	7	3	7	7
-----	C	7	7	7	7	7	7
85674-X22LF	B	7	7	7	7	7	7
	A	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X03	E	I	I	I	I	I	I
	D	I	I	I	I	I	I
-----	C	4	4	4	4	4	4
85674-X03LF	B	I	I	I	I	I	I
	A	I	I	I	I	I	I

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X09	E	5	5	5	5	5	5
	D	5	5	5	5	5	5
-----	C	5	5	5	5	5	5
85674-X09LF	B	5	5	5	5	5	8
	A	5	5	5	5	5	8

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X15	E	49	49	49	49	2
	D	49	49	49	49	2
----- 85674-X15LF	C	49	49	49	49	2
	B	49	49	49	49	2
	A	49	49	49	49	2

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X19	E	3	3	3	3	3
	D	3	3	3	3	3
-----	C	3	3	3	3	3
85674-X19LF	B	-	3	3	3	3
	A	-	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X23	E	7	7	7	7	7	7
	D	7	7	7	7	7	7
-----	C	7	7	7	7	7	7
85674-X23LF	B	3	7	7	7	7	7
	A	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X04	E	I	I	I	I	I	I
	D	I	I	I	I	I	I
-----	C	8	8	8	8	8	8
85674-X04LF	B	I	I	I	I	I	I
	A	I	I	I	I	I	I

METRAL P/N	ROW	CONTACT CODE MOD. I					
		I	2	3	4	5	6
85674-X10	E	2	2	2	2	2	2
	D	2	2	2	2	2	2
-----	C	2	2	2	2	2	2
85674-X10LF	B	2	-	-	-	-	2
	A	2	-	2	-	-	2

METRAL P/N	ROW	CONTACT CODE MOD. I				
		I	2	3	4	5
85674-X16 ----- 85674-X16LF	E	2	2	2	2	2
	D	1	3	2	3	2
	C	1	3	2	3	2
	B	1	3	2	3	2
	A	1	3	2	3	2

METAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X20 ----- 85674-X20LF	E	2	2	2	2	2	2
	D	2	2	2	2	2	2
	C	2	2	2	2	2	2
	B	2	2	2	2	1	1
	A	2	2	2	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X24	E	52	7	7	7	7	7
	D	52	7	22	7	7	7
-----	C	52	7	7	7	7	7
85674-X24LF	B	52	7	7	7	7	7
	A	52	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X05	E	8	8	8	8	8	8
	D	8	8	8	8	8	8
-----	C	8	8	8	8	8	8
85674-X05LF	B	5	5	5	5	5	5
	A	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-XII	E	6	6	6	6	20	6
	D	6	6	6	6	20	6
-----	C	6	6	6	20	20	6
85674-XIIIF	B	6	6	6	6	20	6
	A	6	6	6	6	20	6

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X06	E	5	5	5	5	5	5
	D	5	5	5	5	5	5
----- 85674-X06LF	C	5	5	5	5	5	5
	B	5	5	5	8	8	5
	A	5	5	5	8	8	5

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X12	E	3	2	2	2	2	2
	D	3	2	2	2	1	2
-----	C	3	2	2	2	2	2
85674-X12LF	B	3	2	2	2	2	2
	A	3	2	2	2	2	2

[illegible]



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

A

B

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X25	E	2	2	2	2	2
	D	2	2	2	2	2
	C	2	2	2	2	2
85674-X25LF	B	2	-	-	-	2
	A	2	-	2	-	2

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X26	E	2	2	2	6	6
	D	2	2	2	6	6
	C	2	2	2	6	6
85674-X26LF	B	2	2	2	6	6
	A	2	2	2	6	6

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X27	E	2	2	6	6	6
	D	2	2	6	6	6
	C	2	2	6	6	6
85674-X27LF	B	2	2	6	6	6
	A	2	2	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X28	E	3	3	3	3	3
	D	1	1	1	1	1
	C	1	1	1	1	1
85674-X28LF	B	1	1	1	1	1
	A	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X29	E	3	3	3	3	1
	D	3	3	3	3	3
	C	3	3	3	3	3
85674-X29LF	B	3	3	3	3	3
	A	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X30	E	7	7	7	7	5
	D	7	7	7	7	7
	C	7	7	7	7	7
85674-X30LF	B	7	7	7	7	7
	A	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X31	E	4	2	2	2	2
	D	4	2	2	2	1
	C	4	2	2	2	2
85674-X31LF	B	4	2	2	2	2
	A	4	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X32	E	2	2	2	2	2
	D	2	2	2	2	2
	C	2	2	4	4	2
85674-X32LF	B	2	2	2	2	2
	A	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X33	E	2	2	2	2	2
	D	2	2	2	2	2
	C	2	2	4	4	2
85674-X33LF	B	2	2	2	2	2
	A	2	2	4	4	2

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X34	E	2	2	2	2	2
	D	2	2	2	2	2
	C	2	2	2	2	2
85674-X34LF	B	2	2	2	2	4
	A	2	2	2	2	4

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X35	E	2	2	4	2	2
	D	2	2	2	2	2
	C	2	2	2	2	2
85674-X35LF	B	2	2	2	2	2
	A	2	2	2	4	2

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X36	E	2	2	4	4	2
	D	2	2	2	2	2
	C	2	2	4	4	2
85674-X36LF	B	2	2	2	2	2
	A	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X37	E	2	2	2	2	4
	D	2	2	2	2	4
	C	2	2	2	2	4
85674-X37LF	B	2	2	2	2	4
	A	2	2	2	2	4

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X38	E	2	2	2	2	4
	D	2	2	2	2	4
	C	2	2	2	2	2
85674-X38LF	B	2	2	2	2	2
	A	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X39	E	6	6	6	6	8
	D	6	6	6	6	8
	C	6	6	6	6	6
85674-X39LF	B	6	6	6	6	6
	A	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X40	E	1	1	1	1	1
	D	2	2	2	2	2
	C	2	2	2	1	1
85674-X40LF	B	2	1	1	1	1
	A	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X41	E	1	1	1	1	2
	D	2	2	2	1	1
	C	2	2	2	2	2
85674-X41LF	B	2	2	2	2	2
	A	2	2	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X42	E	2	2	2	2	2
	D	2	2	2	2	2
	C	2	2	2	2	2
85674-X42LF	B	2	2	2	2	1
	A	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X43	E	5	5	5	5	5
	D	6	6	6	6	6
	C	6	6	6	5	5
85674-X43LF	B	6	5	5	5	5
	A	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X44	E	6	6	6	6	6
	D	6	6	6	6	5
	C	6	6	6	6	6
85674-X44LF	B	5	6	5	5	5
	A	5	6	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X45	E	3	3	3	3	2
	D	3	3	3	3	3
	C	3	3	3	3	3
85674-X45LF	B	3	3	3	3	3
	A	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X46	E	5	7	7	7	7
	D	7	7	7	7	7
	C	7	7	7	7	7
85674-X46LF	B	7	7	7	7	7
	A	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X47	E	7	7	7	7	7
	D	7	4	7	7	7
	C	4	7	4	7	7
85674-X47LF	B	7	7	4	7	7
	A	7	7	7	6	7

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X48	E	-	59	59	59	59
	D	-	59	59	59	59
	C	-	59	59	59	59
85674-X48LF	B	-	59	59	59	59
	A	-	59	59	59	59

A

B

mat'l code		tolerances unless otherwise specified		CUSTOMER		FCI	
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY	www.fciconnect.com
CH					0.XX ±0.13	projection	title
					.XXX ±.051		METRAL SIGNAL HEADER
				angles	0° ±2°		1 MOD, 5 ROW PRESS-FIT
				dr	T.BRUNGARD 11/19/99	product family	METRAL
				enrg	M.STRAWER 11/19/99	size	code
				chr	M.STRAWER 11/19/99	dwg no	213
				appd	M.STRAWER 02/29/00	scale	sheet
						1:1	4
sheet index	revision sheet						
						cage code	22526

Pro/E

3

4

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X49	E	3	3	3	3	3	3
	D	3	3	3	3	3	3
-----	C	-	-	3	3	3	3
85674-X49LF	B	-	-	-	-	3	3
	A	3	3	-	-	3	3

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X55 -----	E	1	3	1	1	1	1
	D	1	3	1	1	1	1
	C	1	3	1	1	1	1
	B	1	3	1	1	1	1
85674-X55LF	A	1	3	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X61	E	3	19	3	4	3
	D	3	19	3	3	3
85674-X61LF	C	3	19	3	3	3
	B	3	19	3	3	3
	A	3	19	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X65	E	3	3	3	3	3
	D	3	3	3	3	3
85674-X65LF	C	3	3	3	3	3
	B	3	3	3	3	3
	A	3	3	3	3	4

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X69	E	6	6	6	6	6	6
	D	6	5	6	6	6	6
-----	C	6	6	6	6	6	6
85674-X69LF	B	6	6	6	6	6	6
	A	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X50	E	3	3	3	3	3	3
	D	3	3	19	3	3	3
-----	C	3	3	19	3	3	3
85674-X50LF	B	3	3	3	3	3	3
	A	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X56	E	5	6	6	6	6	6
	D	5	6	6	6	6	6
-----	C	5	6	6	6	6	6
85674-X56LF	B	5	6	6	6	6	6
	A	5	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X62	E	2	2	2	1	2	
	D	2	2	2	1	2	
----- 85674-X62LF	C	2	2	2	1	2	
	B	2	2	2	1	2	
	A	1	2	2	1	2	

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X66	E	2	2	2	2	2
	D	2	2	2	2	1
----- 85674-X66LF	C	2	2	2	2	2
	B	2	2	2	2	2
	A	2	2	2	2	2

METAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X70	E	1	2	4	4	2	1
	D	1	2	4	4	2	1
-----	C	1	2	4	4	2	1
85674-X70LF	B	1	2	4	4	2	1
	A	1	2	4	4	2	1

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X5I	E	5	5	5	5	5	5
	D	6	6	6	6	6	6
-----	C	6	6	6	5	5	5
:85674-X5ILF	B	6	5	5	5	5	5
	A	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X57	E	5	6	6	6	6	6
	D	5	6	6	6	6	6
-----	C	5	6	6	6	6	6
85674-X57LF	B	6	6	6	6	6	6
	A	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X63 ----- 85674-X63LF	E	2	2	2	2	I	
	D	2	2	2	2	I	
	C	I	2	2	2	I	
	B	2	2	2	2	I	
	A	I	2	I	2	I	

METAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X67	E	2	2	2	2	2	
	D	2	1	2	2	1	
85674-X67LF	C	2	2	2	2	2	
	B	2	2	2	2	2	
	A	2	2	2	2	2	

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X7I	E	2	2	2	2	2	I
	D	2	2	2	2	2	I
	C	2	2	2	2	2	I
85674-X7ILF	B	2	2	2	2	2	I
	A	2	2	2	2	2	I

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X52	E	I	I	I	I	I	I
	D	I	I	I	I	I	I
-----	C	3	I	I	I	I	3
:85674-X52LF	B	I	I	I	I	I	I
	A	I	I	I	I	I	I

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X58	E	1	2	2	2	2	2
	D	1	2	2	2	2	2
-----	C	1	2	2	2	2	2
85674-X58LF	B	2	2	2	2	2	2
	A	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X64 ----- 85674-X64LF	E	2	1	2	2	1	
	D	2	2	2	2	1	
	C	2	2	1	1	1	
	B	2	2	2	2	1	
	A	2	2	1	1	1	

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X68	E	7	7	7	7	8
	D	7	7	7	7	8
-----	C	7	7	7	7	8
85674-X68LF	B	7	7	7	7	8
	A	7	7	7	7	8

METAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X72	E	6	6	6	6	6	6
	D	6	6	6	6	6	6
-----	C	20	6	6	6	6	6
85674-X72LF	B	6	6	6	6	6	6
	A	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X53 ----- 85674-X53LF	E	3	3	3	3	3	3
	D	2	2	2	2	3	3
	C	2	2	2	1	1	1
	B	2	2	2	1	1	1
	A	3	2	3	1	1	

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X59 ----- 85674-X59LF	E	3	3	3	1	3	3
	D	3	3	19	3	3	3
	C	19	3	19	3	3	3
	B	3	19	3	3	3	3
	A	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X54	E	2	2	2	2	2	2
	D	2	2	1	1	1	3
----- 85674-X54LF	C	2	2	1	1	1	3
	B	2	2	1	1	1	3
	A	3	2	1	1	1	

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X60	E	-	1	1	1	1	-
	D	-	1	1	1	1	-
	C	-	1	1	1	1	-
85674-X60LF	B	-	1	1	1	1	-
	A	-	1	1	1	1	-

mat'l code		- -		tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0. X $\pm$ 0.3	COPY		projection	
CH					0. XX $\pm$ 0.13	title			
					.XXX $\pm$.051	METRAL SIGNAL HEADER			
				angles	0° $\pm$ 2°	I MOD, 5 ROW PRESS-FIT			
		dr	T.BRUNGARD	11/19/99		product family		METRAL	code
		engr	M. STRAWSER	11/19/99		size		dwg no	213
		chr	M. STRAWSER	11/19/99	scale	A		85674	sheet
		appd	M. STRAWSER	02/29/00					5
sheet index	revision sheet								



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

A

B

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X73	E	20	6	8	8	6
	D	20	6	8	8	6
	C	20	6	8	8	6
85674-X73LF	B	20	6	8	8	6
	A	20	6	8	8	6

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X74	E	2	2	2	2	2
	D	2	2	2	2	2
	C	2	2	2	2	2
85674-X74LF	B	2	2	2	2	2
	A	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X75	E	2	2	2	2	3
	D	2	2	2	2	3
	C	2	2	2	2	3
85674-X75LF	B	4	4	4	4	3
	A	4	4	4	4	3

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X76	E	2	2	2	3	3
	D	2	2	2	3	3
	C	2	2	2	3	3
85674-X76LF	B	2	2	2	3	3
	A	2	2	2	3	3

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X77	E	3	3	3	2	2
	D	3	3	3	2	2
	C	3	3	3	2	2
85674-X77LF	B	3	3	3	2	2
	A	3	3	3	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X78	E	3	4	2	2	2
	D	3	4	2	2	2
	C	3	4	2	2	2
85674-X78LF	B	3	4	2	2	2
	A	3	4	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X79	E	3	2	2	2	2
	D	3	2	2	2	2
	C	3	2	2	2	2
85674-X79LF	B	3	2	2	2	2
	A	3	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X80	E	2	2	1	1	3
	D	2	2	3	3	3
	C	2	2	3	3	3
85674-X80LF	B	1	2	3	3	3
	A	1	2	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X81	E	2	2	3	3	4
	D	2	2	3	3	4
	C	2	2	3	3	4
85674-X81LF	B	2	2	3	3	4
	A	2	2	3	3	4

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X82	E	3	3	3	3	1
	D	3	3	3	3	1
	C	3	3	3	3	1
85674-X82LF	B	3	3	3	3	1
	A	3	3	3	3	1

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X83	E	1	3	3	3	3
	D	1	3	3	3	3
	C	1	3	3	3	3
85674-X83LF	B	1	3	3	3	3
	A	1	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X84	E	3	3	1	2	2
	D	3	3	1	2	2
	C	3	3	1	2	2
85674-X84LF	B	3	3	1	2	2
	A	3	3	1	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X85	E	7	7	6	8	3
	D	7	7	6	8	3
	C	7	7	6	8	3
85674-X85LF	B	7	7	6	8	3
	A	7	7	6	8	3

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X86	E	4	4	4	4	3
	D	4	4	4	4	3
	C	4	4	4	4	3
85674-X86LF	B	4	4	4	4	3
	A	4	4	4	4	3

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X87	E	3	4	3	4	3
	D	3	4	3	4	3
	C	3	4	4	4	4
85674-X87LF	B	3	4	2	2	4
	A	3	4	2	2	4

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X88	E	8	7	8	8	7
	D	8	7	8	8	7
	C	8	7	8	8	7
85674-X88LF	B	8	7	8	8	7
	A	8	7	8	8	7


mat'l code		tolerances unless otherwise specified		CUSTOMER		FCI	
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY	www.fciconnect.com
CH					0.XX ±0.13	projection	
					.XXX ±.051		
				angles	0° ±2°		
				dr	T.BRUNGARD 11/19/99		
				enrg	M.STRAWER 11/19/99		
				chr	M.STRAWER 11/19/99		
				apdd	M.STRAWER 02/29/00		
sheet index	revision sheet						

Pro/E

3

cage code 22526

4



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

A

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X99	E	2	2	1	1	2	2
	D	2	2	2	2	2	2
	C	2	2	2	2	2	2
85674-X99LF	B	1	2	2	2	2	2
	A	1	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X102	E	4	4	-	2	2	2
	D	4	4	-	2	2	4
-----	C	4	4	-	2	2	2
85674-X102LF	B	-	-	-	2	2	2
	A	4	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X105	E	7	8	7	8	7	8
	D	7	8	7	8	7	8
-----	C	8	8	8	8	8	8
85674-X105LF	B	6	8	6	8	6	8
	A	6	8	6	8	6	8

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X108	E	3	3	3	3	19	19
	D	3	3	3	3	19	19
-----	C	3	3	3	3	19	19
85674-X108LF	B	3	3	3	3	19	19
	A	3	3	3	3	19	19

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-XIII	E	6	6	6	6	6	2
	D	6	6	6	6	6	2
-----	C	6	6	6	6	6	2
	B	6	6	6	6	6	2
	A	6	6	6	8	6	2
85674-XIIIF							

[illegible]

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X115 ----- 85674-X115LF	E	64	64	64	64	64	64
	D	64	64	64	64	64	64
	C	65	64	64	64	64	64
	B	64	64	64	64	64	64
	A	64	64	64	64	64	64

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-XI19 ----- 85674-XI19LF	E	1	1	1	3	1	1
	D	1	1	1	3	1	1
	C	1	1	1	3	1	1
	B	1	1	1	3	1	1
	A	1	1	1	3	1	1

cage code	22526	4
-----------	-------	---

Pro/E

3

22526

4

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X12I	E	6	6	6	5	6	6
	D	6	6	6	6	6	6
-----	C	6	6	6	6	6	6
85674-X12ILF	B	6	6	6	6	6	6
	A	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X127	E	4	2	2	2	2	2
	D	4	2	2	2	2	2
-----	C	4	2	2	2	2	2
85674-X127LF	B	4	2	2	2	2	4
	A	4	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I							
		1	2	3	4	5	6		
85674-X133	E	5	9	7	3	1	7	5	9
	D	5	9	7	3	1	7	5	9
-----	C	5	9	7	3	1	7	5	9
85674-X133LF	B	5	9	7	3	1	7	5	9
	A	5	9	7	3	1	7	5	9

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X137	E	2	2	2	2	2
	D	2	2	2	2	2
-----	C	-	-	-	-	-
85674-X137LF	B	2	2	2	2	2
	A	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X141	E	I	I	I	I	I	I
	D	I	I	3	3	I	I
-----	C	I	I	3	3	I	I
85674-X141LF	B	I	I	I	I	I	I
	A	I	I	I	I	I	I

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X122	E	6	5	6	6	6	6
	D	6	6	6	6	6	6
-----	C	6	6	6	6	6	6
85674-X122LF	B	6	6	6	6	6	6
	A	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X128 -----	E	19	2	2	2	2	2
	D	2	2	2	2	2	2
	C	2	2	2	2	2	2
	B	2	2	2	2	2	2
85674-X128LF	A	2	1	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X134	E	2	2	2	2	1
	D	2	2	2	2	2
-----	C	2	2	2	2	2
85674-X134LF	B	2	2	2	2	2
	A	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X138	E	1	1	-	2	2
	D	1	1	-	2	2
-----	C	1	1	-	-	-
85674-X138LF	B	1	1	-	2	2
	A	1	1	-	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X142LF	E	2	2	2	2	3	2
	D	2	2	2	2	3	2
	C	2	2	2	2	3	2
	B	2	2	2	2	3	2
	A	2	2	2	2	3	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X123	E	2	1	2	2	2	2
	D	2	2	2	2	2	2
-----	C	2	2	2	2	2	2
85674-X123LF	B	2	2	2	2	2	2
	A	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X129	E	1	2	2	2	2	2
	D	2	2	2	2	2	2
-----	C	2	2	2	2	2	2
85674-X129LF	B	1	2	2	2	2	2
	A	2	1	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		I	2	3	4	5	6
85674-X135	E	I	I	2	2	3	I
	D	I	I	2	2	3	I
----- 85674-X135LF	C	I	I	2	2	3	I
	B	I	I	2	2	3	I
	A	I	I	2	2	3	I

METAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X139	E	3	3	3	3	3
	D	3	3	3	3	3
-----	C	1	3	3	3	3
85674-X139LF	B	3	3	3	3	3
	A	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X143	E	2	2	2	2	2	1
	D	2	2	2	2	2	1
-----	C	2	2	2	2	2	1
85674-X143LF	B	2	2	2	2	2	1
	A	2	2	1	2	2	1

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X124	E	6	6	6	7	8	8
	D	6	6	6	6	8	8
-----	C	6	8	8	6	6	6
85674-X124LF	B	6	6	6	6	8	8
	A	6	6	5	6	8	8

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X130 -----	E	6	6	6	6	6	2
	D	6	6	6	6	6	2
	C	6	6	6	6	6	2
	B	6	6	6	2	1	6
85674-X130LF	A	6	6	6	6	6	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X136	E	2	2	2	4	2	2
	D	2	2	2	2	2	2
-----	C	2	2	2	2	2	2
85674-X136LF	B	2	2	2	2	2	2
	A	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X140	E	3	3	2	2	2
	D	3	3	2	2	2
-----	C	3	3	2	2	2
85674-X140LF	B	3	3	2	2	2
	A	3	3	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X144	E	19	2	19	2	19	1
	D	19	2	19	2	19	1
-----	C	19	2	19	2	19	1
85674-X144LF	B	19	2	19	2	19	1
	A	19	2	19	2	19	1

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X125	E	1	2	2	2	2	2
	D	1	2	2	2	2	2
-----	C	1	2	2	2	2	2
85674-X125LF	B	1	2	2	2	2	2
	A	1	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X13I	E	2	2	2	2	2	2
	D	2	2	2	2	2	2
-----	C	2	2	2	2	2	2
85674-X13ILF	B	2	2	2	19	2	2
	A	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X126	E	3	3	3	3	3	1
	D	3	3	3	3	3	3
-----	C	3	3	3	3	3	4
85674-X126LF	B	3	3	3	3	3	3
	A	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X132	E	I	3	3	I	3	3
	D	I	I	I	I	I	I
-----	C	I	I	I	I	I	I
85674-X132LF	B	I	I	I	I	I	I
	A	I	3	3	I	3	3

[illegible]

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X145	E	3	3	3	3	2	I
	D	3	3	3	3	2	I
-----	C	3	3	3	3	2	I
85674-X145LF	B	3	3	3	3	2	I
	A	3	3	3	3	2	I

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X151	E	6	6	6	6	6	6
	D	6	6	6	6	6	5
-----	C	6	6	6	6	6	6
85674-X151LF	B	6	6	6	6	6	6
	A	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X157	E	3	3	3	3	19	3
	D	3	3	3	3	19	3
-----	C	3	3	3	3	1	3
85674-X157LF	B	3	3	3	3	19	3
	A	3	3	3	3	19	3

METRAL P/N	ROW	CONTACT CODE MOD. I				
		1	2	3	4	5
85674-X161	E	3	3	3	3	3
	D	3	3	3	3	3
-----	C	19	19	19	19	3
85674-X161LF	B	3	3	3	3	3
	A	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X146	E	2	2	2	2	2	2
	D	2	2	2	2	2	2
-----	C	2	2	2	3	2	2
85674-X146LF	B	2	2	2	3	2	2
	A	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X152	E	7	6	6	6	6	6
	D	7	6	6	6	6	6
85674-X152LF	C	6	6	6	6	6	6
	B	7	6	6	6	6	6
	A	7	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X158	E	3	3	3	3	3	3
	D	3	3	3	3	3	3
-----	C	3	3	3	3	3	I
85674-X158LF	B	3	3	3	3	3	3
	A	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X147	E	2	2	2	2	2	2
	D	2	2	1	2	2	2
-----	C	2	2	2	2	2	2
85674-X147LF	B	2	2	2	2	2	2
	A	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X153	E	2	2	2	2	2	2
	D	2	2	2	2	2	2
----- 85674-X153LF	C	2	2	2	2	2	2
	B	2	2	2	2	2	2
	A	2	2	1	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X159	E	2	2	2	2	2	2
-----	D	2	2	2	2	2	2
	C	2	2	2	2	1	2
	B	2	2	2	2	2	2
85674-X159LF	A	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X148 -----	E	1	1	2	2	2	2
	D	1	1	2	2	2	2
	C	2	2	2	2	2	2
85674-X148LF	B	1	1	2	2	2	2
	A	1	1	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X154 -----	E	2	2	2	2	2	2
	D	2	2	2	2	2	2
	C	2	2	2	1	2	2
	B	2	2	2	2	2	2
85674-X154LF	A	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT MOD.			CODE		
		1	2	3	4	5	6
85674-X160	E	3	3	3	3	3	3
	D	3	3	3	3	3	3
-----	C	3	3	3	3	3	3
85674-X160LF	B	1	1	3	3	3	3
	A	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X149	E	2	2	2	2	2	2
	D	2	2	2	2	1	2
-----	C	2	2	2	2	1	2
85674-X149LF	B	2	2	2	2	2	2
	A	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT MOD.				CODE I			
		I	2	3	4	5	6	7	8
85674-X155 -----	E	1	19	3	3	3	3	3	3
	D	3	19	3	3	3	3	3	3
	C	3	19	3	3	3	3	3	3
	B	19	19	3	3	3	3	3	3
85674-X155LF	A	19	19	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X150	E	1	1	2	2	2	2
	D	2	2	2	2	2	2
-----	C	2	2	2	2	2	2
85674-X150LF	B	2	2	2	2	2	2
	A	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
85674-X156 -----	E	I	I	I	I	I	2
	D	I	I	I	I	I	2
	C	I	I	I	I	I	2
	B	I	I	I	I	I	2
85674-X156LF	A	I	I	I	I	I	2

mat'l code				- -		tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0.X $\pm$ 0.3		COPY			title	
CH					0.XX $\pm$ 0.13		projection			METRAL SIGNAL HEADER	
					.XXX $\pm$.051					I MOD, 5 ROW PRESS-FIT	
					angles 0° $\pm$ 2°						
		dr			T.BRUNGARD	11/19/99			product family		METRAL
		engr			M. STRAWSER	11/19/99	scale		size		dwg no
		chr			M. STRAWSER	11/19/99	1:1		A		85674
		appd			M. STRAWSER	02/29/00					213
sheet index		revision sheet									sheet 9

This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.



PRODUCT NUMBER
85674-XYX OR 85674-XXXX
85674-XYXLF OR 85674-XXXXLF

NOTES:

- FOR DIM A AND B SEE SHEET 2 AND UP.
- BODY MATERIAL: LIQUID CRYSTAL
POLYMER 30 % GLASS.
FLAME RETARDANT ACC. UL 94-V0.
- PIN MATERIAL:
PHOSPHOR BRONZE.
- PLATING ON PRESS-FIT TAIL:
85674-XYX IS SnPb
85674-XYXLF IS SN (LEAD FREE)
PLATING ON CONTACT AREA CONFORMS TO PERFORMANCE
LEVEL SHOWN IN TABLE BELOW.
- PRODUCT MARKING:
PART NUMBER DESIGNATION & BATCH I.D.
- ALL PRODUCTS WITH PART NUMBERS SHOWN IN
SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES.
IF TRAY PACKAGING IS REQUIRED, A SUFFIX "P"
WILL BE ADDED TO THE END OF THE PART NUMBER.
EXAMPLE: XXXXX-XXXXP
- PRODUCT SPECIFICATION GS-12-180
APPLICATION SPECIFICATION BUS-20-073
- AFTER INSERTION INTO CIRCUIT BOARD WITH
QUALIFIED TOOL.
- THE PRODUCTS WHERE THE PART NUMBER ENDS IN LF MEET THE
EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS
AS DESCRIBED IN GS-22-008.

ALL PRODUCTS EXCEPT THOSE WITH PART NUMBERS CONTAINING
(DRAWING NO.)-N1--- OR (DRAWING NO.)-N5---WILL WITHSTAND EXPOSURE
TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRARED OR
VAPOR PHASE REFLOW OVEN. PART NUMBERS (DRAWING NO.)-N1---
AND (DRAWINGS NO.)-N5---WILL NOT WITHSTAND REFLOW AND Au CONTACT
SURFACE OF THE CONTACTS SHALL BE EXPOSED TO A MAXIMUM 140°C FOR
NO LONGER THAN 15 SECONDS IN A WAVE SOLDER APPLICATION.

PLATING IN CONTACT AREA		
DASH NUMBER	PERFORMANCE LEVEL	NOTES
-PYY OR -PYXX	0.25 um GOLD MIN.	-
-N1YY OR -N1XXX	TELCORDIA CO (NXT)	-
-N5YY OR -N5XXX	TELCORDIA UE (NXT)	-
-1YY OR -1XXX	TELCORDIA CO	-
-2YY OR -2XXX	TELECOM CLASS	-
-3YY OR -3XXX	IEC CLASS I	-
-5YY OR -5XXX	TELCORDIA UE	-
-9YY OR -9XXX	TELCORDIA CO	-
-N1YYLF OR -N1XXXLF	TELCORDIA CO (NXT) IEC CLASS I	SEE NOTE 9
-N5YYLF OR -N5XXXLF	TELCORDIA UE (NXT)	SEE NOTE 9
-1YYLF OR -1XXXLF	TELCORDIA CO IEC CLASS I	SEE NOTE 9
-2YYLF OR -2XXXLF	TELECOM CLASS	SEE NOTE 9
-5YYLF OR -5XXXLF	TELCORDIA UE	SEE NOTE 9

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
ltr	ecn no.	dr	date			COPY			www.fciconnect.com
CH				linear	0.X ±0.3	projection		title METRAL SIGNAL HEADER 1 MOD, 5 ROW PRESS-FIT	
					0.XX ±0.13				
					.XXX ±.051				
				angles	0° ±2°			product family METRAL	
				dr	T.BRUNGARD 11/19/99			code 213	
				engr	M.STRAWER 11/19/99			size	
				chr	M.STRAWER 11/19/99			dwg no	
				appd	M.STRAWER 02/29/00			85674	
sheet		revision				scale		sheet	
index		sheet				1:1	A	10	