


REVISIONS			
REV	DESCRIPTION	DATE	NAME
A	Initial Release.	05-07-00	AMH
B	Updated temp spec and labeling	08-17-09	AMH



- NOTES:
- 1.Operation Temperature:-20°C~+60°C
Storage Temperature:-20°C~+70°C
 - 2.Life Time :>1,000,000 times.
 - 3.Linearity: ≤1.5%.
 - 4.ITO Film:Anti-glare Harding Coating And Anti-Newton Ring
Sheet Resistance: 400±100 Ω/square;
 - 5.Tail Type :Gold plated FPC
 - 6.All Tolerance Without Marked:±0.3
 - 7.All Materials and Components must be RoHS compliant
 - 8.No Material is allowed to be larger than the glass size

PIN #	Assignment
1	Top
2	Bottom
3	Left
4	Right



1016 North Lincoln Avenue - Pittsburgh, PA 15233-2302
1.800.366.1904 - 412.322.9900 - Fax: 412.322.9958
e-mail: sales@sawar.com - www.dawar.com

THIS DOCUMENT IS THE PROPERTY OF DAWAR TECHNOLOGIES, INC. AND SHALL NOT BE COPIED, REPRODUCED, DISCLOSED, AND/OR USED AS THE BASIS FOR MANUFACTURING OR SALE WITHOUT PERMISSION OF A DULY AUTHORIZED REPRESENTATIVE OF DAWAR TECHNOLOGIES, INC.

CUSTOMER NAME	UNIT	DAWAR P/N	REV
Standard product offering	mm	PL4_10.4-00001	B
CUSTOMER P/N	REV	DRAWN BY	DATE
		Jason Liao	08-17-09
DESCRIPTION	SHEET	MANUFACTURING NO.	REV
10.4" 4-Wire Resistive Touch Screen	1 OF 1		