




7.62
[.300] MAX

5.08
[.200]

1.27
[.050]

1.22
[.048] REF

1.22
[.048] REF

A SP @ 3.81 [.150] = B

C

TYPICAL FOR -2

3.20
[.126]

6.10
[.240]

13.97
[.550]

6.35
[.250] MAX

TYPICAL FOR -1 & -3

CAVITY IDENTIFICATION

C

AMP

CONTACT

HOUSING

CONNECTOR MATING FACE

SECTION D-D

SCALE 10:1

1 MATERIAL:
HOUSING; GLASS FILLED POLYESTER.

2 FINISH: PLATED WITH 0.00076[.000030] GOLD IN CONTACT
AREA OVER 0.00127[.000050] NICKEL OVER ALL.

3 MATING POST LENGTH SHALL BE 5.08[.200] MINIMUM.

4 BULK PACKAGED.

RED	BERYLLIUM COPPER	2	6.25 [.246]	3.81 [.150]	1	2 X 2	390102-3	4
BLACK	BERYLLIUM COPPER	2	10.01 [.396]	7.62 [.300]	2	2 X 3	390102-2	
BLACK	BERYLLIUM COPPER	2	6.25 [.246]	3.81 [.150]	1	2 X 2	390102-1	
HOUSING COLOR	CONTACT MATERIAL	FINISH	C	B	A SPACES	SIZE	PART NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

FINISH

±-

±-

±0.13 [.005]

±-

±-

±-

SEE TABLE

DWN
W.SORAH
1-20-97

CHK
R.TALLEY
1-20-97

APVD
K.KREIDLER
1-20-97

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME

SIZE

CAGE CODE

DRAWING NO

SCALE

SHEET

OF

REV

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

SHUNT CONTACT ASSEMBLY
MULTI-POSITION
FOR 0.64 [.025] SQUARE POSTS

A2 00779

C=390102

5:1

1

1

C

390102

390102

390102

390102

AMP 1471-9 REV 23FEB95

01-JUN-98 15:08:49 amp12184 /home/amp12184/edmod