


## PRODUCT BRIEF

Intel® True Scale Fabric 12800 Gb JhW



# Intel® True Scale Fabric 12800 Switch

18-864 Port, 40Gbps Modular Switch

## Overview

For over 10 years, InfiniBand® networks have been deployed to address the needs of the most demanding High Performance Computing (HPC) applications. The Intel® 12800 switch is a data center interconnect that links HPC resources using a scalable, 40Gbps, low-latency fabric. Customers can tailor the 12800 modular design to meet meet present and future needs. The Intel® 12800 switch series delivers exceptional high-speed networking features and functions.



# Highlights

## Benefits

- QDR line rate performance
- Predictable low latency under heavy loads
- Flexible quality of service (QoS) maximizes bandwidth utilization
- Modular configuration flexibility
- Highly reliable and available
- Easy to manage
- Lowest per-port power and cooling requirements

## Features

- 18–864 ports of InfiniBand® QDR (40Gbps) performance with support for DDR and SDR
- Intel® True Scale Fabric Architecture with scalable, predictable low latency
- Scales to 51.8Tbps aggregate bandwidth

- Multiple Virtual Lanes (VLs) per physical port
- Supports virtual fabric partitioning
- Fully redundant system design
- Option to use ultra high density (UHD) leafs for maximum connectivity or ultra high performance (UHP) leafs for maximum performance
- Integrated chassis management capabilities for installation, configuration, and ongoing monitoring
- Optional Intel® Fabric Suite (IFS) management solution that provides expanded fabric views and fabric tools
- Minimal power and cooling requirements
- Complies with InfiniBand Trade Association® (IBTA®) version 1.2 specification
- RoHS 6 compliant



## Low Latency

Intel's 12800 switch provides scalable, predictable low latency. Predictable latency means HPC applications can be scaled easily without diminished cluster performance or costly system tuning efforts.

## Flexible Partitioning

Intel's advanced 12800 switch design is based on an architecture that provides comprehensive virtual fabric partitioning that enables the InfiniBand fabric to support today's evolving requirements. The Intel® True Scale Architecture, together with IFS, allows the fabric to be shared by mission-critical applications while delivering maximum bandwidth utilization.

## Modular Design

InfiniBand® port, power, cooling, and management modules are common among the series, giving customers the flexibility to deploy and grow HPC environments in a cost-effective fashion.

## Investment Protection

The Intel® 12800 Series switches adhere to the IBTA v1.2 specification, ensuring the ability to interoperate with all other IBTA compliant devices.

## Highly Reliable

This system is designed for high availability with features that include port-to-port and module-to-module failover, non-disruptive firmware upgrades, component-level diagnostics and alarming, and both in-band and out-of-band management.

## Easy to Manage

The Intel® 12800 switch uses Intel's advanced IFS software for faster installation and configuration. IFS includes advanced tools to verify fabric configuration, topology, and performance. Faults are automatically isolated to the component level and reported.

## Simple Installation and Configuration

The installation and configuration wizards contained in the IFS package cuts the fabric installation and configuration time down to days instead of weeks.

## Power Optimized

Delivers maximum performance with minimal power and cooling requirements as part of Intel's commitment to developing green solutions for the data center.

# Chassis Options Chassis

## 12800-360

- 18–864 ports
- 51.8Tbps capacity
- Supports up to 36 leaf modules

## 12800-180

- 18–432 ports
- 25.9Tbps switching capacity
- Supports up to 18 leaf modules

## 12800-120

- 18–288 ports
- 17.2Tbps switching capacity
- Supports up to 12 leaf modules

## 12800-40

- 18–96 ports
- 5.76Tbps switching capacity
- Supports up to 4 leaf modules

---

## Leaf Module

### UHP Module

- Eighteen 4x QDR ports

### UHD Module

- Twenty-four 4x QDR InfiniBand ports

---

## Switch Specifications

- 40/20/10Gbps auto-negotiation links
- Virtual lanes: Eight plus one management
- Maximum MTU size: 4096 bytes
- Maximum multicast table size: 1024 entries
- Switching latency: 140–420ns
- Supports QSFP optical and copper cable specifications

---

## Interoperability

- Compliant with IBTA\* versions 1.0a, 1.1, and 1.2

---

## Fabric Management

### Management Methods

- Command line interface
- Optional external server-based IBTA\* compliant subnet manager
- Optional embedded fabric management
- IBTA\*-compliant - SMA, PMA, and BMA
- Chassis management GUI
- SNMP support

### Access Methods

- 10 and 100 Ethernet Base-T (RJ45)
- Serial port (RS-232 with DB9)

### LEDs

- Two per leaf module plus one per InfiniBand port
- Two per single-spine module
- Four per dual-spine module
- Three per power supply module
- Eight per management module
- Three per serial port per Ethernet module



## Physical Specifications

### 12800-360

- H x W x D: 1288.4 x 439.6 x 650 mm (50.7 x 17.3 x 26 in)
- 81.9kg (180lbs)

### 12800-180

- H x W x D: 622.6 x 439.6 x 650 mm (24.5 x 17.3 x 26 in)
- 50.1kg (110lbs)

### 12800-120

- H x W x D: 444.7 x 439.6 x 650 mm (17.5 x 17.3 x 26 in)
- 41kg (90lbs)

### 12800-040

- H x W x D: 221.1 x 439.6 x 650 mm (8.7 x 17.3 x 26 in)
- 18.2kg (40lbs)

## Environmental Specifications

### Operating

- Temperature: 0°–40°C
- Humidity: 5–85% non-condensing
- Altitude: 0–10,000 feet
- Vibration: 5–500Hz, 0.27g, 5 sweeps
- Shock: 3.5g, 3ms, half sine, 20 repetitions

### Electrical

- Voltage: 100–240VAC; 50–60Hz
- Receptacle: IEC320-C19
- Power consumption: 85–6749W

### Non-operating

- Temperature: -40°–65°C
- Humidity: 5–90% non-condensing
- Altitude: 0–40,000 feet
- Vibration: 2–200Hz, 0.5g, 5 sweeps
- Shock: 50g, 4216mm/s, 13 msec, 3 axis

### Airflow

- Front-to-back

## Agency Approvals

### Safety

UL/CSA/IEC/EN 60950-1

### EMI

FCC/VCCI/EN/IEC Class A

### Marking

FCC/ICES-003/TUV-CUE/CE/VCCI/C-Tick/GOST/KCC

### RoHS 6



INFORMATION IN THIS DOCUMENT IS PROVIDED IN CONNECTION WITH INTEL® PRODUCTS. NO LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE, TO ANY INTELLECTUAL PROPERTY RIGHTS IS GRANTED BY THIS DOCUMENT. EXCEPT AS PROVIDED IN INTEL'S TERMS AND CONDITIONS OF SALE FOR SUCH PRODUCTS, INTEL ASSUMES NO LIABILITY WHATSOEVER AND INTEL DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY, RELATING TO SALE AND/OR USE OF INTEL PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

A "Mission Critical Application" is any application in which failure of the Intel Product could result, directly or indirectly, in personal injury or death. SHOULD YOU PURCHASE OR USE INTEL'S PRODUCTS FOR ANY SUCH MISSION CRITICAL APPLICATION, YOU SHALL INDEMNIFY AND HOLD INTEL AND ITS SUBSIDIARIES, SUBCONTRACTORS AND AFFILIATES, AND THE DIRECTORS, OFFICERS, AND EMPLOYEES OF EACH, HARMLESS AGAINST ALL CLAIMS COSTS, DAMAGES, AND EXPENSES AND REASONABLE ATTORNEYS' FEES ARISING OUT OF, DIRECTLY OR INDIRECTLY, ANY CLAIM OF PRODUCT LIABILITY, PERSONAL INJURY, OR DEATH ARISING IN ANY WAY OUT OF SUCH MISSION CRITICAL APPLICATION, WHETHER OR NOT INTEL OR ITS SUBCONTRACTOR WAS NEGLIGENT IN THE DESIGN, MANUFACTURE, OR WARNING OF THE INTEL PRODUCT OR ANY OF ITS PARTS.

Intel may make changes to specifications and product descriptions at any time, without notice. Designers must not rely on the absence or characteristics of any features or instructions marked "reserved" or "undefined". Intel reserves these for future definition and shall have no responsibility whatsoever for conflicts or incompatibilities arising from future changes to them. The information here is subject to change without notice. Do not finalize a design with this information.

The products described in this document may contain design defects or errors known as errata which may cause the product to deviate from published specifications. Current characterized errata are available on request. Contact your local Intel sales office or your distributor to obtain the latest specifications and before placing your product order.

Copies of documents which have an order number and are referenced in this document, or other Intel literature, may be obtained by calling 1-800-548-4725, or go to: <http://www.intel.com/design/literature.htm>

© 2012, Intel Corporation. All rights reserved. Intel, and the Intel logo, are trademarks of Intel Corporation in the U.S. and/or other countries.

\*Other names and brands may be claimed as the property of others.

0312/LM/CMD/PDF

327085-001US

