


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC		DIST		REVISIONS					
AD		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					D	EC 0G3C-0261-04	29JUN04	BSV	MSS

D




C


onlinecomponents.com



B



ADF



A

INSERT MOUNT

Specifications:

MATERIAL

BASE, PPS,(12 POS PA46) UL94V-0, BLACK
COVER, PPS,(12 POS PA46) UL94V-0, BLACK
ACTUATOR, PA6T,(12 POS PBT) UL94V-0, WHITE
FIXED CONTACT/TERMINAL, CU ALLOY, PLATE TIN(90%)LEAD(10%)OVER COPPER
MOVING CONTACT, CU ALLOY, PLATE-GOLD FLASH/NICKEL

ELECTRICAL

MAX CONTACT RATING SWITCHING, 100MILLIAMPS @ 24 VDC
MIN CONTACT RATING SWITCHING, .1MICROAMP @ 1 MILLIVOLT
MAX CONTACT NON-SWITCHING, 1AMP @ 5 VDC
INITIAL CONTACT RESISTANCE, 50 MILLIOHMS MAX.
CONTACT RESISTANCE (AFTER ENVIRONMENTAL TEST), 100 MILLIOHMS
CONTACT RESISTANCE (AFTER GAS TEST), 300 MILLIOHMS
INSULATION RESISTANCE, 1,000 MEGOHMS MIN. @ 100 VDC
DIELECTRIC STRENGTH, 500 VAC RMS @ SEA LEVEL
LIFE EXPECTANCY, 1,000 CYCLES


MECHANICAL

OPERATING FORCE, LESS THAN 800 GRAMS
CONTACT PRESSURE, 280,000 PSI

ENVIRONMENTAL

OPERATING TEMPERATURE, -30 TO +85 DEGREES C
STORAGE TEMPERATURE, -45 TO + 100 DEGREES C
CLEANING, AQUEOUS OR SOLVENT
SOLDER HEAT RESISTANCE, 245 +/-5 DEGREES C FOR 30 SECONDS, MOUNTED ON .060 PCB, SWITCH "OFF".

- SWITCHES TO BE RECEIVED IN THE "OFF" POSITION AND PACKAGED IN CLEAR TUBES TO ACCOMMODATE AUTO-INSERTION.
- TOP SURFACE TO BE CLEARLY MARKED AS SHOWN
- SWITCHES TO BE BLACK WITH WHITE ACTUATORS AND MARKINGS.
-  MARK PER 202-37.
- RECOMMENDED SOLDER PROCESS, WAVE SOLDER: BATH TEMPERATURE OF 245 +/-5 DEGREES C FOR 5 SECONDS. SWITCH POSITION SHOULD BE IN THE OFF SETTING.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 19AUG03	 Tyco Electronics Corporation Harrisburg, Pa 17105-3808			
DIMENSIONS: INCHES		CHK M.SARVER 26AUG03				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M.SARVER 26AUG03	NAME DIP SWITCH, ADE THRU HOLE		
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .012 4 PLC ± - ANGLES ± -		PRODUCT SPEC	-		
	FINISH		APPLICATION SPEC	-		
MATERIAL		WEIGHT	-	SIZE A2	CAGE CODE 00779	DRAWING NO C=4-1437586-2
		CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 2	REV D

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
AD	00	P	LTR	DESCRIPTION	DATE	APVD
		—	—	SEE SHEET 1	—	—

onlinecomponents.com

ADF12T	YES	1.28	12	1571336-1
ADF10T	YES	1.078	10	1437587-7
ADF10	NO	1.078	10	1437587-1
ADF09	NO	0.978	9	9-1437586-6
ADF08T	YES	0.878	8	9-1437586-5
ADF08	NO	0.878	8	8-1437586-6
ADF07T	YES	0.778	7	8-1437586-5
ADF07	NO	0.778	7	8-1437586-1
ADF06T	YES	0.678	6	8-1437586-0
ADF06	NO	0.678	6	7-1437586-1
ADF05T	YES	0.578	5	7-1437586-0
ADF05	NO	0.578	5	6-1437586-5
ADF04T	YES	0.478	4	6-1437586-4
ADF04	NO	0.478	4	5-1437586-7
ADF03T	YES	0.378	3	5-1437586-6
ADF03	NO	0.378	3	5-1437586-1
ADF02T	YES	0.278	2	5-1437586-0
ADF02	NO	0.278	2	4-1437586-2
Old T&B P/N	Tape seal	Dim L	Poles	TycoP/N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES



MATERIAL

—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± .012
4 PLC ± —
ANGLES ± —
FINISH —

DWN
M.BINNER
19AUG03

CHK
M.SARVER
26AUG03

APVD
M.SARVER
26AUG03

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

CUSTOMER DRAWING

Tyco Electronics Corporation
Harrisburg, Pa 17105-3808

NAME
DIP SWITCH, ADE THRU HOLE
—
—

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=4-1437586-2

RESTRICTED TO
—

SCALE
1:1

SHEET
2

OF
2

REV
D