



**AC/DC EXTERNAL REGULATED WALLMOUNT ADAPTER
2-BLADE USA AND EURO-STECKER AC PLUG SINGLE OUTPUT
1.6-3.6 WATTS LINEAR POWER SUPPLIES HER-35 SERIES**



FEATURES:

- SMALL & COMPACT IN SIZE
- 2-BLADES USA & EUROPEAN AC PLUG
- MEET USA & CANADA STANDARD
- CE MARKING COMPLIANCE

SPECIFICATION

INPUT SPECIFICATION

Input Voltage: Nominal 100/110/120Vac
Custom Vac available.
Input Connector: U.S. 2-blade AC plug WM1.
Euro-stecker AC plug WM3.
Input Frequency: 60Hz.for nominal 100/110/120Vac.
50Hz for nominal 220/230/240Vac.
Input Current: 0.1A @120Vac input.
Dielectric Withstand: Meet IEC950.
EMI: Inherent low conducted and radiated noise level,
meet EN 55022 & FCC class B.
Hold-up Time: Less than 1mS at nominal input and
typical load.
Thermal Protection: Thermal fuse installed in the
input transformer.

OUTPUT SPECIFICATION

Output Voltage: See Ratings Chart.
Output Current: See Ratings Chart.
Output Wattage: 1.6-3.6 Watts typical.
Output Connector: Optional.
Load Regulation: $\pm 5.0\%$ typical at end of 6ft.cord
AWG#20 wires.
(The exactly voltage regulation obtainable
depends upon the output cord & connector
selected and load current.)
Noise & Ripple: Less than 20 mV.
Overload Protection: Protected by thermal fuse buried
inside the transformer.

GENERAL SPECIFICATION


Efficiency: 16% for 3.3V unit typical, 20% for 5V unit,
30% for 12V, 15V and 24V unit.
Circuit Topology: Line frequency lamination
steel transformer circuit.
Transient Response: Less than 50 μ S following
a 25% load change.
Safety Standard: Meet UL1950 Class II.

Operating Temperature: 0 to +25/35/40°C
without derating. (various with output voltage)
Storage Temperature: -20 to +85°C.
Cooling: Free air convection.
Construction: Impact resistant plastic enclosure case.
Wallmount format in EI-35 case.

NOTE: (1) All measurements are at nominal input, full load, and +25°C unless otherwise specified.

(2) Due to requests in market and advances in technology, specifications subject to change without notice.

MODEL NO. DESCRIPTION: HER-35 — X X X Y Y Y - N



In application.

OUTPUT VOLTAGE / CURRENT RATINGS CHART

U.S.A VERSION Input Voltage 100-120Vac/ Current 0.1A@60Hz

DEFINED OUTPUT VOLTAGE (Vdc)	OUTPUT VOLTAGE (Vdc) / CURRENT (A)
3.3Vdc $\leq$ Any Voltage $\leq$ 12.0Vdc	3.3-4.5V/0.60-0.54A, 5.0-7.0V/0.52-0.40A, 7.50-9.50V/0.40-0.34A, 10.0-12.0V/0.32-0.30A.
12.0Vdc $\leq$ Any Voltage $\leq$ 24.0Vdc	12.0-14.5V/0.30-0.25A, 15.0-17.5V/0.24-0.20A, 18.0-19.5V/0.20-0.18A, 20.0-21.5V/0.18-0.16A 22.0-24.0V/0.16-0.15A.

Note: Refer to the upper Chart or consult factor for the exact Model No. and V/A

SINGLE OUTPUT (Model No. for examples)

MODEL NO.	AC PLUG	I/P VOLTAGE	O/P VOLTAGE	O/P CURRENT
HER-35-033060-1	WM1	120Vac	3.3Vdc	0.60A
HER-35-050052-1	WM1	120Vac	5.0Vdc	0.52A
HER-35-060050-1	WM1	120Vac	6.0Vdc	0.50A
HER-35-090034-1	WM1	120Vac	9.0Vdc	0.34A
HER-35-120030-1	WM1	120Vac	12.0Vdc	0.30A
HER-35-150024-1	WM1	120Vac	15.0Vdc	0.24A
HER-35-240015-1	WM1	120Vac	24.0Vdc	0.15A

EUROPEAN VERSION Input Voltage 220-240Vac/ Current 0.1A@50Hz

DEFINED OUTPUT VOLTAGE (Vdc)	OUTPUT VOLTAGE (Vdc) / CURRENT (A)
3.3Vdc $\leq$ Any Voltage $\leq$ 12.0Vdc	3.3-4.5V/0.60-0.54A, 5.0-7.0V/0.52-0.40A, 7.50-9.50V/0.40-0.34A, 10.0-12.0V/0.32-0.30A,
12.0Vdc $\leq$ Any Voltage $\leq$ 24.0Vdc	12.0-14.5V/0.30-0.25A, 15.0-17.5V/0.24-0.20A, 18.0-19.5V/0.20-0.18A, 20.0-21.5V/0.18-0.16A 22.0-24.0V/0.16-0.15A.

Note: Refer to the upper Chart or consult factor for the exact Model No. and V/A

SINGLE OUTPUT (Model No. for examples)

MODEL NO.	AC PLUG	I/P VOLTAGE	O/P VOLTAGE	O/P CURRENT
HER-35-033050-3	WM3	220Vac	3.3Vdc	0.50A
HER-35-050048-3	WM3	220Vac	5.0Vdc	0.48A
HER-35-060042-3	WM3	220Vac	6.0Vdc	0.42A
HER-35-090034-3	WM3	230Vac	9.0Vdc	0.34A
HER-35-120030-3	WM3	230Vac	12.0Vdc	0.30A
HER-35-150024-3	WM3	230Vac	15.0Vdc	0.24A
HER-35-240015-3	WM3	230Vac	24.0Vdc	0.15A

MECHANICAL DIMENSIONS: MM [INCHES]

WEIGHT: HER-35 200g(7.05 Oz.)

