






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B9	ECR-16-007656		26MAY2016	SS	RR
B10	ECR-16-010175		14 JUL2016	KD	RR
B11	ECR-16-016334		17NOV2016	FV	RR
B12	ECR-17-009651		19 JUL2017	RS	DC











- 1 WIRE RANGE : STRANDED 0.22-0.35 mm² (INS. DIA. 1.30±0.1)
- 2 MATING PART: P.C.B. EDGE, DOUBLE SIDE, THK 1.5 (COPPER CLADDING INCLUDED)
- 3 SIDE LOCKING DEVICE
- 4 KEYING RIBS TO BE REMOVED BY TERMINATION MACHINE
- 5 POLARIZATION RIBS BETWEEN CAVITIES
- 6 CUT OFF DIMENSION DUE TO PRODUCTION PROCESS
- 7 CIRCUIT No. IDENTIFICATION
- 8 TE TRADEMARK (OPTIONAL POSITION)
- 9 TAMPOGRAPHIC COLOUR CODE AREA (P/Ns IDENTIFICATION BEFORE CRIMPING AREA)
- 10 FOR PCB LAYOUT, SEE SHEET 2
FOR CONNECTION VIEW LAYOUT, SEE SHEET 2
- 11 PRELIMINARY NOT YET RELEASED FOR PRODUCTION
- 12 PBT GF
- 13 PBT GF, UL94-V0 & GWEP7 750 NO-FLAME, NATURAL

OBSOLETED	GREEN	13/14	SELECTIVELY 1.3.4.6.8.9.10.11.12.13.14	14	32.5	37.4	5-284866-4	1-2311508-4
	BLUE		SELECTIVELY 1.3.4.6.11.12.13.14				1-284866-4	2311508-4
	BLUE	2/3	SELECTIVELY 1.3.4.6.7.9.11.12	12	27.5	32.4	1-284866-2	2311508-2
	BLUE	2/3	SELECTIVELY 1.2.3.4.5.6.7.8.10	10	22.5	27.4	1-284866-0	-
USED)	GRAY	3/4	SELECTIVELY 1.3.4.6.8.9	9	20.0	24.9	7-284866-9	8-2311507-9
	RED	4/5	SELECTIVELY 1-2-4-6-8-9				8-284866-9	7-2311507-9
	GREEN	2/3	SELECTIVELY 1.2.4.6.7.9				1-284866-9	6-2311507-9
	BLACK		SELECTIVELY 1.3.5.7.8.9				6-284866-9	5-2311507-9
	ORANGE		SELECTIVELY 1.2.3.5.7.9				5-284866-9	4-2311507-9
	BROWN		SELECTIVELY 1.3.4.6.8.9				4-284866-9	3-2311507-9
	RED		SELECTIVELY 1.3.5.6.7.9				3-284866-9	2-2311507-9
	GREEN		SELECTIVELY 1.3.4.5.6.7.8.9				2-284866-9	1-2311507-9
	BLUE		SELECTIVELY 1.3.4.6.7.9				0-284866-9	2311507-9
	BROWN	2/3	SELECTIVELY 1.2.3.4.6.8	8	17.5	22.4	4-284866-8	3-2311507-8
	RED		SELECTIVELY 1.3.5.6.7.8				3-284866-8	2-2311507-8
	GREEN		SELECTIVELY 1.3.4.5.6.7.8				2-284866-8	1-2311507-8
	BLUE		SELECTIVELY 1.3.4.6.7.8				0-284866-8	2311507-8
	BLUE	2/3	SELECTIVELY 1.3.5.7	7	15.0	19.9	1-284866-7	1-2311507-7
	BLUE		SELECTIVELY 1.3.5.6.7				0-284866-7	2311507-7
	BLACK	2/3	SELECTIVELY 1.3.4.6	6	12.5	17.4	4-284866-6	2-2311507-6
	GREEN	4/5	SELECTIVELY 1.2.4.6				2-284866-6	1-2311507-6
	BLUE	2/3	SELECTIVELY 1.3.5.6				0-284866-6	2311507-6
	ORANGE	1/2	SELECTIVELY 3.4.5				5	10.0
	GREEN		SELECTIVELY 1.2.3.5	3-284866-5	2-2311507-5			
	BLUE	3/4	SELECTIVELY 1.3.4.5	2-284866-5	1-2311507-5			
	RED	2/3	SELECTIVELY 2.4	0-284866-5	2311507-5			
	GREEN	N/A	SELECTIVELY 1.2.4	4	7.5	12.4	2-284866-4	2311507-4
	GREEN	1/2	SELECTIVELY 1.3	3	5.0	9.9	2-284866-3	1-2311507-3
BLUE	2/3	SELECTIVELY 1.3	0-284866-3				2311507-3	
	COLOUR CODE	POLARIZ. RIB POS.	CONTACT LOADING	HSG POS.	DIM.A	DIM.B	TE P/N	TE P/N

P/N 2-284866-8 AS SHOWN

-	-	-	-	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. FABRIS CHK -	03JUL2002 -	 TE Connectivity				
SEE TABLE	PH. BRONZE, TIN PLATED	IDC RECEPTACLE CONTACT	2		DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME APVD G. TURCO PRODUCT SPEC 108-20238 APPLICATION SPEC 114-18049-1	SIZE A1	CAGE CODE 00779	DRAWING NO C=284866	RESTRICTED TO -
	PBT GLASS FIBER FILLED	FEMALE HOUSING	1		0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES	±0.2 ±0.2 ±0.2 ±0.2 ±0.2 ±°						
Q.TY	MATERIAL	DESCRIPTION	ITEM			FINISH		WEIGHT				
1	REVISIONE DELL'ASSEMBLATO (REVISION OF EACH ASSY NO)			MATERIAL SEE TABLE		SEE TABLE						
G.TA' PER ASSEMBLATO (QTY REQ'D PER ASSY)		ELENCO DEI COMPONENTI (PARTS LIST)						CUSTOMER DRAWING				
								SCALE 10:1	SHEET 1	OF 4	REV. B12	

4805 (3/13)



REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
-	-	SEE SHEET 1	-	-