


# Educator's Oscilloscope Training Kit for Agilent InfiniiVision X-Series Oscilloscopes

## Data Sheet

Oscilloscope training tools created specifically for electrical engineering and physics undergraduate students and professors



## Introduction

Agilent's InfiniiVision 2000, 3000, and 4000 X-Series digital storage and mixed signal oscilloscopes (DSOs and MSOs) are ideal for students to use in their undergraduate electrical engineering and physics circuits labs. These X-Series scope families include 46 different models ranging from the lowest priced DSOX2002A (2-channel, 70 MHz DSO), to the highest performance MSOX4154A (4 channel, 1.5 GHz MSO). What makes these scopes even more compelling for the EE and physics education environment is the optional Educator's Oscilloscope Training Kit (DSOXEDK).

The Educator's Oscilloscope Training Kit provides an array of built-in training signals, so that electrical engineering and physics students can learn what an oscilloscope does and how they can perform basic oscilloscope measurements. Also included in the kit is a comprehensive oscilloscope lab guide and tutorial written specifically for the undergraduate student. Professors and students can download this at no charge.

Agilent also provides a PowerPoint slide-set that professors and lab assistants can use as a pre-lab lecture on oscilloscope fundamentals. This lecture takes about 30 minutes and should be presented before electrical engineering and physics students begin their first circuits lab. Note that this PowerPoint slide-set also includes a complete set of speaker notes.

## Features

- Up to 28 built-in student training signals
- Oscilloscope lab guide and tutorial
- Oscilloscope fundamentals PowerPoint slide-set



# Built-in Oscilloscope Training Signals with Step-by-Step Instructions and Tutorial


An oscilloscope is the one measurement tool that students will use more than any other instrument to perform assigned circuit experiments. Students will also use oscilloscopes extensively after they graduate and enter today's electronics industry. So it is extremely important that they become proficient in the use of this vital tool.

The DSOXEDK Educator's Oscilloscope Training Kit provides the following 28 signals (and required options) to help teach undergraduate EE students what an oscilloscope is and how to use one effectively:

- Sine
- Sine with noise
- Phase shifted sine
- Sine with glitch
- Amplitude modulated sine wave
- RF burst
- FM burst (3000 and 4000 X-Series only)
- Repetitive pulse with ringing
- Single-shot pulse with ringing
- Clock with infrequent glitch
- Runt pulses (3000 and 4000 X-Series only)
- Edge transition violation signal (3000 and 4000 X-Series only)
- Setup and hold violation signal (3000 and 4000 X-Series only)
- Analog and digital signals (MSOX)
- Digital burst
- Digital burst with infrequent glitch
- Edge then edge (3000 and 4000 X-Series only)
- I<sup>2</sup>C (EMBD)
- RS232/UART (COMP)
- SPI (EMBD)
- I<sup>2</sup>S (AUDIO, 3000 and 4000 X-Series only)
- CAN (AUTO)
- LIN (AUTO)
- CAN & LIN (AUTO)
- FlexRay (FLX, 3000 and 4000 X-Series only)
- ARINC429 (AERO, 3000 and 4000 X-Series only)
- Mil-1553 (AERO, 3000 and 4000 X-Series only)
- Mil-1553 Dual (AERO, 3000 and 4000 X-Series only)
- USB (USBFL, 4000 X-Series only)

These training signals are routed to two test lugs on the scope's front panel and should be probed using the scope's standard 10:1 passive probes. Some of the training signals such as sine waves are very simple, as shown in Figure 1. Other training signals can be quite complex in order to train students how to use the scope's more advanced triggering and measurement capabilities. No other test equipment is required other than the scope and two passive probes.

Along with the built-in training signals, professors and/or lab assistants and students can download the Oscilloscope Lab Guide and Tutorial. This guide provides a series of short oscilloscope labs with simple step-by-step instructions on accessing the training signals and setting up the scope to measure these signals. This training guide also provides a tutorial on oscilloscope theory of operation, bandwidth and triggering basics. Although triggering is probably the most important oscilloscope capability, it is often the least understood.



**Figure 1: The sine wave signal teaches students how to scale waveforms for optimum viewing, how to trigger on edge crossings, and how to make basic voltage and timing measurements.**




**Figure 2: The downloadable Oscilloscope Lab Guide and Tutorial for Undergraduate Electrical Engineering and Physics Students.**

To download the Oscilloscope Lab Guide and Tutorial, go to:  
[www.agilent.com/find/edk](http://www.agilent.com/find/edk)

## Built-in Oscilloscope Training Signals with Step-by-Step Instructions and Tutorial

Agilent recommends that the first six labs (covered in Chapter 2: Basic Oscilloscope and WaveGen Measurements Labs) be completed by students during their first circuits lab session, before beginning any assigned circuit design experiments. Students will learn the following while completing the labs in Chapter 2 of the training guide:

- Probing basics
- Setting up vertical scaling (V/div)
- Setting up horizontal scaling (s/div)
- Making voltage and timing measurements the old-fashioned way
- Using cursors for voltage and timing measurements
- Triggering basics
- Averaging waveforms
- Electronically documenting measurement results
- Using the built-in function generator (optional feature)



**Figure 3: More complex training signals such as the “digital burst with infrequent glitch” signal, train students to use some of the scope’s more advanced triggering and measurement capabilities.**

The remaining nine labs (found in Chapter 3: Advanced Oscilloscope Measurement Labs) provide instructions on how to trigger on, and make measurements on more complex signals. These short labs, which are optional and require about 15 minutes each, can be completed by students who want to learn how to use some of the scope’s more advanced functions. Alternatively professors may choose to assign specific labs they consider as important for students to complete. Students will learn the following while completing the advanced oscilloscope measurement labs in Chapter 3 of the training guide:

- Using trigger holdoff to trigger on a digital burst signal
- Using pulse-width triggering to trigger on an infrequent glitch
- Using infinite-persistence display mode to accumulate all variations of a signal
- Capturing a single-shot event
- Making automatic pulse parametric measurements
- Using the scope’s horizontal zoom mode to perform “gated” measurements
- Making two channel phase delay measurements
- Using the scope’s XY mode to view Lissajous waveforms
- Using waveform math including Fast Fourier Transformation (FFT)
- Using the scope’s peak detect mode to overcome under-sampling
- Using segmented memory to capture multiple low duty cycle events (optional feature)


## Related Products

In addition to oscilloscopes, educational EE circuits or physics labs typically include a variety of test equipment. This equipment may include power supplies, digital multimeters, and function generators, which are used as a dynamic input source for assigned experiments. Another option available on Agilent's InfiniiVision X-Series scopes is the WaveGen built-in 20-MHz function/arbitrary waveform generator. Not only does the built-in function generator save valuable bench space in labs, it can also help stretch the limited test equipment budgets of electrical engineering and physics departments.

It should be noted that signals generated by WaveGen are different from the oscilloscope training signals that are provided with the DSOXEDK Educator's Training Kit. The WaveGen provides general-purpose 20-MHz function generator capabilities with user-definable frequencies, amplitudes, offset, and pulse widths. The WaveGen's output is routed to a BNC on the front panel of the scope below the display. The WaveGen can produce the following wave shapes:

- Sine wave
- Square wave (with variable duty cycle)
- Ramp
- Pulse (with variable pulse width)
- DC
- Noise
- Arbitrary
- Modulation

Output levels can range from 20 mVp-p up to 5.0 Vp-p when terminated into high impedance, or 10 mVp-p to 2.5 Vp-p when terminated into 50-Ω. Note that dual WaveGen option on the 4000 X-Series models has twice the output drive capability.



**Figure 4: The WaveGen general-purpose function generator provides a built-in stimulus source for student experiments.**

## University Courseware from DreamCatcher

Learning how to use an oscilloscope is just the first step in the electrical engineering lab curriculum. Depending upon the specific EE courses, the core content of lab assignments will probably be focused on a variety of analog and digital circuit design experiments. For ready-to-use EE lecturer slide-set and application-specific student training kit resources, Agilent recommends considering courseware from DreamCatcher.<sup>1</sup> DreamCatcher provides the following EE courseware:

### RF/microwave and wireless communications

- RF circuit design
- Digital RF communications
- Antenna and propagation
- EMI and EMC

### Digital and embedded systems

- Microcontroller system design (8051)
- Embedded system design (ARM9)
- Digital systems
- Digital signal processing

### General electronics

- Analog electronics
- Analog circuit design
- Electronic instrumentation and measurement

1. DreamCatcher is not affiliated with Agilent Technologies.

For additional information about DreamCatcher courseware, go to [www.dreamcatcher.asia/cw](http://www.dreamcatcher.asia/cw).

## Ordering Information

The Educator's Oscilloscope Training Kit (DSOXEDK) and the WaveGen function/arbitrary generator options are compatible with all InfiniiVision X-Series (DSO and MSO) models from Agilent. Existing InfiniiVision X-Series oscilloscopes can also be upgraded:

| Model number for user-installed license or for after-purchase upgrade | Option number for factory-installed license | Description  |
|---|---|--|
| DSOXEDK   | Option EDK                                  | Educator's Training Kit option that enables 11 oscilloscope training signals |
| DSOX2WAVEGEN  | Option 001                                  | Built-in 20-MHz function generator for 2000 X-Series scopes                  |
| DSOX3WAVEGEN  | Option 001                                  | Built-in 20-MHz function/arbitrary generator for 3000 X-Series scopes        |
| DSOX4WAVEGEN2   | Option WAV                                  | Built-in dual 20-MHz function/arbitrary generator for 4000 X-Series scopes   |

Additional options and accessories are available for Agilent's InfiniiVision X-Series oscilloscopes. Refer to the appropriate oscilloscope data sheets (see below) for information on ordering options and accessories, as well as ordering information for specific oscilloscope models.

You can download the "Oscilloscope Lab Guide and Tutorial" as well as the "Oscilloscope Fundamentals PowerPoint Slide-set," from Agilent's Web site at [www.agilent.com/find/edk](http://www.agilent.com/find/edk).

## Related Literature


| Publication Title   | Publication Type | Publication Number |
|---|------------------|--------------------|
| <i>InfiniiVision 2000 X-Series Oscilloscopes</i>  | Data Sheet       | 5990-6618EN        |
| <i>InfiniiVision 3000 X-Series Oscilloscope</i>   | Data Sheet       | 5990-6619EN        |
| <i>InfiniiVision 4000 X-Series Oscilloscope</i>   | Data Sheet       | 5991-1103EN        |
| <i>InfiniiVision Series Oscilloscope Probes and Accessories</i>                             | Selection Guide  | 5968-8153EN        |
| <i>Serial Bus Applications for InfiniiVision 2000, 3000 and 4000 X-Series Oscilloscopes</i> | Data Sheet       | 5990-6677EN        |

To download these documents, insert the publication number in the URL:  
<http://cp.literature.agilent.com/litweb/pdf/xxxx-xxxxEN.pdf>

## For Additional Information

For the most up-to-date and complete application and product information, please visit our product Web sites at  
[www.agilent.com/find/edk](http://www.agilent.com/find/edk)  
[www.agilent.com/find/2000X-Series](http://www.agilent.com/find/2000X-Series)  
[www.agilent.com/find/3000X-Series](http://www.agilent.com/find/3000X-Series)  
[www.agilent.com/find/4000X-Series](http://www.agilent.com/find/4000X-Series)





## Agilent Technologies Oscilloscopes

Multiple form factors from 20 MHz to > 90 GHz | Industry leading specs | Powerful applications



[www.agilent.com/find/myagilent](http://www.agilent.com/find/myagilent)

A personalized view into the information most relevant to you.



[www.axistandard.org](http://www.axistandard.org)

AdvancedTCA® Extensions for Instrumentation and Test (AXIe) is an open standard that extends the AdvancedTCA for general purpose and semiconductor test. Agilent is a founding member of the AXIe consortium.



[www.lxistandard.org](http://www.lxistandard.org)

LAN eXtensions for Instruments puts the power of Ethernet and the Web inside your test systems. Agilent is a founding member of the LXI consortium.



[www.pxisa.org](http://www.pxisa.org)

PCI eXtensions for Instrumentation (PXI) modular instrumentation delivers a rugged, PC-based high-performance measurement and automation system.

### Agilent Channel Partners

[www.agilent.com/find/channelpartners](http://www.agilent.com/find/channelpartners)

Get the best of both worlds: Agilent's measurement expertise and product breadth, combined with channel partner convenience.

Agilent  
Advantage  
Services



Agilent Advantage Services is committed to your success throughout your equipment's lifetime. We share measurement and service expertise to help you create the products that change our world. To keep you competitive, we continually invest in tools and processes that speed up calibration and repair, reduce your cost of ownership, and move us ahead of your development curve.

[www.agilent.com/find/advantageservices](http://www.agilent.com/find/advantageservices)



Windows® is a U.S. registered trademark of Microsoft Corporation.

[www.agilent.com](http://www.agilent.com)  
[www.agilent.com/find/edk](http://www.agilent.com/find/edk)

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at:

[www.agilent.com/find/contactus](http://www.agilent.com/find/contactus)

### Americas

|               |                |
|---------------|----------------|
| Canada        | (877) 894 4414 |
| Brazil        | (11) 4197 3600 |
| Mexico        | 01800 5064 800 |
| United States | (800) 829 4444 |

### Asia Pacific

|                    |                |
|--------------------|----------------|
| Australia          | 1 800 629 485  |
| China              | 800 810 0189   |
| Hong Kong          | 800 938 693    |
| India              | 1 800 112 929  |
| Japan              | 0120 (421) 345 |
| Korea              | 080 769 0800   |
| Malaysia           | 1 800 888 848  |
| Singapore          | 1 800 375 8100 |
| Taiwan             | 0800 047 866   |
| Other AP Countries | (65) 375 8100  |

### Europe & Middle East

|                |                      |
|----------------|----------------------|
| Belgium        | 32 (0) 2 404 93 40   |
| Denmark        | 45 45 80 12 15       |
| Finland        | 358 (0) 10 855 2100  |
| France         | 0825 010 700*        |
|                | *0.125 €/minute      |
| Germany        | 49 (0) 7031 464 6333 |
| Ireland        | 1890 924 204         |
| Israel         | 972-3-9288-504/544   |
| Italy          | 39 02 92 60 8484     |
| Netherlands    | 31 (0) 20 547 2111   |
| Spain          | 34 (91) 631 3300     |
| Sweden         | 0200-88 22 55        |
| United Kingdom | 44 (0) 118 927 6201  |

For other unlisted countries:

[www.agilent.com/find/contactus](http://www.agilent.com/find/contactus)


Revised: October 11, 2012

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2012, 2013  
Published in USA, February 14, 2013  
5990-6690EN



**Agilent Technologies**



# Serial Bus Options for InfiniiVision X-Series Oscilloscopes

## Data Sheet



### Supported Protocols and Features

- I<sup>2</sup>C
- SPI
- RS232/UART
- CAN
- LIN
- USB 2.0 low- and full-speed (4000 X-Series only)
- USB 2.0 hi-speed (4000 X-Series only)
- USB 2.0 signal quality (4000 X-Series only)
- I<sup>2</sup>S (3000 and 4000 X-Series only)
- FlexRay (3000 and 4000 X-Series only)
- MIL-STD 1553 (3000 and 4000 X-Series only)
- ARINC 429 (3000 and 4000 X-Series only)
- Hardware-based decoding
- Multi-bus analysis (3000 and 4000 X-Series only)
- Automatic search and navigation
- Compatibility with segmented memory acquisition
- Eye-diagram mask files available for CAN, FlexRay, MIL-STD 1553, and ARINC 429 (requires DSOX2MASK/DSOX3MASK/DSOX4MASK mask test option)
- FlexRay physical layer conformance test software (3000 and 4000 X-Series only)

### Introduction

Serial buses are pervasive in today's digital designs and are used for a variety of purposes including on-board chip-to-chip communication, CPU to peripheral control, as well as for remote sensor data transfer and control. Without intelligent oscilloscope serial bus triggering and protocol decode, it can be difficult to debug these buses and correlate data transfers with other mixed signal interactions in your system. Agilent's InfiniiVision X-Series oscilloscopes (DSOs) and mixed-signal oscilloscopes (MSOs) offer optional integrated serial bus triggering and hardware-based protocol decoding solutions that give you the tools you need to accelerate debug of your designs that include serial bus communication.





## Hardware-Based Decoding




**Figure 1: Hardware-based decoding quickly reveals serial communication errors.**

Agilent's InfiniiVision Series oscilloscopes are the industry's only scopes to use hardware-based decoding. Most other vendor's scopes with serial bus triggering and protocol decode, use software post-processing techniques to decode serial packets/frames. With these software techniques, waveform- and decode-update rates tend to be slow (sometimes seconds per update.) That's especially true when using deep memory, which is often required to capture multiple packetized serial bus signals. And when analyzing multiple serial buses simultaneously, software techniques can make decode update rates even slower.

Faster decoding with hardware-based technology enhances scope usability, and more importantly, the probability of capturing infrequent serial communication errors. Figure 1 shows an example of an Agilent InfiniiVision X-Series scope capturing a random and infrequent CAN error frame. The upper half of the scope's display shows the decoded data in a "Lister" format, along with a time-correlated decode trace shown below the waveform.

## Automatic Search and Navigation



**Figure 2: Automatic "Search & Navigation" quickly finds user-specified serial bus frames/bytes of interest.**

After capturing a long record of serial bus communication using the InfiniiVision scope's *MegaZoom* deep memory, you can easily perform a search operation based on specific criteria that you enter. Then, you can quickly navigate to bytes/frames of serial data that satisfy the entered search criteria. Figure 2 shows an example of searching on captured I<sup>2</sup>C data to find all occurrences of Read or Write operations with "No Ack." In this case, the scope found five occurrences of data transfers with "No Ack," and marked each occurrence with a white triangle to show where in time they happened relative to the captured waveform. Navigating and zooming-in on each marked byte/frame is quick and easy using the scope's front panel navigation keys.


## Multi-bus Analysis



**Figure 3: An interleaved “Lister” makes it easier to time-correlate activity between two decoded serial buses.**

Many of today’s designs include multiple serial buses. Sometimes it may be necessary to correlate data from one serial bus to another. Agilent’s InfiniiVision 3000 and 4000 X-Series oscilloscopes can decode two serial buses simultaneously using hardware-based decoding. Plus they are the only scopes on the market that can also display the captured data in a time-interleaved “Lister” display, as shown in Figure 3. In this particular example, the scope has simultaneously decoded and interleaved a CAN and LIN bus in an automotive system.

## Using Segmented Memory to Capture Multiple Serial Bus Packets



**Figure 4: Segmented memory acquisition selectively captures more packets/bytes of serial bus activity.**

The segmented memory option for Agilent’s InfiniiVision X-Series oscilloscopes can optimize your scope’s memory, letting you capture more packets/frames of serial bus activity. Segmented memory acquisition optimizes the number of packetized serial communication frames that can be captured consecutively. Segmented memory does this by capturing just the selective frames/bytes of interest while ignoring (not digitizing) idle time and other unimportant frames/bytes. Figure 4 shows an example of the oscilloscope capturing 500 consecutive hi-speed USB split packets for a total acquisition time of approximately 200 ms. Capturing this much data using conventional oscilloscope acquisition memory would require 1G bytes of memory.

Agilent’s InfiniiVision X-Series oscilloscopes are the only scopes on the market today that can acquire segments on up to four analog channels of acquisition, and time-correlated segments on digital channels (using an MSO model), along with automatic hardware-based serial bus decoding for each segment. In addition, you can use the scope’s Search & Navigation capability after a segmented memory acquisition has been performed.

## Serial Bus Eye-diagram and Pulse Mask Testing

With the addition of the DSOX2MASK, DSOX3MASK or DSOX4MASK mask test option, which can perform over 200,000 pass/fail tests (50,000 on 2000 X-Series) per second, you can perform eye-diagram and pulse mask testing on CAN signals on all InfiniiVision X-Series oscilloscope. Eye-diagram mask testing on FlexRay, MIL-STD 1553, and ARINC 429 signals can be performed using an InfiniiVision 3000 or 4000 X-Series oscilloscopes. Eye-diagram measurements provide a comprehensive signal quality test of the integrity of your transmitted and received signals. Agilent provides various mask files that you can download at no charge. The mask files are based on published industry mask standards and/or derived from physical layer/electrical specifications.

The following CAN mask files are available:

- 125 kbps – 400 meters
- 250 kbps – 200 meters
- 500 kbps – 10 meters
- 500 kbps – 80 meters
- 800 kbps – 40 meters
- 1000 kbps – 25 meters




Figure 5: CAN 500 kbps mask test on 10 meter system.

The following FlexRay mask test files are available:

- TP1 standard voltage (10 Mbps only)
- TP1 increased voltage (10 Mbps only)
- TP11 standard voltage (10 Mbps only)
- TP11 increased voltage (10 Mbps only)
- TP4 10 Mbps
- TP4 5 Mbps
- TP4 2.5 Mbps




Figure 6: FlexRay TP4 eye-diagram mask test.

The following MIL-STD 1553 mask test files are available:

- System xfrm-coupled Input
- System direct-coupled Input
- BC xfrm-coupled Input
- BC direct-coupled Input
- RT xfrm-coupled Input
- RT direct-coupled Input




Figure 7: MIL-STD 1553 BC to RT xfrm-coupled input mask test reveals a shifted bit that violates the pass/fail mask.

## Serial Bus Eye-diagram and Pulse Mask Testing

The following ARINC 429 mask/pulse test files are available:

- 100 kbps Eye Test
- 100 kbps 1's Pulse Test
- 100 kbps 0's Pulse Test
- 100 kbps Null Level Test
- 12.5 kbps Eye Test
- 12.5 kbps 1's Pulse Test
- 12.5 kbps 0's Pulse Test
- 12.5 kbps Null Level Test

For additional information about eye-diagram mask testing on CAN, FlexRay, MIL-STD 1553, and ARINC 429 signals, refer to the application notes listed at the end of this document.

## Automated Physical Layer Conformance Testing

To perform USB 2.0 signal quality testing based on USB-IF compliance standards, Agilent offers the DSOX4USBSQ option on InfiniiVision 4000 X-Series oscilloscopes. Figure 9 shows an example of the USB 2.0 real-time eye test. Also included with this option is complete signal quality test report generation in HTML format. To see the complete list of supported tests, refer to the DSOX4USBSQ signal quality test option data sheet listed at the end of this document.

To perform physical layer conformance testing on the differential FlexRay bus, Agilent provides a PC-based software package that you can download from Agilent's website at no additional charge. If the InfiniiVision X-Series scope is licensed with the FlexRay, mask test, and segmented memory, you can perform automated physical layer tests at either receiver input or transmitter output test points. Figure 9 shows an example of the generated report from a signal integrity voting test on a 10-Mbs isolated "1" pulse. The test report includes comprehensive pass/fail and margin analysis based on published specifications.

Refer to the tables in the Specifications/Characteristics section of this document on page 15 to see the entire list of 33 available FlexRay tests that can be selected and performed using the FlexRay physical layer conformance test software package.




Figure 8: ARINC 429 100 kbps eye-diagram mask test.




Figure 9: USB 2.0 signal quality eye test based on USB-IF physical layer compliance standards.




Figure 10: FlexRay signal integrity voting test performed on an isolated "1" bit.



## Probing Differential Serial Buses

Some of today's serial buses are based on differential signaling, such as USB, CAN, FlexRay, MIL-STD 1553, and ARINC 429. Probing differential serial buses such as these requires that you use a differential active probe. Agilent offers a range of differential active probes compatible with the InfiniiVision X-Series oscilloscopes for various bandwidth and dynamic range applications.

For the USB 2.0 hi-speed bus applications, Agilent recommends using the N2750A 1.5-GHz bandwidth differential active probe shown in Figure 11. With this probe's unique InfiniiMode feature, all it takes is the press of a button on the probe to quickly switch between viewing the differential signal, high-side signal, low-side signal, or the common mode signal on the USB 2.0 hi-speed bus.

For CAN, MIL-STD 1553, and ARINC 429 differential bus applications, Agilent recommends the 25-MHz bandwidth N2791A differential active probe shown in Figure 12.

For both CAN and FlexRay applications, Agilent recommends the 200-MHz bandwidth N2792A differential active probe shown in Figure 13.

If you need to connect to DB9-SubD connectors on your differential CAN and/or FlexRay bus, Agilent also offers the CAN/FlexRay DB9 probe head (part number 0960-2926). This differential probe head, which is shown in the insert of Figure 12, is compatible with both the N2791A and N2792A differential active probes and allows you to connect easily to your CAN and/or FlexRay differential bus.



**Figure 11: N2750A 1.5-GHz differential active probe.**



**Figure 12: Agilent N2791A 25-MHz differential active probe.**




**Figure 13: Agilent N2792A 200-MHz differential active probe.**




## Specifications/Characteristics

| I <sup>2</sup> C specifications/characteristics (DSOX2EMBD, DSOX3EMBD, and DSOX4EMBD) |   |
|---|---|
| Clock and data input source   | Analog channels 1, 2, 3, or 4<br>Digital channels D0 to D15 (3000 and 4000 X-Series only)   |
| Max clock/data rate   | Up to 3.4 Mbps  |
| Triggering  | Start condition<br>Stop condition<br>Missing acknowledge<br>Address with no acknowledge<br>Restart<br>EEPROM data read<br>Frame (Start:Addr7:Read:Ack:Data)<br>Frame (Start:Addr7:Write:Ack:Data)<br>Frame (Start:Addr7:Read:Ack:Data:Ack:Data2)<br>Frame (Start:Addr7:Write:Ack:Data:Ack:Data2)<br>10-bit write  |
| Hardware-based decode   | Data (HEX digits in white)<br>Address decode size: 7 bits (excludes R/W bit) or 8 bits (includes R/W bit)<br>Read address (HEX digits followed by "R" in yellow)<br>Write address (HEX digits followed by "W" in light-blue)<br>Restart addresses ("S" in green, followed by HEX digits, followed by "R" or "W")<br>Acknowledges (suffixes "A" or "~A" in the same color as the data or address preceding it)<br>Idle bus (mid-level bus trace in dark blue)<br>Active bus (bi-level bus trace in dark blue)<br>Unknown/error bus (bi-level bus trace in red) |
| Multi-bus analysis  | I <sup>2</sup> C plus one other serial bus, including another I <sup>2</sup> C bus. (3000 and 4000 X-Series only)   |




## Specifications/Characteristics

| SPI specifications/characteristics (DSOX2EMBD, DSOX3EMBD, and DSOX4EMBD) |  |
|--|--|
| MOSI, MISO, Clock, and CS input source                                   | Analog channels 1, 2, 3, or 4<br>Digital channels D0 to D15 (3000 and 4000 X-Series only)  |
| Max clock/data rate  | Up to 25 Mb/s  |
| Triggering   | 4- to 64-bit data pattern during a user-specified framing period<br>Framing period can be a positive or negative chip select (CS or ~CS) or clock idle time (timeout)  |
| Hardware-based decode  | Number of decode traces: 2 independent traces (MISO and MOSI)<br>Data (hex digits in white)<br>Unknown/error bus (bi-level bus trace in red)<br>Number of clocks/packet ("XX CLKS" in light-blue above data packet)<br>Idle bus (mid-level bus trace in dark blue)<br>Active bus (bi-level bus trace in dark blue) |
| Multi-bus analysis   | SPI plus one other serial bus, excluding another SPI bus. (3000 and 4000 X-Series only)  |



## Specifications/Characteristics


| RS232/UART specifications/characteristics (DSOX2COMP, DSOX3COMP, and DSOX4COMP) |  |
|---|--|
| Tx and Rx input source  | Analog channels 1, 2, 3, or 4<br>Digital channels D0 to D15 (3000 and 4000 X-Series only)  |
| Bus configuration   |  |
| Baud rates  | 100 b/s up to 8 Mb/s   |
| Number of bits  | 5 to 9   |
| Parity  | None, odd, or even   |
| Polarity  | Idle low or idle high  |
| Bit order   | LSB out first or MSB out first   |
| Triggering  | Rx start bit<br>Rx stop bit<br>Rx data<br>Rx 1:data (9-bit format)<br>Rx 0:data (9-bit format)<br>Rx X:data (9-bit format)<br>Rx or Tx parity error<br>Tx start bit<br>Tx stop bit<br>Tx data<br>Tx 1:data (9-bit format)<br>Tx 0:data (9-bit format)<br>Tx X:data (9-bit format)<br>Burst (nth frame within burst defined by timeout) |
| Hardware-based decode   |  |
| Number of decode traces   | 2 independent traces (Tx and Rx)   |
| Data format   | Binary, hex, or ASCII-code characters  |
| Data byte display   | White characters if no parity error, red characters if parity or bus error   |
| Idle bus trace  | Mid-level bus trace in blue  |
| Active bus trace  | Bi-level trace in blue   |
| Multi-bus analysis  | RS232/UART plus one other serial bus, including another RS232/UART bus.<br>(3000 and 4000 X-Series only)   |
| Totalize/counter function   | Total received frames<br>Total transmitted frames<br>Total parity error frames (with percentage)   |



## Specifications/Characteristics

### USB 2.0 low- and full-speed specifications/characteristics (DSOX4USBFL)

|  |   |
|--|---|
| USB input source (D+ & D-)             | Analog channels 1, 2, 3, 4<br>Digital channels D0-D15   |
| Speed                                  | Low (1.5 Mb/s) and Full (12 Mb/s)   |
| Triggering                             | Start of packet (SOP)<br>End of packet (EOP)<br>Suspend – when bus is idle for > 3 ms<br>Resume – when exiting an idle state > 10 ms<br>Reset – when SE0 is > 10 ms<br>Token packet with specified content<br>Data packet with specified content<br>Handshake packet with specified content<br>Special packet with specified content<br>All errors – any of the below error conditions<br>PID error – if packet type field does not match check field<br>CRC5 error – if 5 bit CRC error is detected<br>CRC16 error – if 16 bit CRC error is detected<br>Glitch error – if two transitions occur in half a bit time<br>Bit stuff error – if >6 consecutive “ones” are detected<br>SE1 error – if SE1 > 1 bit time |
| <b>Hardware-based decode</b>           |   |
| Base format                            | Hex, Binary, ASCII, or Decimal data decode  |
| Token packets (excluding SOF, 3 bytes) | PID (yellow, “OUT”, “IN”, “SETUP”, “PING”)<br>PID Check (yellow when valid, red when error detected) – numeric value<br>Address (blue, 7 bits)<br>Endpoint (green, 4 bits)<br>CRC (blue when valid, red when error detected, 5 bits)  |
| Token packets (SOF, 3 bytes)           | PID (yellow, “SOF”)<br>PID Check (yellow when valid, red when error detected, 5 bits)<br>Frame (green, 11-bits) – the frame number<br>CRC (blue when valid, red when error detected, 5 bits)  |
| Data packets (3 to 1027 bytes)         | PID (yellow, “DATA0”, “DATA1”, “DATA2”, “MDATA”)<br>PID Check (yellow when valid, red when error detected, 16 bits)   |
| Handshake packets (1 byte)             | PID (yellow, “ACK”, “NAK”, “STALL”, “NYET”, “PRE”, “ERR”)<br>PID Check (yellow when valid, read when error detected) – numeric value<br>Hub Addr (green, 7 bits)<br>SC (blue, 1 bit)<br>Port (green, 7 bits)<br>S & E U (blue, 2 bits)<br>ET (green, 2 bits)<br>CRC (blue when valid, red when error detected, 5 bits)  |
| Multi-bus analysis                     | USB low-full-speed plus one other serial bus (including another USB bus)  |



## Specifications/Characteristics


| USB 2.0 high-speed specifications/characteristics (DSOX4USBH) |  |
|---|--|
| USB differential input source                                 | Analog channels 1, 2, 3, 4 (using a differential active probe)   |
| Speed   | High (480 Mb/s)  |
| Triggering  | Token packet with specified content<br>Data packet with specified content<br>Handshake packet with specified content<br>Special packet with specified content<br>All errors – any of the below error conditions<br>PID error – if packet type field does not match check field<br>CRC5 error – if 5 bit CRC error is detected<br>CRC16 error – if 16 bit CRC error is detected<br>Glitch error – if two transitions occur in half a bit time |
| Hardware-based decode   |  |
| Base format   | Hex, Binary, ASCII, or Decimal data decode   |
| Token packets (excluding SOF, 3 bytes)                        | PID (yellow, "OUT", "IN", "SETUP", "PING")<br>PID check (yellow when valid, red when error detected) – numeric value<br>Address (blue, 7 bits)<br>Endpoint (green, 4 bits)<br>CRC (blue when valid, red when error detected, 5 bits)   |
| Token packets (SOF, 3 bytes)                                  | PID (yellow, "SOF")<br>PID check (yellow when valid, red when error detected, 5 bits)<br>Frame (green, 11-bits) – the frame number<br>CRC (blue when valid, red when error detected, 5 bits)   |
| Data packets (3 to 1027 bytes)                                | PID (yellow, "DATA0", "DATA1", "DATA2", "MDATA")<br>PID check (yellow when valid, red when error detected, 16 bits)  |
| Handshake packets (1 byte)                                    | PID (yellow, "ACK", "NAK", "STALL", "NYET", "PRE", "ERR")<br>PID check (yellow when valid, red when error detected) – numeric value<br>Hub Addr (green, 7 bits)<br>SC (blue, 1 bit)<br>Port (green, 7 bits)<br>S & E U (blue, 2 bits)<br>ET (green, 2 bits)<br>CRC (blue when valid, red when error detected, 5 bits)  |
| Multi-bus analysis  | N/A  |






## Specifications/Characteristics

| CAN specifications/characteristics (DSOX2AUTO, DSOX3AUTO, and DSOX4AUTO) |  |
|--|--|
| CAN input source   | Analog channels 1, 2, 3, or 4<br>Digital channels D0 to D15 non-differential. (3000 and 4000 X-Series only)  |
| Signal types   | Rx<br>Tx<br>CAN_L<br>CAN_H<br>Diff (L-H)<br>Diff (H-L)   |
| Baud rates   | 10 kb/s up to 5 Mb/s   |
| Triggering   | Start-of-frame (SOF)<br>Remote frame ID (RMT)<br>Data frame ID (~RMT)<br>Remote or data frame ID<br>Data frame ID and data<br>Error frame<br>All errors (includes protocol “form” errors that may not generate flagged error frames)<br>Acknowledge errors<br>Overload frames<br>ID length: 11 bits or 29 bits (extended)  |
| Hardware-based decode  | Frame ID (hex digits in yellow)<br>Remote frame (RMT in green)<br>Data length code (DLC in blue)<br>Data bytes (hex digits in white)<br>CRC (hex digits in blue = valid, hex digits in red = error)<br>Error frame (bi-level bus trace and ERR message in red)<br>Form error (bi-level bus trace and “?” in red)<br>Overload frame (“OVRD” in blue)<br>Idle bus (mid-level bus trace in dark blue)<br>Active bus (bi-level bus trace in dark blue) |
| Multi-bus analysis   | CAN plus one other serial bus, including another CAN bus. (3000 and 4000 X-Series only)  |
| Totalize function  | Total frames, total overload frames, total error frames, bus utilization (bus load)  |
| Eye-diagram mask testing (requires DSOX3MASK)                            | Various downloadable mask files available based on differential probing polarity, baud rate, and network length  |




## Specifications/Characteristics

| LIN specifications/characteristics (DSOX2AUTO, DSOX3AUTO, and DSOX4AUTO) |  |
|--|--|
| LIN input source   | Analog channels 1, 2, 3, or 4<br>Digital channels D0 to D15 (3000 and 4000 X-Series only)  |
| LIN standards  | LIN 1.3 or LIN 2.0   |
| Baud rates   | 2400 b/s to 625 kb/s   |
| Triggering   | Sync break<br>Frame ID (0X00 <sub>HEX</sub> to 0X3F <sub>HEX</sub> )<br>Frame ID and data  |
| Hardware-based decode  | Frame ID (6-bit hex digits in yellow)<br>Frame ID and optional parity bits (8-bit hex digits in yellow if valid, red if parity bit error)<br>Data bytes (hex digits in white)<br>Lin 2.0 check sum (hex digits in white)<br>Lin 1.3 check sum (hex digits in blue = valid, hex digits in red = error)<br>Sync error ("SYNC" in red)<br>THeader-max ("THM" in red)<br>TFrame-max ("TFM" in red)<br>Parity error ("PAR" in red)<br>LIN 1.3 wake-up error ("WUP" in red)<br>LIN 1.3 idle bus (mid-level bus trace in dark blue)<br>LIN 2.0 idle bus (bi-level bus trace in dark blue)<br>Active bus (bi-level bus trace in dark blue) |
| Multi-bus analysis   | LIN plus one other serial bus, including another LIN bus. (3000 and 4000 X-Series only)  |



## Specifications/Characteristics

| FlexRay specifications/characteristics (DSOX3FLEX and DSOX4FLEX)                            |   |
|---|---|
| FlexRay input source  | Channel 1, 2, 3, or 4 (using differential probe)  |
| FlexRay channels  | A or B  |
| Baud rates  | 2.5 Mbps, 5.0 Mbps, and 10 Mbps   |
| Frame triggering  | <ul style="list-style-type: none"> <li>Frame type: startup (SUP), not startup (~SUP), sync (SYNC), not sync (~SYNC), null (NULL), not null (~NULL), normal (NORM), and All</li> <li>Frame ID: 1 to 2047 (decimal format), and All</li> <li>Cycle - <ul style="list-style-type: none"> <li>Base: 0 to 63 (decimal format), and All</li> <li>Repetition: 1, 2, 4, 8, 16, 32, 64 (decimal format), and All</li> </ul> </li> </ul>              |
| Error triggering  | <ul style="list-style-type: none"> <li>All errors</li> <li>Header CRC error</li> <li>Frame CRC error</li> </ul>   |
| Event triggering  | <ul style="list-style-type: none"> <li>Wake-up</li> <li>TSS (transmission start sequence)</li> <li>BSS (byte start sequence)</li> <li>FES/DTS (frame end or dynamic trailing sequence)</li> </ul>   |
| Frame decoding  | <ul style="list-style-type: none"> <li>Frame type (NORM, SYNC, SUP, NULL in blue)</li> <li>Frame ID (decimal digits in yellow)</li> <li>Payload-length (decimal number of words in green)</li> <li>Header CRC (hex digits in blue if valid, or red digits if invalid)</li> <li>Cycle number (decimal digits in yellow)</li> <li>Data bytes (HEX digits in white)</li> <li>Frame CRC (hex digits in blue if valid, or red digits)</li> </ul> |
| Totalize function   | <ul style="list-style-type: none"> <li>Total frames</li> <li>Total synchronization frames</li> <li>Total null frames</li> </ul>   |
| Eye-diagram mask testing (requires DSOX3MASK mask test option plus downloadable mask files) | TP1 standard voltage (10 Mbps only)<br>TP1 increased voltage (10 Mbps only)<br>TP11 standard voltage (10 Mbps only)<br>TP11 increased voltage (10 Mbps only)<br>TP4 10 Mbps, TP4 5 Mbps and TP4 2.5 Mbps  |
| Multi-bus analysis  | FlexRay plus one other serial bus (including another FlexRay bus)   |



**FlexRay Physical Layer Conformance Test software**  
**(Requires DS0X3FLEX/DS0X4FLEX, DS0X3MASK/DS0X4MASK, and DS0X3SGM)**


| Table 1: Receiver input tests  |   |
|--|---|
| Parameter tested   | Test description                              |
| <b>Eye-diagram mask tests:</b>   |   |
| TP4 – All  | Receiver mask test on all frames              |
| TP4 – ID   | Receiver mask test on specified frame         |
| <b>Signal integrity voting tests on 13 MHz low-pass filtered Isolated “1”:</b> |   |
| uData1Top  | Required maximal level                        |
| dBitShort  | Shortest single bit                           |
| dBitLengthVariation  | Bit asymmetry                                 |
| dEdge01  | Rising edge duration (-300 mV to +300 mV)     |
| dEdge10  | Falling edge duration (+300 mV to -300 mV)    |
| dEdgeMax   | Slowest edge                                  |
| Sq1  | Isolated “1” voted signal quality             |
| <b>Signal integrity voting tests on 13 MHz low-pass filtered Isolated “0”:</b> |   |
| uData0Top  | Required minimal level                        |
| dBitShort  | Shortest single bit                           |
| dBitLengthVariation  | Bit asymmetry                                 |
| dEdge01  | Rising edge duration (-300 mV to +300 mV)     |
| dEdge10  | Falling edge duration (+300 mV to -300 mV)    |
| dEdgeMax   | Slowest edge                                  |
| Sq0  | Isolated “0” voted signal quality             |
| <b>Advanced diagnostic tests:</b>  |   |
| gdTSSTransmitter   | Transmitted TSS width @ receiver              |
| MCT  | Mean corrected cycle time                     |
| uBusRx-Data  | Data 1 amplitude                              |
| -uBusRx-Data   | Data 0 amplitude                              |
| uRx-Idle   | Mean idle level                               |
| dBusRx01   | Rise time Data0 to Data1 (-300 mV to +300 mV) |
| dBusRx10   | Fall time Data1 to Data0 (+300 mV to -300 mV) |

| Table 2: Transmitter output tests            |   |
|--|---|
| Parameter tested                             | Test description                                  |
| <b>Eye-diagram mask tests (10 Mbs only):</b> |   |
| TP1 – Std V                                  | Mask test on standard voltage bus driver output   |
| TP1 – Incr V                                 | Mask test on increased voltage bus driver output  |
| TP11 – Std V                                 | Mask test on standard voltage active star output  |
| P11 – Incr V                                 | Mask test on increased voltage active star output |
| <b>Advanced diagnostic tests:</b>            |   |
| gdTSSTransmitter                             | Transmitted TSS width                             |
| uBusTx-Data                                  | Data 1 amplitude                                  |
| -uBusTx-Data                                 | Data 0 amplitude                                  |
| uRx-Idle                                     | Mean idle level                                   |
| dBusTx01                                     | Rise time Data0 to Data1 (20% to 80%)             |
| dBusTx10                                     | Fall time Data1 to Data0 (80% to 20%)             |

## Specifications/Characteristics

### I<sup>2</sup>S specifications/characteristics (DSOX3AUDIO and DSOX4AUDIO)

|                                  |   |
|----------------------------------|---|
| SCLK, WS, and SDATA input source | Analog channels 1, 2, 3, or 4<br>Digital channels D0 to D15   |
| Bus configuration:               |   |
| Transmitted word size            | 4 to 32 bits (user selectable)  |
| Decoded/receiver word size       | 4 to 32 bits (user selectable)  |
| Alignment                        | Standard, left-justified, or right-justified  |
| Word select - low                | Left-channel or right-channel   |
| SCLK slope                       | Rising edge or falling edge   |
| Decoded base                     | Hex (2's complement) or signed decimal  |
| Baud rates                       | 2400 b/s to 625 kb/s  |
| Triggering:                      |   |
| Audio channel                    | Audio left, audio right, or either  |
| Trigger modes                    | = (Equal to entered data value)<br>≠ (Not equal to entered data value)<br>< (Less than entered data value)<br>> (Greater than entered data value)<br>>< (Within range of entered data values)<br><> (Out of range of entered data values)<br>Increasing value that crosses armed (<=) and trigger (>=) entered data values<br>Decreasing value that crosses armed (>=) and trigger (<=) entered data values |
| Hardware-based decode:           |   |
| Left channel                     | L: "decoded value" in white   |
| Right channel                    | R: "decoded value" in green   |
| Error                            | ERR in red (mismatch between transmitted and received word size, or invalid input signaling)  |
| Word size indicator              | "# of TX / # of RX" CLKS in blue displayed above each decoded word  |
| Multi-bus analysis               | I <sup>2</sup> S plus one other serial bus (excluding another I <sup>2</sup> S bus)   |






## Specifications/Characteristics


### MIL-STD 1553 specifications/characteristics (DSOX3AERO and DSOX4AERO)

|   |  |
|---|--|
| MIL-Std 1553 Input Source   | Analog channels 1, 2, 3, or 4 (using a differential active probe)  |
| Triggering  | <ul style="list-style-type: none"> <li>• Data word start</li> <li>• Data word stop</li> <li>• Command/status word start</li> <li>• Command/status word stop</li> <li>• Remote terminal address (hex)</li> <li>• Remote terminal address (hex) + 11 bits (binary)</li> <li>• Parity error</li> <li>• Sync error</li> <li>• Manchester error</li> </ul>  |
| Color-coded, hardware-accelerated decode  | <ul style="list-style-type: none"> <li>• Base: HEX or binary</li> <li>• Command or status word ("C/S" in green)</li> <li>• Remote terminal address (hex or binary digits in green)</li> <li>• 11 Bits following RTA (hex or binary digits in green)</li> <li>• Data word ("D" in white)</li> <li>• Data word bits (hex or binary digits in white)</li> <li>• Parity error (all decoded text in red)</li> <li>• Synchronization error ("Sync" in red)</li> <li>• Manchester error ("Manch" in red)</li> </ul> |
| Eye-diagram mask testing (requires DSOX3MASK mask test option plus downloadable mask files) | <ul style="list-style-type: none"> <li>• System xfmr-coupled Input</li> <li>• System direct-coupled Input</li> <li>• BC xfmr-coupled Input</li> <li>• BC direct-coupled Input</li> <li>• RT xfmr-coupled Input</li> <li>• RT xfmr-coupled Input</li> </ul>   |
| Multi-bus analysis  | MIL-STD 1553 plus one other serial bus, (including another MIL-STD 1553 bus)   |



## Specifications/Characteristics

| ARINC 429 specifications/characteristics (DSOX3AERO and DSOX4AERO)                   |   |
|--|---|
| ARINC 429 input source   | Analog channels 1, 2, 3, or 4 (using a differential active probe)   |
| Baud rates   | High (100 kbps)<br>Low (12.5 kbps)  |
| Triggering   | Word start<br>Word stop<br>Label (octal)<br>Label (octal) + bits (binary)<br>Label range (octal)<br>Parity error<br>Word error<br>Gap error<br>Word or gap error<br>All errors<br>All bits (useful for eye-diagram testing)<br>All 0 bits<br>All 1 bits |
| Color-coded, hardware-accelerated decode   | Word format: label/SDI/data/SSM or label/data/SSM or label/data<br>Label (octal digits in yellow)<br>SDI (binary digits in blue)<br>Data (hex or binary digits in white)<br>SSM (binary digits in green)<br>Errors (text in red)                        |
| Totalize function  | Total words<br>Total errors   |
| Eye-diagram and pulse mask testing (requires DSOX3MASK plus downloadable mask files) | 100 kbps eye test<br>100 kbps 1's test<br>100 kbps 0's test<br>100 kbps null test<br>12.5 kbps eye test<br>12.5 kbps 1's test<br>12.5 kbps 0's test<br>12.5 kbps null test  |
| Multi-bus analysis   | ARINC 429 plus one other bus (including another ARINC 429 bus)  |



## Ordering Information

The various serial bus options are compatible on most models of the Agilent InfiniiVision 3000 and 4000 X-Series oscilloscopes. The entry-level 2000 X-Series oscilloscopes support only the I2C/SPI, RS232/UART, and CAN/LIN options. Existing InfiniiVision X-Series oscilloscopes can also be upgraded with these options.

For most model numbers, the number after DSOX tells you to which series of oscilloscope it applies. For example, DSOX2EMBD applies to the 2000 X-Series and DSOX3EMBD applies to the 3000 X-Series.

| Model number                      | Description  |
|-----------------------------------|--|
| DSOX2EMBD, DSOX3EMBD or DSOX4EMBD | I <sup>2</sup> C and SPI trigger and decode  |
| DSOX2COMP, DSOX3COMP or DSOX4COMP | RS232/UART trigger and decode  |
| DSOX2AUTO, DSOX3AUTO or DSOX4AUTO | CAN and LIN trigger and decode   |
| DSOX3FLEX or DSOX4FLEX            | FlexRay trigger and decode   |
| DSOX3AERO or DSOX4AERO            | MIL-STD 1553 and ARINC 429 trigger and decode  |
| DSOX3AUDIO or DSOX4AUDIO          | I <sup>2</sup> S trigger and decode  |
| DSOX4USBFL                        | USB 2.0 low- and full-speed trigger and decode   |
| DSOX4USBH                         | USB 2.0 hi-speed trigger and decode (1 GHz and 1.5 GHz bandwidth models of 4000 X-Series only)   |
| DSOX4USBSQ                        | USB 2.0 signal quality test (hi-speed tests require 1.5 GHz bandwidth models)                    |
| DSOX2SGM and DSOX3SGM             | Segmented memory (standard on 4000 X-Series models)  |
| DSOX2MASK, DSOX3MASK or DSOX4MASK | Mask test option   |
| N2791A                            | 25-MHz differential active probe (recommended for CAN, MIL-STD 1553, and ARINC 429 applications) |
| N2792A                            | 200-MHz differential active probe (recommended for FlexRay applications)                         |
| N2750A                            | 1.5 GHz differential active probe (recommended for USB 2.0 hi-speed applications)                |
| 0960-2926                         | DB9 probe head adapter for N2791A and N2792A   |

Additional options and accessories are available for Agilent's InfiniiVision oscilloscopes. Refer to the first four documents in the list below for ordering information about these additional options and accessories.

## Related Agilent literature

| Publication Title   | Publication Type | Publication Number |
|---|------------------|--------------------|
| <i>InfiniiVision 2000 X-Series Oscilloscope</i>                         | Data Sheet       | 5990-6618EN        |
| <i>InfiniiVision 3000 X-Series Oscilloscope</i>                         | Data Sheet       | 5990-6619EN        |
| <i>InfiniiVision 4000 X-Series Oscilloscope</i>                         | Data Sheet       | 5991-1103EN        |
| <i>InfiniiVision Series Oscilloscope Probes and Accessories</i>         | Selection Guide  | 5968-8153EN        |
| <i>N2750A/51A/52A InfiniiMode Differential Active Probes</i>            | Data Sheet       | 5991-0560EN        |
| <i>DSOX4USBSQ USB 2.0 Signal Quality Test Option</i>                    | Data Sheet       | 5991-1762EN        |
| <i>Using Oscilloscope Segmented Memory for Serial Bus Applications</i>  | Application Note | 5990-5817EN        |
| <i>Characterizing Hi-speed USB 2.0 Serial Buses in Embedded Designs</i> | Application Note | 5991-1148EN        |
| <i>CAN Eye-diagram Mask Testing</i>                                     | Application Note | 5991-0484EN        |
| <i>FlexRay Eye-diagram Mask Testing</i>                                 | Application Note | 5990-4923EN        |
| <i>MIL-STD 1553 Eye-diagram Mask Testing</i>                            | Application Note | 5990-9324EN        |
| <i>ARINC 429 Eye-diagram Mask Testing</i>                               | Application Note | 5990-9325EN        |

To download these documents, insert the publication number in the URL:

<http://cp.literature.agilent.com/litweb/pdf/xxxx-xxxxEN.pdf>

## Product Web site

For the most up-to-date and complete application and product information, please visit our product Web sites at:

[www.agilent.com/find/2000X-Series](http://www.agilent.com/find/2000X-Series)

[www.agilent.com/find/3000X-Series](http://www.agilent.com/find/3000X-Series)

[www.agilent.com/find/4000X-Series](http://www.agilent.com/find/4000X-Series)



**myAgilent**

[www.agilent.com/find/myagilent](http://www.agilent.com/find/myagilent)

A personalized view into the information most relevant to you.



[www.axistandard.org](http://www.axistandard.org)

AdvancedTCA® Extensions for Instrumentation and Test (AXIe) is an open standard that extends the AdvancedTCA for general purpose and semiconductor test. Agilent is a founding member of the AXIe consortium.



[www.lxistandard.org](http://www.lxistandard.org)

LAN eXtensions for Instruments puts the power of Ethernet and the Web inside your test systems. Agilent is a founding member of the LXI consortium.

### Agilent Channel Partners

[www.agilent.com/find/channelpartners](http://www.agilent.com/find/channelpartners)

Get the best of both worlds: Agilent's measurement expertise and product breadth, combined with channel partner convenience.




Agilent Advantage Services is committed to your success throughout your equipment's lifetime. To keep you competitive, we continually invest in tools and processes that speed up calibration and repair and reduce your cost of ownership. You can also use Infoline Web Services to manage equipment and services more effectively. By sharing our measurement and service expertise, we help you create the products that change our world.

[www.agilent.com/find/advantageservices](http://www.agilent.com/find/advantageservices)



[www.agilent.com/quality](http://www.agilent.com/quality)

Windows® is a U.S. registered trademark of Microsoft Corporation.



Agilent Technologies Oscilloscopes

Multiple form factors from 20 MHz to > 90 GHz | Industry leading specs | Powerful applications

[www.agilent.com](http://www.agilent.com)

[www.agilent.com/find/2000X-Series](http://www.agilent.com/find/2000X-Series)

[www.agilent.com/find/3000X-Series](http://www.agilent.com/find/3000X-Series)

[www.agilent.com/find/4000X-Series](http://www.agilent.com/find/4000X-Series)

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at:

[www.agilent.com/find/contactus](http://www.agilent.com/find/contactus)

### Americas

|               |                |
|---------------|----------------|
| Canada        | (877) 894 4414 |
| Brazil        | (11) 4197 3600 |
| Mexico        | 01800 5064 800 |
| United States | (800) 829 4444 |

### Asia Pacific

|                    |                |
|--------------------|----------------|
| Australia          | 1 800 629 485  |
| China              | 800 810 0189   |
| Hong Kong          | 800 938 693    |
| India              | 1 800 112 929  |
| Japan              | 0120 (421) 345 |
| Korea              | 080 769 0800   |
| Malaysia           | 1 800 888 848  |
| Singapore          | 1 800 375 8100 |
| Taiwan             | 0800 047 866   |
| Other AP Countries | (65) 375 8100  |

### Europe & Middle East

|                |                      |
|----------------|----------------------|
| Belgium        | 32 (0) 2 404 93 40   |
| Denmark        | 45 45 80 12 15       |
| Finland        | 358 (0) 10 855 2100  |
| France         | 0825 010 700*        |
|                | *0.125 €/minute      |
| Germany        | 49 (0) 7031 464 6333 |
| Ireland        | 1890 924 204         |
| Israel         | 972-3-9288-504/544   |
| Italy          | 39 02 92 60 8484     |
| Netherlands    | 31 (0) 20 547 2111   |
| Spain          | 34 (91) 631 3300     |
| Sweden         | 0200-88 22 55        |
| United Kingdom | 44 (0) 118 927 6201  |

For other unlisted countries:

[www.agilent.com/find/contactus](http://www.agilent.com/find/contactus)

Revised: October 11, 2012

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2012, 2013  
Published in USA, February 19, 2013  
5990-6677EN



**Agilent Technologies**