


Glass Passivated Bridge Rectifiers

GBPC 25 Series



Features:

- The plastic material
- Integrally moulded heatsink provide very low thermal resistance for maximum heat dissipation
- Surge overload ratings from 300 to 400 A
- Terminals solderable per MIL-STD-202, method 208 (for wire type)
- Typical I_R less than 0.2 μ A
- High temperature soldering guaranteed, 260°C / 10 seconds 0.375 inches (9.5 mm) lead lengths (for wire type)
- Isolated voltage from case to lead over 2,500 V



Dimensions : Inches (Millimetres)

Glass Passivated Bridge Rectifiers

GBPC 25 Series

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate current by 20%

Type Number	GBPC2501	GBPC2502	GBPC2504	GBPC2506	Unit
Maximum Recurrent Peak Reverse Voltage	100	200	400	600	V
Maximum RMS Voltage	70	140	280	420	
Maximum DC Blocking Voltage	100	200	400	600	
Maximum Average Forward Rectified Current at T _C = 55°C	25				A
Peak Forward Surge Current, Single Sine-wave Superimposed on Rated Load (JEDEC method)	300				
Maximum Instantaneous Forward Voltage Drop Per 12.5 A Element at Specified Current	1.1				V
Maximum DC Reverse Current at Rated DC Blocking Voltage Per Element	5				mA
Typical Thermal Resistance (Note 1) RθJC	1.5				°C / W
Operating and Storage Temperature Range T _J , T _{STG}	-50 to +150				°C

Notes: 1. Thermal resistance from junction to case

Ratings and Characteristic Curves

Fig. 1 Maximum Forward Current Derating Curve





Fig. 3 Typical Reverse Characteristics Per Bridge Element



Glass Passivated Bridge Rectifiers



GBPC 25 Series

Fig. 2 Maximum Non-Repetitive Forward Surge Current Per Bridge Element





Fig. 4 Typical Forward Characteristics Per Bridge Element



Part Number Table

Description	Part Number
Bridge Rectifier, 25 A, 100 V	GBPC2501
Bridge Rectifier, 25 A, 200 V	GBPC2502
Bridge Rectifier, 25 A, 400 V	GBPC2504
Bridge Rectifier, 25 A, 600 V	GBPC2506

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.