


[illegible]










ALTERNATE ENGRAVING LOCATION
(7-12 CKT PARTS ONLY). LOCATION
IS DEPENDENT ON TOOLING.

QUALITY SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
	= 0	SEE SHEET 1 EC NO: 111298 DRWN: MKIPPER CHKD: MKIPPER APPR: FSMITH	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION UNITS		SCALE								
	= 0				MM/IN	NTS								
	= 0													
	= 0				DRWN BY		DATE		FRICITION LOCK HEADER ASY .100 CL BENT SQ. PINS 7478 SERIES					
	= 0			4 PLACES	±	±	GUZIC						1987/07/30	
	= 0			3 PLACES	±	± .010	CHK'D BY						DATE	
	= 0			2 PLACES	± 0.25	± .015	PATEL		1987/07/30		PRODUCT CUSTOMER DRAWING			
	= 0			1 PLACES	± 0.38	±	APPR BY		DATE					
	= 0			0 PLACES	±	±	FSMITH		2014/05/16					
	= 0			ANGULAR TOL = 1/2		DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES 7478 MATERIAL NUMBER SEE CHART CUSTOMER GENERAL MARKET				
	= 0		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		C									
	= 0													
AA2			REV	DOCUMENT NUMBER SDA-7478							DOC TYPE PSD	DOC PART 000	SHEET NUMBER 2 OF 5	

[illegible]

[illegible]

12		11		10		9		8		7		6		5		4		3		2		1	
A-7478-ANE197				A-7478-NM197				A-7478-NH228				A-7478-NN197				A-7478-NP197							
PART NO.		ENG. NO.		PART NO.		ENG. NO.		PART NO.		ENG. NO.		PART NO.		ENG. NO.		PART NO.		ENG. NO.					
		A-7478-A2E197			22-12-4028	A-7478-2M197			22-16-3026	A-7478-2H228				A-7478-2N197		50-29-0033		A-7478-2P197					
		A-7478-A3E197			22-12-4038	A-7478-3M197			22-16-3036	A-7478-3H228				A-7478-3N197				A-7478-3P197					
		A-7478-A4E197			22-12-4048	A-7478-4M197			22-16-3046	A-7478-4H228				A-7478-4N197				A-7478-4P197					
22-05-3055		A-7478-A5E197			22-12-4058	A-7478-5M197			22-16-3056	A-7478-5H228				A-7478-5N197		22-05-8053		A-7478-5P197					
		A-7478-A6E197			22-12-4068	A-7478-6M197			22-16-3066	A-7478-6H228				A-7478-6N197				A-7478-6P197					
22-05-3075		A-7478-A7E197			22-12-4078	A-7478-7M197			22-16-3076	A-7478-7H228				A-7478-7N197				A-7478-7P197					
		A-7478-A8E197			22-12-4088	A-7478-8M197			22-16-3086	A-7478-8H228				A-7478-8N197				A-7478-8P197					
		A-7478-A9E197			22-12-4098	A-7478-9M197			22-16-3096	A-7478-9H228				A-7478-9N197				A-7478-9P197					
		A-7478-A10E197			22-12-4108	A-7478-10M197			22-16-3106	A-7478-10H228				A-7478-10N197				A-7478-10P197					
		A-7478-A11E197			22-12-4118	A-7478-11M197			22-16-3116	A-7478-11H228				A-7478-11N197				A-7478-11P197					
		A-7478-A12E197			22-12-4128	A-7478-12M197			22-16-3126	A-7478-12H228				A-7478-12N197				A-7478-12P197					
		A-7478-A13E197			22-12-4138	A-7478-13M197			22-16-3136	A-7478-13H228				A-7478-13N197				A-7478-13P197					
		A-7478-A14E197			22-12-4148	A-7478-14M197			22-16-3146	A-7478-14H228				A-7478-14N197				A-7478-14P197					
		A-7478-A15E197			22-12-4158	A-7478-15M197			22-16-3156	A-7478-15H228				A-7478-15N197				A-7478-15P197					
		A-7478-A16E197			22-12-4168	A-7478-16M197			22-16-3166	A-7478-16H228				A-7478-16N197				A-7478-16P197					
		A-7478-A17E197			22-12-4178	A-7478-17M197			22-16-3176	A-7478-17H228		22-59-5176		A-7478-17N197				A-7478-17P197					
		A-7478-A18E197			22-12-4188	A-7478-18M197			22-16-3186	A-7478-18H228				A-7478-18N197				A-7478-18P197					
22-05-3195		A-7478-A19E197			22-12-4198	A-7478-19M197			22-16-3196	A-7478-19H228				A-7478-19N197				A-7478-19P197					
		A-7478-A20E197			22-12-4208	A-7478-20M197			22-16-3206	A-7478-20H228				A-7478-20N197				A-7478-20P197					
		A-7478-A21E197			22-12-4218	A-7478-21M197			22-16-3216	A-7478-21H228				A-7478-21N197				A-7478-21P197					
		A-7478-A22E197			22-12-4228	A-7478-22M197			22-16-3226	A-7478-22H228				A-7478-22N197				A-7478-22P197					
		A-7478-A23E197			22-12-4238	A-7478-23M197			22-16-3236	A-7478-23H228				A-7478-23N197				A-7478-23P197					
		A-7478-A24E197			22-12-4248	A-7478-24M197			22-16-3246	A-7478-24H228				A-7478-24N197				A-7478-24P197					
		A-7478-A25E197			22-12-4258	A-7478-25M197			22-16-3256	A-7478-25H228				A-7478-25N197				A-7478-25P197					
		A-7478-A26E197			22-12-4268	A-7478-26M197			22-16-3266	A-7478-26H228				A-7478-26N197				A-7478-26P197					
		A-7478-A27E197			22-12-4278	A-7478-27M197			22-16-3276	A-7478-27H228				A-7478-27N197				A-7478-27P197					
		A-7478-A28E197			22-12-4288	A-7478-28M197			22-16-3286	A-7478-28H228				A-7478-28N197				A-7478-28P197					

QUALITY SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																									
SEE SHEET 1		= 0	2016/03/16 2017/04/11 2017/04/28	EC NO: 111298 DRWN: MKIPPER CHKD: MKIPPER REV APPR: FSMITH	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION UNITS		SCALE																	
					MM	INCH	MM/IN	NTS																			
		= 0			4 PLACES	±	±	DRWN BY		DATE		FRICITION LOCK HEADER ASY .100 CL BENT SQ. PINS 7478 SERIES															
		= 0			3 PLACES	±	± .010	GUZIC		1987/07/30																	
		= 0			2 PLACES	± 0.25	± .015	CHK'D BY		DATE										PRODUCT CUSTOMER DRAWING							
		= 0			1 PLACES	± 0.38	±	PATEL		1987/07/30																	
		= 0			0 PLACES	±	±	APPR BY		DATE		SERIES		MATERIAL NUMBER				CUSTOMER									
		= 0			ANGULAR TOL ± 1/2			DRAWING SIZE		THIRD ANGLE PROJECTION		7478		SEE CHART				GENERAL MARKET									
		= 0			DRAFT WHERE APPLICABLE WITHIN DIMENSIONS			C				DOCUMENT NUMBER		PSD				DOC PART		SHEET NUMBER							
		= 0			AA2							SDA-7478						000		5 OF 5							

RELEASE STATUS		P1	RELEASE DATE		28.04.2017	22:16:23	12		11		10		9		8		7		6		5		4		3		2		1	
----------------	--	----	--------------	--	------------	----------	----	--	----	--	----	--	---	--	---	--	---	--	---	--	---	--	---	--	---	--	---	--	---	--