PD -95199

International
IOR Rectifier

IRF7341PbF

HEXFET® Power MOSFET

- Generation V Technology
- Ultra Low On-Resistance
- Dual N-Channel Mosfet
- Surface Mount
- Available in Tape & Reel
- Dynamic dv/dt Rating
- Fast Switching
- Lead-Free



Top View

V_{DSS} = 55V

$R_{DS(on)}$ = 0.050Ω


SO-8

Description

Fifth Generation HEXFETs from International Rectifier utilize advanced processing techniques to achieve extremely low on-resistance per silicon area. This benefit, combined with the fast switching speed and ruggedized device design that HEXFET Power MOSFETs are well known for, provides the designer with an extremely efficient and reliable device for use in a wide variety of applications.

The SO-8 has been modified through a customized leadframe for enhanced thermal characteristics and multiple-die capability making it ideal in a variety of power applications. With these improvements, multiple devices can be used in an application with dramatically reduced board space. The package is designed for vapor phase, infra red, or wave soldering techniques. Power dissipation of greater than 0.8W is possible in a typical PCB mount application.

Absolute Maximum Ratings

	Parameter	Max.	Units
V_{DS}	Drain- Source Voltage	55	V
I_D @ T_C = 25°C	Continuous Drain Current, V_{GS} @ 10V	4.7	A
I_D @ T_C = 70°C	Continuous Drain Current, V_{GS} @ 10V	3.8	
I_{DM}	Pulsed Drain Current ①	38	
P_D @T_C = 25°C	Power Dissipation	2.0	W
P_D @T_C = 70°C	Power Dissipation	1.3	
	Linear Derating Factor	0.016	W/°C
V_{GS}	Gate-to-Source Voltage	± 20	V
V_{GSM}	Gate-to-Source Voltage Single Pulse tp<10µs	30	V
E_{AS}	Single Pulse Avalanche Energy②	72	
dv/dt	Peak Diode Recovery dv/dt ③	5.0	V/ns
T_J, T_{STG}	Junction and Storage Temperature Range	-55 to + 150	°C

Thermal Resistance

	Parameter	Typ.	Max.	Units
$R_{\theta JA}$	Maximum Junction-to-Ambient⑤	——	62.5	°C/W

11/9/04

Electrical Characteristics @ T_J = 25°C (unless otherwise specified)

	Parameter	Min.	Typ.	Max.	Units	Conditions
$V_{(BR)DSS}$	Drain-to-Source Breakdown Voltage	55	—	—	V	V_{GS} = 0V, I_D = 250µA
$\Delta V_{(BR)DSS}/\Delta T_J$	Breakdown Voltage Temp. Coefficient	—	0.059	—	V/°C	Reference to 25°C, I_D = 1mA
$R_{DS(on)}$	Static Drain-to-Source On-Resistance	—	0.043	0.050	Ω	V_{GS} = 10V, I_D = 4.7A ④
		—	0.056	0.065		V_{GS} = 4.5V, I_D = 3.8A ④
$V_{GS(th)}$	Gate Threshold Voltage	1.0	—	—	V	V_{DS} = V_{GS}, I_D = 250µA
g_{fs}	Forward Transconductance	7.9	—	—	S	V_{DS} = 10V, I_D = 4.5A
I_{DSS}	Drain-to-Source Leakage Current	—	—	2.0	µA	V_{DS} = 55V, V_{GS} = 0V
		—	—	25		V_{DS} = 55V, V_{GS} = 0V, T_J = 55°C
I_{GSS}	Gate-to-Source Forward Leakage	—	—	-100	nA	V_{GS} = -20V
	Gate-to-Source Reverse Leakage	—	—	100		V_{GS} = 20V
Q_g	Total Gate Charge	—	24	36	nC	I_D = 4.5A
Q_{gs}	Gate-to-Source Charge	—	2.3	3.4		V_{DS} = 44V
Q_{gd}	Gate-to-Drain ("Miller") Charge	—	7.0	10		V_{GS} = 10V, See Fig. 10 ④
$t_{d(on)}$	Turn-On Delay Time	—	8.3	12	ns	V_{DD} = 28V
t_r	Rise Time	—	3.2	4.8		I_D = 1.0A
$t_{d(off)}$	Turn-Off Delay Time	—	32	48		R_G = 6.0Ω
t_f	Fall Time	—	13	20		R_D = 16Ω, ④
C_{iss}	Input Capacitance	—	740	—	pF	V_{GS} = 0V
C_{oss}	Output Capacitance	—	190	—		V_{DS} = 25V
C_{rss}	Reverse Transfer Capacitance	—	71	—		f = 1.0MHz, See Fig. 9

Source-Drain Ratings and Characteristics

	Parameter	Min.	Typ.	Max.	Units	Conditions
I_S	Continuous Source Current (Body Diode)	—	—	2.0	A	MOSFET symbol showing the integral reverse p-n junction diode.
I_{SM}	Pulsed Source Current (Body Diode) ①	—	—	38		
V_{SD}	Diode Forward Voltage	—	—	1.2	V	T_J = 25°C, I_S = 2.0A, V_{GS} = 0V ③
t_{rr}	Reverse Recovery Time	—	60	90	ns	T_J = 25°C, I_F = 2.0A
Q_{rr}	Reverse RecoveryCharge	—	120	170	nC	di/dt = -100A/µs ③



Notes:

① Repetitive rating; pulse width limited by max. junction temperature. (See fig. 11)

② Starting T_J = 25°C, L = 6.5mH R_G = 25Ω, I_{AS} = 4.7A. (See Figure 8)

③ $I_{SD} \leq$ 4.7A, di/dt ≤ 220A/µs, $V_{DD} \leq V_{(BR)DSS}$, $T_J \leq$ 150°C

④ Pulse width ≤ 300µs; duty cycle ≤ 2%.

⑤ When mounted on 1 inch square copper board, t<10 sec



Fig 1. Typical Output Characteristics



Fig 2. Typical Output Characteristics



Fig 3. Typical Transfer Characteristics



Fig 4. Typical Source-Drain Diode Forward Voltage



Fig 5. Normalized On-Resistance Vs. Temperature



Fig 6. Typical On-Resistance Vs. Drain Current



Fig 7. Typical On-Resistance Vs. Gate Voltage



Fig 8. Maximum Avalanche Energy Vs. Drain Current



Fig 9. Typical Capacitance Vs. Drain-to-Source Voltage



Fig 10. Typical Gate Charge Vs. Gate-to-Source Voltage



Fig 11. Maximum Effective Transient Thermal Impedance, Junction-to-Ambient

SO-8 Package Outline

Dimensions are shown in milimeters (inches)







DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	.0532	.0688	1.35	1.75
A1	.0040	.0098	0.10	0.25
b	.013	.020	0.33	0.51
c	.0075	.0098	0.19	0.25
D	.189	.1968	4.80	5.00
E	.1497	.1574	3.80	4.00
e	.050 BASIC		1.27 BASIC	
e1	.025 BASIC		0.635 BASIC	
H	.2284	.2440	5.80	6.20
K	.0099	.0196	0.25	0.50
L	.016	.050	0.40	1.27
y	0°	8°	0°	8°

NOTES:

1. DIMENSIONING & TOLERANCING PER ASME Y14.5M-1994.
2. CONTROLLING DIMENSION: MILLIMETER
3. DIMENSIONS ARE SHOWN IN MILLIMETERS (INCHES).
4. OUTLINE CONFORMS TO JEDEC OUTLINE MS-012AA.

5 DIMENSION DOES NOT INCLUDE MOLD PROTRUSIONS. MOLD PROTRUSIONS NOT TO EXCEED 0.15 (.006).

6 DIMENSION DOES NOT INCLUDE MOLD PROTRUSIONS. MOLD PROTRUSIONS NOT TO EXCEED 0.25 (.010).

7 DIMENSION IS THE LENGTH OF LEAD FOR SOLDERING TO A SUBSTRATE.

FOOTPRINT



SO-8 Part Marking Information (Lead-Free)

EXAMPLE: THIS IS AN IRF7101 (MOSFET)



SO-8 Tape and Reel

Dimensions are shown in milimeters (inches)



NOTES:
1. CONTROLLING DIMENSION : MILLIMETER.
2. ALL DIMENSIONS ARE SHOWN IN MILLIMETERS(INCHES).
3. OUTLINE CONFORMS TO EIA-481 & EIA-541.



NOTES :
1. CONTROLLING DIMENSION : MILLIMETER.
2. OUTLINE CONFORMS TO EIA-481 & EIA-541.

Data and specifications subject to change without notice.
This product has been designed and qualified for the Consumer market.
Qualifications Standards can be found on IR's Web site.

International
IOR Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
TAC Fax: (310) 252-7903
Visit us at www.irf.com for sales contact information.11/04