




SMT GaAs MMIC x2 ACTIVE FREQUENCY MULTIPLIER, 8 - 22 GHz OUTPUT

Typical Applications

The HMC573LC3B is suitable for:

- Clock Generation Applications:
 SONET OC-192 & SDH STM-64
- Point-to-Point & VSAT Radios
- Test Instrumentation
- Military & Space

Functional Diagram



Features

High Output Power: +12 dBm

Low Input Power Drive: 0 to +6 dBm
Fo Isolation: >20 dBc @ Fout= 16 GHz
100 KHz SSB Phase Noise: -134 dBc/Hz

Single Supply: +5V@ 92 mA

RoHS Compliant 3x3 mm SMT Package

General Description

The HMC573LC3B is a x2 active broadband frequency multiplier utilizing GaAs PHEMT technology in a leadless RoHS compliant SMT package. When driven by a +5 dBm signal, the multiplier provides +12 dBm typical output power from 8 to 22 GHz. The Fo and 3Fo isolations are >20 dBc and >25 dBc respectively at 16 GHz. The HMC573LC3B is ideal for use in LO multiplier chains for Pt-to-Pt & VSAT Radios yielding reduced parts count vs. traditional approaches. The low additive SSB Phase Noise of -134 dBc/Hz at 100 kHz offset helps maintain good system noise performance. The RoHS packaged HMC573LC3B eliminates the need for wire bonding, and allows the use of surface mount manufacturing techniques.

Electrical Specifications, $T_{\Delta} = +25^{\circ}\text{C}$, Vdd = +5V, 5 dBm Drive Level

Parameter	Min.	Тур.	Max.	Units
Frequency Range, Input		4 - 11		GHz
Frequency Range, Output	8 - 22 GHz		GHz	
Output Power	9	12		dBm
Fo Isolation (with respect to output level)		20		dBc
3Fo Isolation (with respect to output level)		25		dBc
4Fo Isolation (with respect to output level)	15		dBc	
Input Return Loss		10		dB
Output Return Loss		10		dB
SSB Phase Noise (100 kHz Offset)		-134		dBc/Hz
Supply Current (ldd) (Vdd = 5V, Vgg = -1.25V Typ.)		92		mA

^{*}Adjust Vgg between -1.5 and \sim 1.1V to achieve Idd = 92 mA

HMC573* PRODUCT PAGE QUICK LINKS

Last Content Update: 02/23/2017

COMPARABLE PARTS -

View a parametric search of comparable parts.

EVALUATION KITS

• HMC573LC3B Evaluation Board

DOCUMENTATION

Data Sheet

• HMC573 Data Sheet

TOOLS AND SIMULATIONS

• HMC573 S-Parameter

REFERENCE MATERIALS 🖵

Quality Documentation

- Package/Assembly Qualification Test Report: LC3, LC3B, LC3C (QTR: 2014-00376 REV: 01)
- Semiconductor Qualification Test Report: PHEMT-F (QTR: 2013-00269)

DESIGN RESOURCES

- HMC573 Material Declaration
- PCN-PDN Information
- · Quality And Reliability
- Symbols and Footprints

DISCUSSIONS

View all HMC573 EngineerZone Discussions.

SAMPLE AND BUY 🖵

Visit the product page to see pricing options.

TECHNICAL SUPPORT

Submit a technical question or find your regional support number.

DOCUMENT FEEDBACK \Box

Submit feedback for this data sheet.


This page is dynamically generated by Analog Devices, Inc., and inserted into this data sheet. A dynamic change to the content on this page will not trigger a change to either the revision number or the content of the product data sheet. This dynamic page may be frequently modified.






SMT GaAs MMIC x2 ACTIVE FREQUENCY MULTIPLIER, 8 - 22 GHz OUTPUT


Output Power vs. Temperature @ 5 dBm Drive Level




Output Power vs. Drive Level




Output Power vs. Supply Voltage @ 5 dBm Drive Level




Isolation @ 5 dBm Drive Level



Output Power vs. Input Power



Supply Current vs. Input Power









SMT GaAs MMIC x2 ACTIVE FREQUENCY MULTIPLIER, 8 - 22 GHz OUTPUT

Input Return Loss vs. Temperature



Output Return Loss vs. Temperature







SMT GaAs MMIC x2 ACTIVE FREQUENCY MULTIPLIER, 8 - 22 GHz OUTPUT

Absolute Maximum Ratings

RF Input (Vdd = +5V)	+10 dBm	
Supply Voltage (Vdd)	+6.0 Vdc	
Channel Temperature	175 °C	
Continuous Pdiss (T= 85 °C) (derate 8.0 mW/°C above 85 °C)	719 mW	
Thermal Resistance (channel to ground paddle)	125 °C/W	
Storage Temperature	-65 to +150 °C	
Operating Temperature	-40 to +85 °C	
ESD Sensitivity (HBM)	Class 1A	

Typical Supply Current vs. Vdd

Vdd (Vdc)	Idd (mA)
4.5	90
5.0	92
5.5	94


Note:


Multiplier will operate over full voltage range shown above.



ELECTROSTATIC SENSITIVE DEVICE OBSERVE HANDLING PRECAUTIONS

Outline Drawing





NOTES:

- 1. PACKAGE BODY MATERIAL: ALUMINA
- 2. LEAD AND GROUND PADDLE PLATING: 30-80 MICROINCHES GOLD OVER 50 MICROINCHES MINIMUM NICKEL.
- 3. DIMENSIONS ARE IN INCHES [MILLIMETERS].
- 4. LEAD SPACING TOLERANCE IS NON-CUMULATIVE
- 5. PACKAGE WARP SHALL NOT EXCEED 0.05mm DATUM -C-
- 6. ALL GROUND LEADS AND GROUND PADDLE MUST BE SOLDERED TO PCB RF GROUND.

Package Information

Pa	art Number	Package Body Material	Lead Finish	MSL Rating	Package Marking [2]
HM	1C573LC3B	Alumina, White	Gold over Nickel	MSL3 ^[1]	H573 XXXX

^[1] Max peak reflow temperature of 260 °C

^{[2] 4-}Digit lot number XXXX





SMT GaAs MMIC x2 ACTIVE FREQUENCY MULTIPLIER, 8 - 22 GHz OUTPUT

Pin Description

Pin Number	Function	Description	Interface Schematic
1, 3, 7, 9	GND	Package bottom must also be connected to RF/DC ground.	GND =
2	RFIN	Pin is AC coupled and matched to 50 Ohms.	RFIN ○── ├──
4 - 6, 11	N/C	These pins are internally not connected; however, this product was specified with these pins connected to RF/DC ground.	
8	RFOUT	Pin is AC coupled and matched to 50 Ohms.	— —○ RFOUT
10	Vdd	Supply voltage 5V \pm 0.5V. External bypass capacitors of 100 pF, 1,000 pF and 2.2 μ F are required.	Vdd
12 Vgg		Gate control for amplifier. Adjust to achieve Idd of 92 mA. Please follow "MMIC Amplifier Biasing Procedure" Application note.	Vgg O

Application Circuit


Component	Value		J	3 \Diamond	(⊋ J5	
C1, C2	100 pF						
C3, C4	1,000 pF	C1 C3	c_5 \perp			C2	C4 \(\preccept{C6} \)
C5, C6	2.2 μF						
			1	2		10	1
				۷gç	g Vd	d	
		0	2	ı.		DEOUT	8
		J1	RF		1C573LC	RFOUT 3B	J2
					1,3	,7,9	,
				,	ل لے 4ر		





SMT GaAs MMIC x2 ACTIVE FREQUENCY MULTIPLIER, 8 - 22 GHz OUTPUT

Evaluation PCB



List of Materials for Evaluation PCB 115739 [1]

Item	Description
J1, J2 PCB Mount SRI K Connector	
J3 - J5	DC Pin
C1, C2	100 pF Capacitor, 0402 Pkg.
C3, C4	1,000 pF Capacitor, 0603 Pkg.
C5, C6	2.2 µF Tantalum Capacitor
U1	HMC573LC3B x2 Active Multiplier
PCB [2]	115864 Eval Board

^[1] Reference this number when ordering complete evaluation PCB

[2] Circuit Board Material: Rogers 4350

The circuit board used in the final application should be generated with proper RF circuit design techniques. Signal lines should have 50 ohm impedance while the package ground leads and exposed paddle should be connected directly to the ground plane similar to that shown. A sufficient number of via holes should be used to connect the top and bottom ground planes. The evaluation circuit board shown is available from Hittite upon request.