

Audio Connector, Plug, 6.3 mm, 2-pole, solder terminal, insulated, angled



Description

- Solder terminal:
for cable mounting
- Audio entrances and exits
- Data and Signal transfer
- Audio Plug: 2-pole, insulated, angled

References

Alternative: Housing shielded 4833.1200


Weblinks

pdf-datasheet, html-datasheet, General Product Information, RoHS, CHINA-RoHS, REACH, Mating Connectors, e-Shop, SCHURTER-Stock-Check, Distributor-Stock-Check

Technical Data

Diameter	6.3 mm	Allowable Operation Temp.	-20 °C to 70 °C
Number of Poles	2-pole	Terminal	solder terminal nickel-plated
Ratings DC	1 A / 30 VDC	Housing	insulated
Ratings AC	1 A / 30 VAC	Style	angled
Dielectric Strength	500 VDC	Lifetime	5000 Insertions
Insulation Resistance	> 50 MΩ @ 500 VDC		

Dimensions



Cable diameter max. 8.0 mm

All Variants

Product group	Diameter [mm]	Number of Poles	Terminal	Order Number
Audio Plug/Sockets	6.3	2-pole	solder terminal	4833.1220

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging unit 500 Pcs

Mating Outlets/Connectors

Category / Description



[Audio Plug/Sockets Overview complete](#)

4833, solder terminal, screened, 2-pole, Audio Plug/Sockets, 6.3 mm	4833.2200
4833, PCB terminals, screened, 2-pole, Audio Plug/Sockets, 6.3 mm	4833.2220
4833, PCB terminals, insulated, 2-pole, Audio Plug/Sockets, 6.3 mm	4833.2230
4833, solder terminal, insulated, 2-pole, Audio Plug/Sockets, 6.3 mm	4833.3200

[Audio Plug/Sockets further types to 4833 Audio-Stecker, D=6,3mm](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schurter:](#)

[4833.122](#)