



DESCRIPTION: HIGH DENSITY .125" FOOTPRINT FEMALE



#### MATERIALS:

INSULATOR: NYLON 9T, UL94V-0 – 260°C PROCESS TEMP.  
CHEMICAL RESISTANCE, COLOR BLACK

SHELL: STEEL, NICKEL PLATED

CONTACT: PHOSPHOR BRONZE  
GOLD FLASH IN MATING AREA  
TIN PLATING ON TAIL ENDS

RoHS COMPLIANT

#### ELECTRICAL:

CURRENT RATING: 2 AMPERES

DIELECTRIC WITHSTANDING VOLTAGE: 1000VAC rms AT SEA LEVEL

INSULATION RESISTANCE: 5000 MEGOHMS MIN.

CONTACT RESISTANCE: 10 MILLIOHMS MAX.

WORKING TEMPERATURE: -55° TO +125° C

SERIES 193-015-213RXX1

NUMBER OF CONTACTS 15

GENDER

2 = FEMALE (NO GROUND INDENTS)

PC MOUNT

3 = NICKEL SHELL

HARDWARE OPTIONS:

53 = 4-40 INSERT WITH BOARD LOCKS

56 = 4-40 STANOFFS WITH BOARD LOCKS

NUMBER OF CONTACTS	"A" Inch (mm)	"B" Inch (mm)	"C" Inch (mm)	"E" Inch (mm)	"F" Inch (mm)
15	1.214(30.84)	.984 (24.99)	.642 (16.30)	.405 (10.29)	.090 (2.29)



THESE DRAWINGS AND SPECIFICATIONS  
ARE THE PROPERTY OF NorComp AND  
SHALL NOT BE REPRODUCED, COPIED  
OR USED AS THE BASIS FOR THE  
MANUFACTURE OR SALE OF APPARATUS  
WITHOUT WRITTEN PERMISSION.

DRAWN:  
PAM JENKINS

DATE:  
9-15-05

CHECKED:  
\_\_\_\_\_

DATE:  
\_\_\_\_\_

SCALE: 1 SHEET 1 OF 1 REV 1

DWG NO.  
193-015-213RXX1

# NorComp

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[193-015-213R561](#)