


SURFACE MOUNT LED LAMP

Bi-Color Right Angle

PACKAGE DIMENSIONS




NOTE:
Dimensions are in inches (mm).

AllnGaP Red / AllnGaP Green

QTLP610C-RAG

FEATURES

- Ultra-miniature
- Water clear optics
- Moisture-proof packaging
- Available in 0.315" (8mm) width tape on 7" (178mm) diameter
- Compatible with IR and vapor phase reflow solder processes



DESCRIPTION

This bi-color surface mount lamp is designed to fit industry standard profile and footprint. The low profile, right angle mounting is ideal for side and multicolor illuminations.

ABSOLUTE MAXIMUM RATINGS (T_A = 25°C unless otherwise specified)

Parameter	QTLP610C-RAG AllnGaP Red / AllnGaP Green	Units
Continuous Forward Current - I _F	30/30	mA
Peak Forward Current - I _F (f = 1.0 KHz, Duty Factor = 1/10)	160/160	mA
Reverse Voltage - V _R (I _R = 10 µA)	5/5	V
Power Dissipation - P _D	60/60	mW
Operating Temperature - T _{OPR}	-40 to +85	°C
Storage Temperature - T _{STG}	-40 to +100	°C
Lead Soldering Time - T _{SOL}	260 for 5 sec	°C

AllnGaP Red / AllnGaP Green

QTLP610C-RAG

ELECTRICAL / OPTICAL CHARACTERISTICS (T_A = 25°C)

Part Number	QTLP610C-RAG AllnGaP Red / AllnGaP Green	Condition
Luminous Intensity (mcd)		I _F = 20 mA
Minimum	20/15	
Typical	45/25	
Forward Voltage (V)		I _F = 20 mA
Maximum	2.4/2.4	
Typical	2.0/2.0	
Wavelength (nm)		I _F = 20 mA
Peak	630/575	
Dominant	624/573	
Spectral Line Half Width (nm)	20/20	I _F = 20 mA
Viewing Angle (°)	120/120	I _F = 20 mA

TYPICAL PERFORMANCE CURVES




Fig. 1 Forward Current vs. Forward Voltage







Fig. 2 Relative Luminous Intensity vs. DC Forward Current


TYPICAL PERFORMANCE CURVES




AllnGaP Red / AllnGaP Green

QTLP610C-RAG

RECOMMENDED PRINTED CIRCUIT BOARD PATTERN



RECOMMENDED IR REFLOW SOLDERING PROFILE





SURFACE MOUNT LED LAMP

Bi-Color Right Angle

AllnGaP Red / AllnGaP Green

QTLP610C-RAG



DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.