





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/8/05	
A		REVISED DIM.	8/11/11	



PCB LAYOUT



SPECIFICATIONS:

Material: Insulator: Nylon, rated UL 94V-2
Insulator color: Ivory
Contacts: Brass
Plating: Tin over Copper underplate overall
Electrical: Operating voltage: 250 VAC max
Current rating: 3 Amps max
Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Operating temperature: -25°C to +85°C
Environmental: Lead free, RoHS compliant

Positions: 2 thru 20
A = .100 [2.54] x No. of Positions
B = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES .X ± .10 ØXX ± .10 .XX ± .020 ØXXX ± .015 .XXX ± .015 ØXXX ± .010				APPROVALS			
DRAWN	SS	4/8/05		DATE			
CHECKED							
APPROVED							
ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710				TITLE .100 [2.54] LOCKING HEADER STRAIGHT, PCB			
SIZE X				PART NO. LHA-XX-TS			
REF: S00016T				SCALE: NTS			
SHEET 1 OF 1				REV. A			