


DURACELL®



SIZE LR44

Alkaline Manganese Dioxide Battery



SPECIFICATIONS

Min. No Load Voltage	1.5V
Min. On Load Voltage	1.42V on 50 Ω at 300ms
Rated Capacity	105mAh on 6.8k Ω to 0.8V
Min. Life	400Hrs on 6.8k Ω to 1.2V
Volume	0.56 cm ³
Weight	1.9 g



DURACELL Batteries.

Issue 61

To be read in conjunction with the General Information module
In line with its continuing development programme, Duracell reserves the right to alter specifications without prior notice