



HBL5869VY -- Valise Connector Body



Product Specifications

Product Type	 Connectors
Body Style	Straight
Standard	NEMA
Amperage	15A
Voltage	125V
Poles and Wires	2 Pole, 2 Wire Non-Grounding
Wiring Method	Back Wire
Hospital Grade ?	No
Plug/Connector Grade	Valise
Color	 Yellow
NEMA No.	1-15R
Cord Dia.	.218-.385" (5.5-9.8)

Description	Straight Blade Connector
Type	2 Pole, 2 Wire, Non Grounding
Rating	15A, 125V
Certification	UL Listed to UL498 File E1706, CSA Certified to C22.2 No. 42 File 280
IP Suitability	IP20
Housing Material	Nylon
Cord Clamp Material	Nylon
Terminal Screw Material	#8-32 Steel (copper or nickel finish)
Wire Clamps Material	0.062" (1.6) Steel - Ni Plated
Cable Inserts Material	Poly Phenylene Oxide
Body Holding Screws	Steel Multiple Drive
Power Contacts Material	.040" (1.0) Copper Alloy
Dielectric Voltage	Withstands 2,000V minimum.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%..
Terminal Identification	Terminals identified in accordance with UL498 (Brass, White, Green).
Terminal Accommodation	#18-#14 AWG copper stranded or solid conductor only.
Product Identification	Ratings are a permanent part of the device.
Flammability	UL 94 HB or better.
Operating Temperatures	Maximum continuous 75°C, minimum -40°C (w/o impact).
M Drawings	Click here for M-Drawing
Catalog Page	Click here for catalog page A4
Brochures	Click here for product brochure
Hubbellnet	Click here for Hubbellnet
Catalog Section	Click here for Section-A
UPC Number	78358501323
Weight in LBs	0.15



Hubbell Incorporated (Delaware)
185 Plains Road
Milford, CT 06460-2420
Ph: (203) 882-4800
Fax: (800) 255-1031

