

NOTES:

1. MATERIAL AND FINISH:
HOUSING, SHELL - BRASS, NICKEL PLATING
CONTACT - PHOSPHOR BRONZE, GOLD PLATING
INSULATOR - PTFE, NATURAL


2. ELECTRICAL:
A. IMPEDANCE:50 OHM
B. FREQUENCY RANGE: DC-11 GHz
C. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS. MIN.


3. MECHANICAL:
A. DURABILITY:500 CYCLES MIN.
B. TEMPERATURE RANGE: -40°C TO +85°C

THIRD ANGLE PROJ. 

REVISIONS				
REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	27-May-02	-----	SH
B	ADD SHEET 2	10-Apr-14	49976	SH

SCALE 1.500





CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL	DRAWN SUNDE	DATE 09-Apr-14	TITLE TNC MALE TO N FEMALE ADAPTOR		Amphenol RF www.amphenolrf.com	
	-	ENGINEER TONY	DATE 27-May-02				
	REFERENCE CONNEX P/N: 242131	APPROVED SCOTT	DATE 09-Apr-14	SCALE: 5.0:1.0 SHEET 2 OF 3		DRAWING NO. NF-TM-NT3G-50	
	CONFIGURATION LEVEL:	CAD FILE		DWG SIZE B	REV B	ITEM NO. 03F-02M2-NA-5-F	PART NO. APH-NJ-TNCP
	FINISH						