



Home: PCB Headers >

Part Number: 98629-1112

2.50mm Pitch HDX™ Header, with PCB Mounting Flange, Dual Row, Vertical, 30 Circuits, Red

Image not available

Status:	OBsolete
Replacement:	98462-1112, 98462-1122
Series:	98629
Category:	PCB Headers

[CHECK DISTRIBUTOR INVENTORY](#)[Add to My Parts](#)[Email this page](#)[Go to Part Detail ▾](#)

Series image - Reference only

Mates With Part(s):[98631](#) HDX™ Module Frame with Lever**Product Environmental Compliance**[EU ELV](#):Product not active[EU RoHS](#):Product not active[EU RoHS Phthalates](#):Product not active[China RoHS](#):[REACH SVHC](#):Product not active[Low-Halogen Status](#):Product not active[EU RoHS Certificate of Compliance \(PDF\)](#)[Multiple Part Product Compliance Statements](#)

EU RoHS, REACH SVHC, & Low-Halogen

[Multiple Part Industry Compliance Documents](#)

*IPC 1752A Class C

*IPC 1752A Class D

*Molex Product Compliance Declaration

Application Tooling**FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling[Check our list of old tooling that used to be available for this part](#)Questions on Product Environmental Compliance? Email ProductCompliance@molex.comRequest Molex's CMRT from conflictminerals@molex.com**Part Detail**[COLLAPSE ALL](#)[▼ General](#)

Status	Obsolete
Category	PCB Headers
Series	98629
Application	Power, Wire-to-Board
Product Name	HDX™
UPC	756054552841

[▼ Physical](#)

Breakaway	No
Circuits (Loaded)	30
Circuits (maximum)	30
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	6.830/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.25mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.50mm
Plating min - Mating	1.016µm
Plating min - Termination	3.048µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Through Hole

[▼ Electrical](#)

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	5.0A
Voltage - Maximum	12V

PRODUCTS**QUICK LINKS****RESOURCES****STAY CONNECTED**

Antennas
Application Tooling
Cable Assemblies
Connected Lighting
Connectors
Copper Flex
Electrical Products
Industrial Automation
Membrane Switches
Optical Solutions
Printed Electronic Solutions

Company Information
Contact Molex
Cross-Reference
Koch Industries
Industries
Investor Relations
Literature
Molex Racing
Press Room / Press Releases
Product Index
Sitemap
Terms & Conditions

Supply Chain Transparency
Business Continuity
Compliance
ecocare
Feedback | Help
Jobs
Legal | Trademarks
Mobile Site
Supplier Portal
Privacy Policy
Tradeshows

