

FL IF MEM 2TX-D

Order No.: 2832483



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2832483>

Memory module, 2 port twisted pair module for saving the switch configuration

Commercial data

GTIN (EAN)	 4 017918 974497
sales group	K000
Pack	1 pcs.
Customs tariff	85176200
Catalog page information	Page 187 (AX-2009)

Product notes

WEEE/RoHS-compliant since:
11/27/2007



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Interfaces

Interface	Ethernet 10/100 Base T
No. of ports	2
Type of connection	RJ45 female connector
Transmission physics	Copper

Transmission speed	10/100 MBit/s
Transmission length	100 m

Function

Basic functions	Configuration memory (plug-in)
-----------------	--------------------------------

Supply voltage

Supply voltage	(via head station)
Typical current consumption	10 mA

General data

Weight	70 g
Width	31 mm
Height	78 mm
Depth	72.5 mm
Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 55 °C (no condensation)
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	10 % ... 95 % (no condensation)
Permissible humidity (storage/transport)	10 % ... 95 % (no condensation)
Housing material	PA
Noise emission	EN 61000-6-3/-4
Noise immunity	EN 61000-6-2:2005

Conformity with EMC directives

Developed in acc. with standard	IEC 61000-6.2
Test standard	IEC 61000-4-2 (ESD)
Test result	Criterion B
Test standard	IEC 61000-4-3 (immunity to radiated interference)
Test result	Criterion A
Test standard	IEC 61000-4-4 (burst)
Test result	Criterion A
Test standard	IEC 61000-4-5 (surge)
Test result	Criterion A
Test standard	IEC 61000-4-6 (immunity to conducted interference)
Test result	Criterion A
Test standard	IEC 61000-4-8 (immunity to magnetic fields)

Test result	Criterion A
Test standard	EN 55022 (emitted interference)
Test result	Criterion A

Certificates / Approvals



Certification

ABS, BV, CUL, DNV, GL, LR, UL

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2011 Phoenix Contact
Technical modifications reserved;