





No. of pos.	A ^{-0.76}	B ^{-0.25}	C ^{+0.12 -0.13}	Part NO.
9	31.19	16.46	25.00	FDCNXSTCM39S132X
15	39.52	24.79	33.30	FDCPXSTCM39S132X
25	53.42	38.50	47.04	FDCRXSTCM39S132X
37	69.70	54.96	63.50	FDCSXSTCM39S132X



NOTES:

- METALSHELLS: COPPER ALLOY; min. 320μ" TIN
- INSULATORS: HIGH TEMPERATURE PLASTIC UL 94 V-0, BLACK
- CONTACTS: COPPER ALLOY
PLATING: 30μ" HARD GOLD OVER min. 50μ" NICKEL
CONTACT TAILS PRETINNED
- METAL BRACKET: DIE-CASTING; min. 320μ" TIN over 80μ" NICKEL
- THREADED INSERT: COPPER ALLOY; min. 200μ" TIN over 80μ" NICKEL
- PCB-SNAP: COPPER ALLOY; min. 200μ" TIN over 80μ" NICKEL
PCB-HOLE: $\phi 3.1 \pm 0.1$; PCB THICKNESS 1.6mm
- FIXING-PLATE: HIGH TEMPERATURE PLASTIC UL 94 V-0, BLACK
- P.C.B. HOLE DRILLINGS ON SHEET 2
- CAPACITANCE: 1300pF $\pm 20\%$
- DIELECTRIC WITHSTANDING VOLTAGE: 424 VDC
- MAXIMUM TORQUE VALUE FOR THREAD: 6" LBS
- CONNECTOR IS PART MARKED: PART-NO. CONEC ABC
- = CHECK DIMENSION

Directive 2002/95/EC
RoHS
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	


THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY, WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		


tolerance	dim. in mm
2006	date
drawn	24.03. Lehmenkühler
appd.	24.03. Mickenbecker
norm	DIN 41652
d-old	

scale:	2:1 (5:1)
material:	SEE NOTES
title:	
D-SUB FILTER FEMALE 90°	
9-37pos. 0.318inch	
threaded insert, metal bracket, fixing-plate, clip	
dwg no:	AutoCAD 2006
24K2A771	
part no:	SEE TABLE


9pos.




15pos.



25pos.



37pos.



used for: D-SUB FILTER

APPROVAL # FREIGABE # DEBLOCAGE # AUTOR/ZACON	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTOR/ZACON	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		

tolerance



scale:

2:1

material:

SEE SHEET 1

title:

P.C.B. HOLE DRILLINGS

D-SUB FILTER FEMALE 90° 9-37pos. 0.318inch threaded insert, metal bracket, fixing-plate, clip

dwg no:

AutoCAD 2006

DIN-A

24K2A771

3

part no:

SEE SHEET 1

sh:2/2