

1200 series

Momentary pushbutton switches - round plunger

Distinctive features and specifications

UG1410A



- ❑ Butt action contacts, double break
- ❑ NF (EN 61058-1), UL and CSA approved

ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load :
 - silver contacts (A) : 4A 250VAC - 8A 125VAC - 4A 24VDC - 8A 12VDC
 - silver plated copper contacts (C) : 2A 250VAC - 3A 125VAC - 2A 24VDC - 3A 12VDC
- Initial contact resistance : 10 mΩ
- Insulation resistance : 1.000 MΩ min. at 500VDC
- Dielectric strength :
 - 2.000 Vrms 50 Hz min. between terminals
 - 3.000 Vrms 50 Hz min. between terminals and frame
- Electrical life : 10.000 cycles at full load

MATERIALS

- Case : polyamide
- Plunger : polyamide
- Bushing : brass, nickel plated
- Contacts :
 - A : silver
 - C : copper, silver plated

GENERAL SPECIFICATIONS

- Torque : 1,50 Nm (1.10 Ft.lb) max. applied to nut
- Panel thickness : 5 mm (.196) max.
- Total travel :
 - NO : 4,5 (.177) +/- 0,3 (.011)
 - NC : 3,5 (.137) +/- 0,3 (.011)
- Operating temperature : -20°C to +55°C

AGENCY APPROVALS



EN 61058-1

2A 250VAC or 4A 250VAC, T55/125°C
All models



4A 250VAC - 8A 125VAC
All models function 3 (NO)

Models 1233X209 and 1233X209L are standard marked NF.
To order switches marked NF, UL or CSA, complete appropriate box of ordering format.

ABOUT THIS SERIES

Dimensions : first dimensions are in mm while inches are shown as bracketed numbers.



Sealing boots are available to protect the switches against dust and water. They are presented in section H.



Mounting accessories : standard hardware supplied :

- silver contact models : 1 hex nut U166 and 1 knurled nut U411
- copper contact models : 1 hex nut U42 and 1 knurled nut U411

Standard and special hardware are presented in section I.



Packaging unit : 40 pieces, except model 1200.L (50 pieces).


The company reserves the right to change specifications without notice.

1200 series


Momentary pushbutton switches - round plunger

Solder lug/quick-connect terminals - screw terminals

MODEL
STRUCTURE



- Single pole configurations
- Approved models : see following pages
- Panel cut-out : $\varnothing 12,2$ (.480)



MODEL
STRUCTURE




Plunger height : NO model : 7,50 mm, NC model : 5,80 mm

Solder lug/quick-connect terminals




1212		Normally Closed
1213		Normally Open



Screw terminals




1222		Normally Closed
1223		Normally Open



Normalized quick-connect terminals



1232		Normally Closed
1233		Normally Open



1200 series

Momentary pushbutton switches - round plunger

Plunger height : NO model : 7,50 mm, NC model : 5,80 mm

Straight screw terminals + clamp



1202




Normally Closed

1203



Normally Open

→ Keyway



Right angle screw terminals + clamp




1203-7




Normally Open

→ Keyway



CONTACT MATERIALS




A Silver
C Copper, silver plated

FINISH



LUXE Chrome plated cap nut U117 instead of knurled nut U411

PLUNGER COLOURS



2 : Black - 3 : Green - 6 : Red - 7/1 : White


1200 series

Momentary pushbutton switches - round plunger

OPTIONS



SPECIAL MODELS



X209 NF standard marked - Silver contacts





1233A•X209



Normally open

Replace • with the desired plunger colour.

→ Keyway



X209L NF standard marked - Silver contacts





1233A•X209L



Normally open


Replace • with the desired plunger colour.

→ Keyway



 **NOTE :** Ground connector **U187** compulsory on models X209 and X209L if the panel is not metallic or not connected to ground. Order separately : see section I.

AGENCY APPROVALS



NF All models

UL-CSA All models function 3 (NO), including X209 and X209L

Marking : to order switches marked NF, UL or CSA, complete above box with desired approvals.

1200M/MR series

Robust momentary pushbutton switches - metal plunger

Distinctive features and specifications

UG1410A



❑ Butt action contacts, double break

❑ UL and CSA approved

ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load :
 - silver contacts (A) : 4A 250VAC - 8A 125VAC - 4A 24VDC - 8A 12VDC
 - silver plated copper contacts (C) : 2A 250VAC - 3A 125VAC - 2A 14VDC - 3A 12VDC
- Initial contact resistance : 10 mΩ max.
- Insulation resistance : 1.000 MΩ min. at 500VDC
- Dielectric strength :
 - 2.000 Vrms 50 Hz min. between terminals
 - 3.000 Vrms 50 Hz min. between terminals and frame
- Electrical life : 10.000 cycles at full load

MATERIALS

- Case : polyamide
- Plunger : top chrome plated brass on polyamide base
- Bushing : brass, nickel plated
- Cap nut : brass, chrome plated
- Contacts : **A** : silver
C : copper, silver plated

GENERAL SPECIFICATIONS

- Torque : 1,50 Nm (1.10 Ft.lb) max. applied to nut
- Panel thickness : 4,5 mm (.177) max.
- Total travel :
 - NO : 4,5 mm (.177) +/- 0,3 (.011)
 - NC : 3,5 mm (.137) +/- 0,3 (.011)
- Operating temperature : -20°C to +55°C

AGENCY APPROVALS



4A 250VAC - 8A 125VAC

Availability : approved models are 1213A and 1203A (M or MR)
(model 1223A is only UL approved).

Marking : to order switches marked UL or CSA, complete appropriate box of ordering format.

ABOUT THIS SERIES

Dimensions : first dimensions are in mm while inches are shown as bracketed numbers.



Mounting accessories : standard hardware supplied with all models : 1 hex nut U166 and 1 conic cap nut U1866-6.
Special cap nut U1874 is presented on the following pages.



Packaging unit : 40 pieces


The company reserves the right to change specifications without notice.

1200M/MR series

Robust momentary pushbutton switches - metal plunger


Solder lug/quick-connect terminals - screw terminals

MODEL
STRUCTURE




- Flat or curved plunger
- Panel cut-out $\varnothing 12,2$ (.480)
- Single pole


121.



122.



120.



MODEL
STRUCTURE



Solder lug/quick-connect terminals 6,35 x 0,8 (.250 x .031) → Keyway



Curved plunger Flat plunger

1212MR

1212M






NC

1213MR

1213M



NO



Screw terminals



Curved plunger Flat plunger

1222MR

1222M






NC

1223MR

1223M



NO



Screw terminals + clamp



Curved plunger Flat plunger

1202MR

1202M





NC

1203MR

1203M



NO






1200M/MR series


Robust momentary pushbutton switches - metal plunger

CONTACT MATERIALS



- A Silver
C Copper, silver plated

AGENCY APPROVALS




UL - CSA

Availability : approved models are 1213A and 1203A (M or MR) - model 1223A is only UL approved.

Marking : to order switches marked UL or CSA, complete above box with desired approvals.

SPECIAL CAP NUT

Chrome plated cap nut $\varnothing 16$ (.629), flat and plain.
Can be supplied instead of standard cap nut U1866-6.
Order separately.



U1874

B2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apem:](#)

[12037A2ULCSA](#) [1213C2](#) [1213A2ULCSA](#) [1223A2ULCSA](#) [1233A2X209LULCSA](#) [1233A2X209ULCSA](#) [1202A2](#)
[1202A6](#) [1212A2](#) [1213A2](#) [1222A2](#) [1203A2UL](#) [1212C2](#) [1212C3](#) [1212C6](#) [1212C7/1](#) [1213A2UL](#) [1213C3](#) [1213C6](#)
[1213C7/1](#) [1232A2](#) [1232A6NF](#) [1232AX2119](#) [1232C2](#) [1233A2NF](#) [1233A2X209UL](#) [1233C6](#) [1213MAULCSA](#)
[1203A2ULCSA](#)