

LP11 SERIES PUSHBUTTON SWITCH

ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS




APPLICATIONS / MARKETS




Audio / Visual



Consumer Electronics



Vending Machines



Kiosks



Instrumentation



Medical Equipment

RoHS

SPECIFICATIONS

Electrical Rating: 100mA @ 12VDC
Contact Arrangement: SPST
Electrical Life: 1,000,000 Cycles
Contact Resistance: 200mΩ Max. initial
Insulation Resistance: 100 MΩ Min. @ 500VDC
Dielectric Strength: 500VAC for 1 Minute
Travel: 4.50mm (Momentary)
 3.50mm (Latching)
Actuation Force: 200 gf (Momentary)
 160 gf (Latching)
Operating Temperature: -40°C to 85°C

FEATURES & BENEFITS

- RGB or multiple bi-color illumination options
- Tactile or non tactile feel
- Multiple cap sizes
- Long electrical life
- Latching and momentary functions

PART NUMBER CONFIGURATOR

Series	Function	Circuit	Actuators	Cap	Cap Configuration	LED Color Options*
LP 11	OA EE	1	N T	A B C	S	RR RG RB RY RW BB BW GG GB GW YY YG YB YW WW RGB
LP11	OA - Momentary EE - Latching (Only using N Actuator Type)	1 - SPST	N - Non Tactile T - Tactile	A - 12mm square B - 15mm square C - 17.4mm square	S - Sculptured	RR - Red-Red RG - Red-Green RB - Red-Blue RY - Red-Yellow RW - Red-White BB - Blue-Blue BW - Blue-White GG - Green-Green GB - Green-Blue GW - Green-White YY - Yellow-Yellow YG - Yellow-Green YB - Yellow-Blue YW - Yellow-White WW - White-White RGB - Red-Green-Blue

* Please refer to individual part number drawings for LED specifications.

Specifications subject to change without notice 9.5.2018



E-SWITCH®


www.e-switch.com

800.867.2717


1

ANTI-VANDAL SWITCHES	DETECTOR SWITCHES	DIP SWITCHES	KEYLOCK SWITCHES	NAVIGATION SWITCHES	PUSHBUTTON SWITCHES	ROCKER SWITCHES	ROTARY SWITCHES	SLIDE SWITCHES	SNAP ACTION SWITCHES	TACTILE SWITCHES	TOGGLE SWITCHES	CAP SWITCHES
----------------------	-------------------	--------------	------------------	---------------------	---------------------	-----------------	-----------------	----------------	----------------------	------------------	-----------------	--------------




PCB LAYOUT



PCB LAYOUT



SCHEMATIC




E♦SWITCH®

800.867.2717


2

LP11 SERIES PUSHBUTTON SWITCH




BODY DIMENSIONS MOMENTARY RGB



PCB LAYOUT



SCHEMATIC



OA - MOMENTARY WITH A - 12MM CAP
RGB ILLUMINATION



E-SWITCH®


www.e-switch.com

800.867.2717


3

LP11 SERIES PUSHBUTTON SWITCH




BODY DIMENSIONS LATCHING LED



PCB LAYOUT



SCHEMATIC



EE - LATCHING WITH A - 12MM CAP
LED ILLUMINATION



E-SWITCH®

www.e-switch.com


800.867.2717

4


ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS

LP11 SERIES PUSHBUTTON SWITCH




BODY DIMENSIONS LATCHING RGB



PCB LAYOUT



SCHEMATIC



EE - LATCHING WITH A - 12MM CAP
RGB ILLUMINATION




E-SWITCH®

www.e-switch.com

800.867.2717

5

CAP OPTIONS



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[LP110A1NASRG](#) [LP110A1TBSRG](#) [LP110A1NBSRB](#) [LP110A1TASRB](#) [LP110A1NASBW](#) [LP110A1NBSBW](#)
[LP110A1NBSWW](#) [LP110A1NCSBB](#) [LP110A1NCSBW](#) [LP110A1NCSRW](#) [LP110A1NCSWW](#) [LP110A1NCSYY](#)
[LP110A1TBSWW](#) [LP110A1TCSYY](#) [LP110A1NASRB](#) [LP110A1NASRY](#) [LP110A1NASYG](#) [LP110A1NBSRG](#)
[LP110A1NCSGB](#) [LP110A1NCSRB](#) [LP110A1NCSRG](#) [LP110A1TASRG](#) [LP110A1TBSGG](#) [LP110A1TBSRB](#)
[LP110A1TBSRR](#) [LP110A1TBSYY](#) [LP110A1TCSRB](#) [LP110A1TCSRG](#) [LP110A1NBSRR](#) [LP110A1TCSGB](#)
[LP110A1TXXRG](#) [LP110A1NASRGB](#) [LP110A1NBSRGB](#) [LP110A1NCSRGB](#)