

346 **0%**
MERCURY

SR712SW

Watch Battery OEM

Technical Data Sheet


Specifications

Chemical system	Zinc / Monovalent Silver Oxide, low drain
Nominal Voltage	1,55 V
Capacity	9,5 mAh, Discharge over 47 k Ω at 23 $\pm$ 3 $^{\circ}$ C to 1,2 V
Operating Temperature	0 $^{\circ}$ C – 60 $^{\circ}$ C
Self Discharge	Less than 10% per year at 20 $^{\circ}$ C
Weight	~0,25 g

Dimensions


(according IEC 60086-3)

Diameter	7,90 mm (0,311")
Height	1,25 mm (0,049")



Discharge Curve

Constant Load	47 k Ω
Starting Drain	32.5 μ A
Temperature	23 $\pm$ 3 $^{\circ}$ C



Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative.

Rev. 346MF_OEM.01 01.2011

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Renata:

[346.TS 0% HG](#) [346.MP 0% HG](#)