

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

39-30-1160

Status:

Active

Overview:

Mini-Fit Jr.™ Power Connectors

Description:

Mini-Fit® Jr. Header, Dual Row, Right Angle, with Snap-in Plastic Peg PCB Lock, 16 Circuits, PA Polyamide Nylon 6/6 94V-2, Tin (Sn) Plating



Series

image - Reference only

Documents:

- 3D Model

Packaging Specification PK-5569-002 (PDF)
- Drawing (PDF)

Packaging Specification SPK-5569-NA2 (PDF)
- Product Specification PS-45750-001 (PDF)

Test Summary TS-5556-002 (PDF)
- Product Specification PS-5556-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

5569

Application

Power, Wire-to-Board

Comments

Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 Mini-Fit® Plus HCS Crimp Terminal Crimped to 16 AWG wire., See Molex Product specification PS-5556-001 for additional current de-rating information.

Overview

Mini-Fit Jr.™ Power Connectors

Product Name

Mini-Fit Jr.™

UPC

800753579675

Physical

Breakaway

No

Circuits (Loaded)

16

Circuits (maximum)

16

Color - Resin

Natural

Durability (mating cycles max)

30

First Mate / Last Break

No

Flammability

94V-2

Glow-Wire Compliant

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

Yes

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Nylon

Net Weight

5.658/g

Number of Rows

2

Orientation

Right Angle

PCB Locator

Yes

PCB Retention

Yes

PCB Thickness - Recommended

1.78mm

Packaging Type

Bag

Pitch - Mating Interface

4.20mm

Pitch - Termination Interface

4.20mm

Plating min - Mating

5.080µm

Plating min - Termination

5.080µm

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

5569Series

Mates With

5557 Mini-Fit Jr.™ Receptacle Housing

Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	13A
Voltage - Maximum	600V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	240
Material Info	
Old Part Number	5569-16A2
Reference - Drawing Numbers	
Packaging Specification	PK-5569-002, SPK-5569-NA2
Product Specification	PS-45750-001, PS-5556-001, RPS-5556-004
Sales Drawing	SDA-5569-NA2*-*
Test Summary	TS-5556-002

This document was generated on 01/20/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION