






LOC	DIST	REVISIONS				
		REV	DATE	BY	CHK	APPV
AA	22	A3	REVISED PER ECO-13-014513	03SEP2013	LL	SH

- ⚠ MATERIAL:
HOUSING – PCT POLYESTER, BLACK, UL94V-0.
OVERMOLDED TERMINAL ARRAY – PBT, BROWN.
TERMINALS – 0.33 [.013] THICK PHOS BRONZE
PLATED WITH 1.27um [.000050] MIN THICK
HARD GOLD IN LOCALIZED AREA AND 3.81um
[.000150] MIN THICK MATTE TIN SOLDER
AREA OVER 1.27um [.000050] MIN THICK
NICKEL UNDERPLATE.
SHIELDS – 0.25 [.010] THICK COPPER ALLOY
PLATED WITH 1.27 um [.000050] MINIMUM NICKEL
AND 2.03 um [.000080] MINIMUM HOT TIN DIP
ON PCB GROUND TABS.
- ⚠ JACK CAVITY CONFORMS TO FCC RULES AND
REGULATIONS, PART 68 SUBPART F.
- ⚠ DATE CODE LOCATED ON REAR OF PART
APPROXIMATELY AS SHOWN:
FIRST 2 DIGITS ARE LAST 2 DIGITS OF YEAR,
SECOND 2 DIGITS ARE MANUFACTURING
WORK WEEK,
LAST DIGIT IS DAY OF WEEK, WITH SUNDAY = 1.



PC BOARD LAYOUT VIEWED FROM COMPONENT SIDE

SUGGESTED PANEL CUTOUT DIMENSIONS
SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN VARELA - DOCKS 06/JUN/2005		5569380-1	
				CHK J. WESTMAN 06/JUN/2005		PART NUMBER	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. FLICKINGER 06/JUN/2005		NAME	
		0 PLC ± - 1 PLC ± 0.25[.01] 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-1163-2 APPLICATION SPEC 114-2048		STACKED MODULAR JACK ASSEMBLY, 2 X 1 PORT, 8 POSITION, SHIELDED, PRINTED CIRCUIT BOARD GROUND, CATEGORY 5	
MATERIAL		FINISH		WEIGHT		SIZE	
				-		CAGE CODE	
						DRAWING NO	
						RESTRICTED TO	
						A1 00779	
						C=5569380	
						SCALE	
						4:1	
						SHEET	
						1 OF 1	
						REV	
						A3	