


Data Sheet 2501 Rev.—

Features

- Diffused Junction
- Low Leakage
- Low Cost
- High Surge Current Capability
- Low Cost Construction Utilizing Void-Free Molded Plastic Technique

Mechanical Data

- Case: Molded Plastic
- Terminals: Plated Terminals Solderable per MIL-STD-202, Method 208
- Polarity: Color Ring Denotes Cathode End
- Weight: 1.8 grams (approx.)
- Mounting Position: Any
- Marking: Color Band



Dim	AR		ARS	
	Min	Max	Min	Max
A	0.382(9.70)	0.409(10.4)	0.327(8.30)	0.350(8.90)
B	0.217(5.50)	0.224(5.70)	0.217(5.50)	0.224(5.70)
C	0.236(6.00)	0.252(6.40)	0.236(6.00)	0.252(6.40)
D	0.165(4.20)	0.185(4.70)	0.165(4.20)	0.185(4.70)

All Dimensions in inch(mm)

S Suffix Designates ARS Package
No Suffix Designates AR Package

Maximum Ratings and Electrical Characteristics @ $T_A=25^\circ\text{C}$ unless otherwise specified

Single Phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

Characteristic	Symbol	AR/S 35A	AR/S 35B	AR/S 35D	AR/S 35G	AR/S 35J	AR/S 35K	AR/S 35M	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _{RRM} V _{RWM} V _R	50	100	200	400	600	800	1000	V
RMS Reverse Voltage	V _{R(RMS)}	35	70	140	280	420	560	700	V
Average Rectified Output Current @ $T_c = 150^\circ\text{C}$	I _o				35				A
Non-Repetitive Peak Forward Surge Current 8.3ms Single half sine-wave superimposed on rated load (JEDEC Method) at $T_j = 150^\circ\text{C}$	I _{FSM}				500				A
Forward Voltage @ $I_F = 35\text{A}$	V _{FM}				1.0				V
Peak Reverse Current @ $T_A = 25^\circ\text{C}$ At Rated DC Blocking Voltage @ $T_A = 100^\circ\text{C}$	I _{RM}				5.0 250				µA
Reverse Recovery Time (Note 1)	t _{rr}				3.0				µS
Typical Junction Capacitance (Note 2)	C _j				300				pF
Typical Thermal Resistance Junction to Case (Note 3)	R _{θJC}				1.0				K/W
Operating and Storage Temperature Range	T _J , T _{STG}				-50 to +175				°C
Polarity and Voltage Denotation Color Band		Red	Yellow	Silver	Orange	Green	Blue	Violet	

*Glass passivated forms are available upon request

- Note: 1. Measured with IF = 0.5A, IR = 1.0A, IRR = 0.25A
2. Measured at 1.0 MHz and applied reverse voltage of 4.0V D.C.
3. Thermal Resistance: Junction to case, single side cooled.




Fig. 1 Forward Current Derating Curve




Fig. 2 Typical Forward Characteristics




Fig. 3 Max Non-Repetitive Peak Fwd Surge Current




Fig. 4 Typical Junction Capacitance