


Product: [8421](#) 

Audio & Instrumentation, 25 AWG TC, O/A Braid, CM



Product Description

25 AWG Stranded (7x33) Tinned Copper/Tinned Copper Covered Steel conductor, FPE insulation, tinned copper spiral wrapped shield (85% coverage), PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	Audio Connecting Cable
------------------------	------------------------

Physical Characteristics (Overall)

Conductor			
AWG	Stranding	Material	No. of Coax
25	7x33	TC+TCCS - Tinned Copper (High Conductivity) + Tinned Copper Covered Steel (High Conductivity)	1
Conductor Count:		1	

Insulation	
Material	Nominal Diameter
PE - Polyethylene (Foam)	0.125 in

Outer Shield Material		
Type	Material	Coverage [%]
Spiral Serve / Screen	Tinned Copper (TC)	85%

Outer Jacket Material	
Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.18 in

Electrical Characteristics

Conductor DCR	
Nominal Conductor DCR	
32.27 Ohm/1000ft	

Capacitance	
Nom. Capacitance Conductor to Shield	
16 pF/ft	

Impedance	
Nominal Characteristic Impedance	
80 Ohm	

Current	
Max. Recommended Current [A]	
1.9 Amps per Conductor at 25°C	

Voltage

Non-UL Voltage Rating
300 V RMS

Temperature Range

Non-UL Temp Rating:	80°C
Operating Temp Range:	-20°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	15 lbs/1000ft
Max. Pull Tension:	5 lbs
Min Bend Radius (Overall):	2 in

Standards

CPR Euroclass:	Fca
----------------	-----

Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
8421 060250	Black	Reel	250 ft	612825206538

History

Update and Revision:	Revision Number: 0.257 Revision Date: 06-08-2020
----------------------	--

© 2020 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.