





NOTES:

1. FOR USE WITH RG-178 & 196/U CABLE GROUPS.
2. FOR CABLING INSTRUCTIONS SEE CP-1901.
3. FOR CABLE TRIMMING USE KTJ-222 AND KTD-159.
4. FOR CRIMPING USE DIE KTH-2008.
5. INTERFACE PER MIL-STD-348, FIG. 313-2.
6. FOR USE WITH .130 MAX. PANEL.
7. MATERIALS:
 INSULATORS: TEFLON, ASTM-D-4894
 K-GRIP SLEEVE: COM. BRONZE, ASTM-B-135
 CENTER CONTACT: BER. COPPER, ASTM-B-196
 ALL OTHER METAL PARTS: BRASS, ASTM-B16
8. FINISHES:
 CENTER CONTACT: GOLD PLATE, PER MIL-G-45204
 ALL OTHER METAL PARTS: KINGS TARNISH RESISTANT NICKEL FINISH (TR-5)
9. ELECTRICAL CHARACTERISTICS:
 NOMINAL IMPEDANCE: 50 OHMS
 WORKING VOLTAGE: 500 VRMS
 FREQUENCY RANGE: DC TO 11 GHz



GSD

121-11-9

REVISIONS

ISSUE	CHANGES
1	CN 35774 C REDRAWN KH 10/10/94

KAM3966

SCALE 4:1

APPROX SURFACE AREA

WAS: E-15169-2

USED ON

REF:

JK, PNL, TNC

DRAWN	KH	DATE	10/10/94
DESIGN	JT	DATE	10/11/94
APPR.		DATE	

KINGS
ELECTRONICS CO., INC.
TUCKAHOE, NEW YORK 10707

121-11-9

GSD