

Summer 2009



PIC® Microcontrollers for 8-bit Applications



*A Partner in **Your** Success*

8-bit PIC® Microcontrollers from Microchip

A Partner in Your Success



Microchip Technology Inc is the leader in the 8-bit microcontroller market by continually providing versatile products that are innovative and cost effective. As our customers' needs grow and evolve, Microchip continues to invest significantly in technologies and products that will answer the challenges of today's applications as well

as those into the future. With more than 350 8-bit PIC microcontrollers in the product portfolio, Microchip can provide solutions for a multitude of simple to complex applications that will contribute to your success.

When you purchase a PIC microcontroller, you're buying "more than just an MCU" – you're buying Microchip's expertise in product design, development support and supply management.

Design

Microchip realizes the challenges of the embedded engineer, and designs technology into every product to decrease the susceptibility to Electromagnetic Interference (EMI) and provide the most electrically robust products available in the industry. Defense against EMI also incorporates methods to deal with Electrical Fast Transient (EFT), as well as bursts of Electrostatic Discharge (ESD).

Development

Low-risk development begins with utilizing Microchip's MPLAB Integrated Development Environment as well as inexpensive programmers and development tools. Ease in development is further achieved with C Compiler programming support.

- Order samples at: <http://sample.microchip.com>
- Purchase low-cost 8-bit development kits and download your FREE MPLAB IDE at: www.microchip.com/tools
- FREE compiler download at: www.microchip.com/FREE
- Learn more about specific applications at: www.microchip.com/designcenters

Training & Collateral

To ensure that new and existing PIC microcontroller users are knowledgeable on the latest products and technologies – standard code libraries, reference designs, application notes and seminars are available.

- Find the latest product data sheets, application notes and more at www.microchip.com
- Leverage our huge support ecosystem – internet forums, code examples, application notes, software libraries and contact other developers at: <http://forum.microchip.com>
- Watch educational webinars and other on-line training at: <http://techtrain.microchip.com>
- Regional Training Centers are high tech engineering labs conveniently located worldwide and equipped with the most current embedded control tools, techniques and instructors. Learn more at: www.microchip.com/RTC
- The MASTERS Conference is three days of technical training for embedded systems design engineers. The classes are taught by Microchip engineers and technical experts and include classes for all experience levels. Information and registration at: www.microchip.com/MASTERS

Support

Utilize our worldwide network of associates for sales and 24/7 global technical support for help with your next design. In addition to on-call support, also available are hundreds of dedicated field sales and application engineers located in more than 50 sales offices and through our authorized distributors worldwide. For more information please contact your nearest Microchip sales office listed on the back cover of this guide.

Availability

With shortest lead times in the industry – Microchip's world-class manufacturing and supply chain management help ensure that you have product when you need it.

8-bit PIC® Microcontrollers

Product	Released (R) Not Released (NR)	5 ku Pricing [†]	Pins		Core	Memory					Voltage Range	Operating Speed		LCD Segments	mTouch™		Analog			Digital				Communication						Monitors		SR-Latch	Timer 1 Gate	Packages (Designator)	Special Features			
			Total	I/O		Program	Self-Read	Self-Write	Data RAM (B)	Data EE (B)		Maximum Speed	Internal Oscillator		Module	Channels	8-bit ADC	10-bit ADC	12-bit ADC	Comparators	CCP	ECCP	8-bit Timer	16-bit Timer	AUSART	EUSART	PC™	SPI	Ethernet (MAC/PHY)	FS-USB	ECAN					BOR/PBOR	PLVD	
6-Pin	PIC10F200	R	\$0.41	6	4	BL	0.375 KB 0.25 Kw	-	-	16	-	2V-5.5V	4 MHz	4 MHz	0	-	-	-	-	0	-	-	1	-	-	-	-	-	-	-	-	-	-	-	PDIP (P), 2x3 DFN (MC), SOT-23 (OT)	Smallest form-factor		
	PIC10F202	R	\$0.43	6	4	BL	0.75 KB 0.50 Kw	-	-	24	-	2V-5.5V	4 MHz	4 MHz	0	-	-	-	-	0	-	-	1	-	-	-	-	-	-	-	-	-	-	PDIP (P), 2x3 DFN (MC), SOT-23 (OT)	Smallest form-factor			
	PIC10F204	R	\$0.43	6	4	BL	0.375 KB 0.25 Kw	-	-	16	-	2V-5.5V	4 MHz	4 MHz	0	Comp	1	-	-	1	-	-	1	-	-	-	-	-	-	-	-	-	-	PDIP (P), 2x3 DFN (MC), SOT-23 (OT)	Smallest form-factor			
	PIC10F206	R	\$0.46	6	4	BL	0.75 KB 0.50 Kw	-	-	24	-	2V-5.5V	4 MHz	4 MHz	0	Comp	1	-	-	1	-	-	1	-	-	-	-	-	-	-	-	-	-	PDIP (P), 2x3 DFN (MC), SOT-23 (OT)	Smallest form-factor			
	PIC10F220	R	\$0.46	6	4	BL	0.375 KB 0.25 Kw	-	-	16	-	2V-5.5V	8 MHz	4 MHz, 8 MHz	0	-	-	3	-	0	-	-	1	-	-	-	-	-	-	-	-	-	-	PDIP (P), 2x3 DFN (MC), SOT-23 (OT)	Smallest form-factor			
	PIC10F222	R	\$0.49	6	4	BL	0.75 KB 0.50 Kw	-	-	23	-	2V-5.5V	8 MHz	4 MHz, 8 MHz	0	-	-	3	-	0	-	-	1	-	-	-	-	-	-	-	-	-	-	PDIP (P), 2x3 DFN (MC), SOT-23 (OT)	Smallest form-factor			
8-Pin	PIC12F508	R	\$0.50	8	6	BL	0.75 KB 0.50 Kw	-	-	25	-	2V-5.5V	4 MHz	4 MHz	0	-	-	-	-	0	-	-	1	-	-	-	-	-	-	-	-	-	-	-	PDIP (P), SOIC (SN), MSOP (MS), 2x3 DFN (MC)	-		
	PIC12F509	R	\$0.53	8	6	BL	1.5 KB 1 Kw	-	-	41	-	2V-5.5V	4 MHz	4 MHz	0	-	-	-	-	0	-	-	1	-	-	-	-	-	-	-	-	-	-	-	PDIP (P), SOIC (SN), MSOP (MS), 2x3 DFN (MC)	-		
	PIC12F510	R	\$0.59	8	6	BL	1.5 KB 1 Kw	-	-	38	-	2V-5.5V	8 MHz	4 MHz, 8 MHz	0	Comp	1	3	-	1	-	-	1	-	-	-	-	-	-	-	-	-	-	PDIP (P), SOIC (SN), MSOP (MS), 2x3 DFN (MC)	-			
	PIC12F519	R	\$0.59	8	6	BL	1.5 KB 1 Kw	-	-	41	64	2V-5.5V	8 MHz	4 MHz, 8 MHz	0	-	-	-	-	0	-	-	1	-	-	-	-	-	-	-	-	-	-	-	PDIP (P), SOIC (SN), MSOP (MS), 2x3 DFN (MC)	Lowest cost Data EE		
	PIC12F609	R	\$0.63	8	6	MR	1.75 KB 1 Kw	-	-	64	-	2V-15V	20 MHz	4 MHz, 8 MHz	0	Comp	1	-	-	1	-	-	1	1	-	-	-	-	-	-	-	BOR	-	-	√	PDIP (P), SOIC (SN), MSOP (MS), 4x4 DFN (MD), 3x3 DFN (MF)	-	
	PIC12F615	R	\$0.70	8	6	MR	1.75 KB 1 Kw	-	-	64	-	2V-15V	20 MHz	4 MHz, 8 MHz	0	Comp	1	-	4	-	1	-	1	2	1	-	-	-	-	-	-	BOR	SW ◇	-	√	PDIP (P), SOIC (SN), MSOP (MS), 4x4 DFN (MD), 3x3 DFN (MF)	-	
	PIC12F675	R	\$0.77	8	6	MR	1.75 KB 1 Kw	-	-	64	128	2V-5.5V	20 MHz	4 MHz	0	Comp	1	-	3	-	1	-	-	1	1	-	-	-	-	-	-	BOR	-	-	√	PDIP (P), SOIC (SN), 4x4 DFN (MD)	-	
	PIC12F629	R	\$0.70	8	6	MR	1.75 KB 1 Kw	-	-	64	128	2V-5.5V	20 MHz	4 MHz	0	Comp	1	-	-	1	-	-	1	1	-	-	-	-	-	-	-	BOR	-	-	√	PDIP (P), SOIC (SN), 4x4 DFN (MD)	-	
	PIC12F635	R	\$0.84	8	6	MR	1.75 KB 1 Kw	-	-	64	128	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	Comp	1	-	-	1	-	-	1	1	-	-	-	-	-	-	-	BOR	√	-	√	PDIP (P), SOIC (SN), 4x4 DFN (MD)	Keeloq®	
	PIC12F683	R	\$0.91	8	6	MR	3.5 KB 2 Kw	-	-	128	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	Comp	1	-	3	-	1	1	-	2	1	-	-	-	-	-	-	PBOR	-	-	√	PDIP (P), SOIC (SN), 4x4 DFN (MD)	-	
	14-Pin	PIC16F505	R	\$0.59	14	12	BL	1.5 KB 1 Kw	-	-	72	-	2V-5.5V	20 MHz	4 MHz	0	-	-	-	-	0	-	-	1	-	-	-	-	-	-	-	-	-	-	-	PDIP (P), SOIC (SL), TSSOP (ST)	-	
PIC16F506		R	\$0.63	14	12	BL	1.5 KB 1 Kw	-	-	67	-	2V-5.5V	20 MHz	4/8 MHz	0	Comp	2	4	-	2	-	-	1	-	-	-	-	-	-	-	-	-	-	-	PDIP (P), SOIC (SL), TSSOP (ST)	-		
PIC16F526		R	\$0.67	14	12	BL	1.5 KB 1 Kw	-	-	67	64	2V-5.5V	20 MHz	4/8 MHz	0	Comp	2	4	-	2	-	-	1	-	-	-	-	-	-	-	-	-	-	-	PDIP (P), SOIC (SL), TSSOP (ST)	Lowest cost Data EE		
PIC16F610		R	\$0.72	14	12	MR	1.75 KB 1 Kw	-	-	64	-	2V-15V	20 MHz	4/8 MHz	0	SR Latch	4	-	-	2	-	-	1	1	-	-	-	-	-	-	-	BOR	-	√	√	PDIP (P), SOIC (SL), TSSOP (ST), 4x4 QFN (ML)	-	
PIC16F616		R	\$0.79	14	12	MR	3.5 KB 2 Kw	-	-	128	-	2V-15V	20 MHz	4/8 MHz	0	SR Latch	4	-	8	-	2	-	1	2	1	-	-	-	-	-	-	BOR	SW ◇	√	√	PDIP (P), SOIC (SL), TSSOP (ST), 4x4 QFN (ML)	-	
PIC16F630		R	\$0.91	14	12	MR	1.75 KB 1 Kw	-	-	64	128	2V-5.5V	20 MHz	4 MHz	0	Comp	1	-	-	1	-	-	1	1	-	-	-	-	-	-	-	BOR	-	-	√	PDIP (P), SOIC (SL), TSSOP (ST), 4x4 QFN (ML)	-	
PIC16F636		R	\$0.92	14	12	MR	3.5 KB 2 Kw	-	-	128	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	Comp	2	-	-	2	-	-	1	1	-	-	-	-	-	-	-	BOR	-	-	√	PDIP (P), SOIC (SL), TSSOP (ST), 4x4 QFN (ML)	Keeloq®	
PIC16F676		R	\$0.98	14	12	MR	1.75 KB 1 Kw	-	-	64	128	2V-5.5V	20 MHz	4 MHz	0	Comp	1	-	8	-	1	-	-	1	1	-	-	-	-	-	-	BOR	-	-	√	PDIP (P), SOIC (SL), TSSOP (ST), 4x4 QFN (ML)	-	
PIC16F684		R	\$0.98	14	12	MR	3.5 KB 2 Kw	-	-	128	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	Comp	2	-	8	-	2	-	1	2	1	-	-	-	-	-	-	-	BOR	-	-	√	PDIP (P), SOIC (SL), TSSOP (ST), 4x4 QFN (ML)	-
PIC16F688		R	\$1.04	14	12	MR	7 KB 4 Kw	√	-	256	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	Comp	2	-	8	-	2	-	-	1	1	-	1	-	-	-	-	-	BOR	-	-	√	PDIP (P), SOIC (SL), TSSOP (ST), 4x4 QFN (ML)	-

Products sorted by pin count followed by pricing.

† - Pricing subject to change; please contact your Microchip representative for most current pricing.

◇ - Software PLVD implemented via ADC.

8-bit PIC® Microcontrollers																																								
Product		Released (R) Not Released (NR)	5 ku Pricing¹	Pins		Core	Memory				Voltage Range	Operating Speed		LCD Segments	mTouch™		Analog				Digital				Communication						ECAN	Monitors		SRLatch	Timer 1 Gate	Packages (Designator)	Special Features			
				Total	I/O		Program	Self-Read	Self-Write	Data RAM (B)		Data EE (B)	Maximum Speed		Internal Oscillator	Module	Channels	8-bit ADC	10-bit ADC	12-bit ADC	Comparators	CCP	ECCP	8-bit Timer	16-bit Timer	AUSART	EUSART	I²C™	SPI	Ethernet (MAC/PHY)		FS-USB	BOR/PBOR					PLVD		
18-Pin	PIC16F1826	NR	Call for pricing	18	16	EMR	3.5 KB 2 Kw	√	√	256	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	0	CSM	12	–	12	–	2	–	1	2	1	–	1	1	1	–	–	–	BOR	SW ◊	√	√	PDIP (P), SOIC (SO), SSOP (SS), QFN (ML)	DSM, XLP	18-Pin	
	PIC16F1827	NR	Call for pricing	18	16	EMR	7 KB 4 Kw	√	√	384	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	0	CSM	12	–	12	–	2	2	2	4	1	–	1	2	2	–	–	–	BOR	SW ◊	√	√	PDIP (P), SOIC (SO), SSOP (SS), QFN (ML)	DSM, XLP		
	PIC16F54	R	\$0.39	18	12	BL	0.75 KB 0.50 Kw	–	–	25	–	2V-5.5V	20 MHz	0	0	–	–	–	–	0	–	–	1	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–		
	PIC16F716	R	\$0.77	18	13	MR	3.5 KB 2 Kw	–	–	128	–	2V-5.5V	20 MHz	0	0	–	–	–	4	–	0	–	1	2	1	–	–	–	–	–	–	–	–	–	–	–	–	–		
	PIC16F627A	R	\$1.30	18	16	MR	1.75 KB 1 Kw	–	–	224	128	2V-5.5V	20 MHz	4 MHz, 48 kHz	0	Comp	2	–	–	–	2	1	–	2	1	1	–	–	–	–	–	–	–	–	–	–	–	–		
	PIC16F628A	R	\$1.47	18	16	MR	3.5 KB 2 Kw	–	–	224	128	2V-5.5V	20 MHz	4 MHz, 48 kHz	0	Comp	2	–	–	–	2	1	–	2	1	1	–	–	–	–	–	–	–	–	–	–	–	–		
	PIC16F648A	R	\$1.67	18	16	MR	7 KB 4 Kw	–	–	256	256	2V-5.5V	20 MHz	4 MHz, 48 kHz	0	Comp	2	–	–	–	2	1	–	2	1	1	–	–	–	–	–	–	–	–	–	–	–	–		
	PIC18F1220	R	\$1.96	18	16	PIC18	4 KB 2 Kw	√	√	256	256	2V-5.5V	40 MHz	32 MHz, 31 kHz	0	–	–	–	7	–	0	–	1	1	3	–	1	–	–	–	–	–	–	–	–	–	–	–		–
	PIC18F1230	R	\$2.03	18	16	PIC18	4 KB 2 Kw	√	√	256	128	2V-5.5V	40 MHz	32 MHz, 31 kHz	0	–	–	–	4	–	3	–	–	–	2	–	1	–	–	–	–	–	–	–	–	–	–	–		–
	PIC18F1320	R	\$2.17	18	16	PIC18	8 KB 4 Kw	√	√	256	256	2V-5.5V	40 MHz	32 MHz, 31 kHz	0	–	–	–	7	–	0	–	1	1	3	–	1	–	–	–	–	–	–	–	–	–	–	–		–
PIC18F1330	R	\$2.24	18	16	PIC18	8 KB 4 Kw	√	√	256	128	2V-5.5V	40 MHz	32 MHz, 31 kHz	0	–	–	–	4	–	3	–	–	–	2	–	1	–	–	–	–	–	–	–	–	–	–	–	–	–	
20-Pin	PIC16F631	R	\$0.91	20	18	MR	1.75 KB 1 Kw	√	–	64	128	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	SR Latch	4	–	–	–	2	–	–	1	1	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–
	PIC16F677	R	\$0.99	20	18	MR	3.5 KB 2 Kw	√	–	128	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	SR Latch	4	–	12	–	2	–	–	1	1	–	–	1	1	–	–	–	–	–	–	–	–	–	–	–
	PIC16F687	R	\$1.07	20	18																																			

Products sorted by pin count followed by pricing.
† - Pricing subject to change; please contact your Microchip representative for most current pricing.
◇ - Software PLVD implemented via ADC.

8-bit PIC® Microcontrollers

Product	Released (R) Not Released (NR)	5 ku Pricing [†]	Pins		Core	Memory					Voltage Range	Operating Speed		LCD Segments	mTouch™		Analog					Digital				Communication						Monitors		Timer 1 Gate	Packages (Designator)	Special Features		
			Total	I/O		Program	Self-Read	Self-Write	Data RAM (B)	Data EE (B)		Maximum Speed	Internal Oscillator		Module	Channels	8-bit ADC	10-bit ADC	12-bit ADC	Comparators	CCP	ECCP	8-bit Timer	16-bit Timer	AUSART	EUSART	I²C™	SPI	Ethernet (MAC/PHY)	FS-USB	ECAN	BOR/PBOR	PLVD				SR-Latch	
28-Pin (Cont.)	PIC16F1933	NR	\$1.23	28	25	EMR	7 KB 4 Kw	✓	✓	256	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	60	CSM	8	–	11	–	2	2	3	4	1	–	1	1	1	–	–	–	PBOR	SW ◇	✓	✓	SPDIP (SP), SOIC (SO), SSOP (SS), 6x6 QFN (ML)	XLP
	PIC16F1936	NR	\$1.30	28	25	EMR	14 KB 8 Kw	✓	✓	512	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	60	CSM	8	–	11	–	2	2	3	4	1	–	1	1	1	–	–	–	PBOR	SW ◇	✓	✓	SPDIP (SP), SOIC (SO), SSOP (SS), 6x6 QFN (ML)	XLP
	PIC16F883	R	\$1.37	28	25	MR	7 KB 4 Kw	✓	✓	256	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	SR Latch	4	–	11	–	2	1	1	2	1	–	1	1	1		–	–	BOR	SW ◇	✓	✓	SPDIP (SP), SSOP (SS), SOIC (SO), 6x6 QFN (ML)	–
	PIC16F1938	NR	\$1.37	28	25	EMR	28 KB 16 Kw	✓	✓	1024	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	60	CSM	8	–	11	–	2	2	3	4	1	–	1	1	1	–	–	–	PBOR	SW ◇	✓	✓	SPDIP (SP), SOIC (SO), SSOP (SS), 6x6 QFN (ML)	XLP
	PIC18F23K20	R	\$1.37	28	25	PIC18	8 KB 4 Kw	✓	✓	512	256	1.8V-3.6V	64 MHz	16 MHz, 31 kHz	0	–	–	–	11	–	2	1	1	1	3	–	1	1	1		–	–	BOR	✓	–	–	SPDIP (SP), SSOP (SS), SOIC (SO), 6x6 QFN (ML)	XLP
	PIC18F24J10	R	\$1.44	28	21	PIC18	16 KB 8 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	32 kHz	0	–	–	–	10	–	2	2	–	1	2	–	1	1	1	–	–	–	BOR	–	–	–	SPDIP (SP), SOIC (SO), QFN (ML)	–
	PIC16F886	R	\$1.49	28	25	MR	14 KB 8 Kw	✓	✓	368	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	SR Latch	4	–	11	–	2	1	1	2	1	–	1	1	1		–	–	BOR	SW ◇	✓	✓	SPDIP (SP), SSOP (SS), SOIC (SO), 6x6 QFN (ML)	–
	PIC18F24K20	R	\$1.51	28	25	PIC18	16 KB 8 Kw	✓	✓	768	256	1.8V-3.6V	64 MHz	16 MHz, 31 kHz	0	Comp	2	–	11	–	2	1	1	1	3	–	1	1	1	–	–	–	PBOR	✓	–	–	SPDIP (SP), SSOP (SS), SOIC (SO), 6x6 QFN (ML)	XLP
	PIC18F25J10	R	\$1.58	28	21	PIC18	32 KB 16 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	32 kHz	0	–	–	–	10	–	2	2	–	1	2	–	1	1	1	–	–	–	BOR	–	–	–	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	–
	PIC18F24J11	R	\$1.65	28	21	PIC18	16 KB 8 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	CTMU	10	–	10	–	2	–	2	2	3	–	2	2	2	–	–	–	BOR	SW ◇	–	–	SPDIP (SP), SOIC (SO), QFN (ML)	Peripheral Pin Select, Deep Sleep Mode, XLP
	PIC18F25K20	R	\$1.65	28	25	PIC18	32 KB 16 Kw	✓	✓	1536	256	1.8V-3.6V	64 MHz	16 MHz, 31 kHz	0	Comp	2	–	11	–	2	1	1	1	3	–	1	1	1	–	–	–	PBOR	✓	–	–	SSPDIP (SP), SSOP (SS), SOIC (SO), 6x6 QFN (ML)	XLP
	PIC16F913	R	\$1.72	28	25	MR	7 KB 4 Kw	✓	–	256	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	60	Comp	2	–	5	–	2	1	–	2	1	1	–	1	1		–	–	BOR	✓	–	✓	SPDIP (SP), SSOP (SS), SOIC (SO), 6x6 QFN (ML)	–
	PIC18F25J11	R	\$1.79	28	21	PIC18	32 KB 16 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	CTMU	10	–	10	–	2	–	2	2	3	–	2	2	2	–	–	–	BOR	SW ◇	–	–	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	Peripheral Pin Select, Deep Sleep Mode, XLP
	PIC18F24J50	R	\$1.86	28	22	PIC18	16 KB 8 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	CTMU	10	–	10	–	2	–	2	2	3	–	2	2	2	–	1	–	BOR	SW ◇	–	–	SPDIP (SP), SOIC (SO), QFN (ML)	USB 2.0 (Full Speed), Peripheral Pin Select, Deep Sleep Mode, XLP
	PIC16F916	R	\$1.93	28	25	MR	14 KB 8 Kw	✓	–	352	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	60	Comp	2	–	5	–	2	1	–	2	1	1	–	1	1		–	–	BOR	✓	–	✓	SPDIP (SP), SSOP (SS), SOIC (SO), 6x6 QFN (ML)	–
	PIC18F26K20	R	\$1.93	28	25	PIC18	64 KB 32 Kw	✓	✓	3936	1024	1.8V-3.6V	64 MHz	16 MHz, 31 kHz	0	Comp	2	–	11	–	2	1	1	1	3	–	1	1	1	–	–	–	PBOR	✓	–	–	SPDIP (SP), SSOP (SS), SOIC (SO), 6x6 QFN (ML)	XLP
	PIC18F25J50	R	\$2.00	28	22	PIC18	32 KB 16 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	CTMU	10	–	10	–	2	–	2	2	3	–	2	2	2	–	1	–	BOR	SW ◇	–	–	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	USB 2.0 (Full Speed), Peripheral Pin Select, Deep Sleep Mode, XLP
	PIC18F26J11	R	\$2.07	28	21	PIC18	64 KB 32 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	CTMU	10	–	10	–	2	–	2	2	3	–	2	2	2	–	–	–	BOR	SW ◇	–	–	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	Peripheral Pin Select, Deep Sleep Mode, XLP
	PIC18F2450	R	\$2.23	28	23	PIC18	16 KB 8 Kw	✓	✓	768	–	2V-5.5V	48 MHz	32 kHz	0	–	–	–	10	–	0	1	–	1	2	–	1	–	–	–	1	–	PBOR	SW ◇	–	–	SPDIP (SP), SOIC (SO), QFN (ML)	USB 2.0 (Full Speed)
	PIC18F26J50	R	\$2.28	28	22	PIC18	64 KB 32 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	CTMU	10	–	10	–	2	–	2	2	3	–	2	2	2	–	1	–	BOR	SW ◇	–	–	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	USB 2.0 (Full Speed), Peripheral Pin Select, Deep Sleep Mode, XLP
	PIC18F2550	R	\$3.44	28	24	PIC18	32 KB 16 Kw	✓	✓	2048	256	2V-5.5V	48 MHz	8 MHz, 31 kHz	0	–	–	–	10	–	2	2	–	1	3	–	1	1	1	–	1	–	PBOR	SW ◇	–	–	PDIP (P), SPDIP (SP), SOIC (SO)	USB 2.0 (Full Speed)
	PIC18F2480	R	\$3.72	28	25	PIC18	16 KB 8 Kw	✓	✓	768	256	2V-5.5V	40 MHz	8 MHz, 31 kHz	0	–	–	–	8	–	0	1	0	1	3	0	1	1	1	–	–	1	PBOR	SW ◇	–	–	SPDIP (SP), SOIC (SO), QFN (ML)	CAN 2.0
	PIC18F2553	R	\$4.12	28	24	PIC18	32 KB 16 Kw	✓	✓	2048	256	2V-5.5V	48 MHz	8 MHz, 31 kHz	0	–	–	–	10	2	2	–	1	3	–	1	1	1	–	1	–	PBOR	SW ◇	–	–	SPDIP (SP), SOIC (SO)	USB 2.0 (Full Speed)	
	PIC18F2580	R	\$4.17	28	25	PIC18	32 KB 16 Kw	✓	✓	1536	256	2V-5.5V	40 MHz	8 MHz, 31 kHz	0	–	–	–	8	–	0	1	0	1	3	–	1	1	1	–	–	1	PBOR	SW ◇	–	–	SPDIP (SP), SOIC (SO), QFN (ML)	CAN 2.0
	PIC18F2680	R	\$5.05	28	25	PIC18	64 KB 32 Kw	✓	✓	3328	1024	2V-5.5V	40 MHz	8 MHz, 31 kHz	0	–	–	–	8	–	0	1	0	1	3	–	1	1	1		–	1	PBOR	SW ◇	–	–	28/PDIP 300mil, 28/SOIC 300mil	CAN 2.0

Products sorted by pin count followed by pricing.
† - Pricing subject to change; please contact your Microchip representative for most current pricing.
◇ - Software PLVD implemented via ADC.

8-bit PIC® Microcontrollers

Product	Released (R) Not Released (NR)	5 ku Pricing [†]	Pins		Core	Memory					Voltage Range	Operating Speed		LCD Segments	mTouch™		Analog			Digital				Communication						ECAN	Monitors		SR-Latch	Timer 1 Gate	Packages (Designator)	Special Features		
			Total	I/O		Program	Self-Read	Self-Write	Data RAM (B)	Data EE (B)		Maximum Speed	Internal Oscillator		Module	Channels	8-bit ADC	10-bit ADC	12-bit ADC	Comparators	CCP	ECCP	8-bit Timer	16-bit Timer	AUSART	EUSART	PC™	SPI	Ethernet (MAC/PHY)		FS-USB	BOR/PBOR					PLVD	
40/44-Pin	PIC16F59	R	\$0.85	40	32	BL	3 KB 2 Kw	–	–	134	–	2V-5.5V	20 MHz	0	–	–	–	–	–	0	–	–	1	–	–	–	–	–	–	–	–	–	–	–	PDIP (P), TQFP (PT)	–		
	PIC16F724	R	\$1.40	40	36	MR	7 KB 4 Kw	✓	–	192	–	1.8V-5.5V	20 MHz	16 MHz	0	CSM	16	14	–	–	0	2	–	2	1	1	–	1	1	–	–	–	BOR	SW ◇	–	✓	PDIP (P), TQFP (PT), 8x8 QFN (ML)	XLP
	PIC16F1934	NR	\$1.47	40	36	EMR	7 KB 4 Kw	✓	✓	256	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	96	CSM	16	–	14	–	2	2	3	4	1	–	1	1	1	–	–	–	PBOR	SW ◇	✓	✓	PDIP (P), TQFP (PT), 8x8 QFN (ML)	XLP
	PIC16F727	R	\$1.54	40	36	MR	14 KB 8 Kw	✓	–	368	–	1.8V-5.5V	20 MHz	16 MHz	0	CSM	16	14	–	–	0	2	–	2	1	1	–	1	1	–	–	–	BOR	SW ◇	–	✓	PDIP (P), TQFP (PT), 8x8 QFN (ML)	XLP
	PIC16F1937	NR	\$1.54	40	36	EMR	14 KB 8 Kw	✓	✓	512	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	96	CSM	16	–	14	–	2	2	3	4	1	–	1	1	1	–	–	–	PBOR	SW ◇	✓	✓	PDIP (P), TQFP (PT), 8x8 QFN (ML)	XLP
	PIC16F1939	NR	\$1.61	40	36	EMR	28 KB 16 Kw	✓	✓	1024	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	96	CSM	16	–	14	–	2	2	3	4	1	–	1	1	1	–	–	–	PBOR	SW ◇	✓	✓	PDIP (P), TQFP (PT), 8x8 QFN (ML)	XLP
	PIC16F884	R	\$1.63	40	36	MR	7 KB 4 Kw	✓	✓	256	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	SR Latch	4	–	14	–	2	1	1	2	1	–	1	1	1	–	–	–	BOR	SW ◇	✓	✓	PDIP (P), TQFP (PT), 8x8 QFN (ML)	–
	PIC18F44J10	R	\$1.67	40	32	PIC18	16 KB 8 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	31 kHz	0	–	–	–	13	–	2	1	1	1	2	–	1	2	2	–	–	–	BOR	–	–	–	PDIP (P), TQFP (PT), QFN (ML)	–
	PIC18F43K20	NR	\$1.68	40	36	PIC18	8 KB 4 Kw	✓	✓	512	256	1.8V-3.6V	64 MHz	16 MHz, 31 kHz	0	Comp	2	–	14	–	2	1	1	1	3	–	1	1	1	–	–	–	BOR	✓	–	–	PDIP (P), TQFP (PT), 8x8 QFN (ML)	XLP
	PIC16F887	R	\$1.78	40	36	MR	14 KB 8 Kw	✓	✓	368	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	SR Latch	4	–	14	–	2	1	1	2	1	–	1	1	1	–	–	–	BOR	SW ◇	✓	✓	PDIP (P), TQFP (PT), 8x8 QFN (ML)	–
	PIC18F45J10	R	\$1.81	40	32	PIC18	32 KB 16 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	31 kHz	0	–	–	–	13	–	2	1	1	1	2	–	1	2	2	–	–	–	BOR	–	–	–	PDIP (P), TQFP (PT), QFN (ML)	–
	PIC18F44K20	R	\$1.82	40	36	PIC18	16 KB 8 Kw	✓	✓	768	256	1.8V-3.6V	64 MHz	16 MHz, 31 kHz	0	Comp	2	–	14	–	2	1	1	1	3	–	1	1	1	–	–	–	PBOR	✓	–	–	PDIP (P), TQFP (PT), 8x8 QFN (ML)	XLP
	PIC18F44J11	R	\$1.95	40	34	PIC18	16 KB 8 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	CTMU	13	–	13	–	2	–	2	2	3	–	2	2	2	–	–	–	BOR	SW ◇	–	–	TQFP (PT), QFN (ML)	Peripheral Pin Select, Deep Sleep Mode, XLP
	PIC18F45K20	R	\$1.96	40	36	PIC18	32 KB 16 Kw	✓	✓	1536	256	1.8V-3.6V	64 MHz	16 MHz, 31 kHz	0	Comp	2	–	14	–	2	1	1	1	3	–	1	1	1	–	–	–	PBOR	✓	–	–	PDIP (P), TQFP (PT), 8x8 QFN (ML)	XLP
	PIC16F914	R	\$2.03	40	36	MR	7 KB 4 Kw	✓	–	256	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	96	Comp	2	–	8	–	2	2	–	2	1	1	–	1	1	–	–	–	BOR	✓	–	✓	PDIP (P), TQFP (PT), 8x8 QFN (ML)	–
	PIC18F45J11	R	\$2.09	40	34	PIC18	32 KB 16 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	CTMU	13	–	13	–	2	–	2	2	3	–	2	2	2	–	–	–	BOR	SW ◇	–	–	TQFP (PT), QFN (ML)	Peripheral Pin Select, Deep Sleep Mode, XLP
	PIC18F44J50	R	\$2.16	40	34	PIC18	16 KB 8 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	CTMU	13	–	13	–	2	–	2	2	3	–	2	2	2	–	1	–	BOR	SW ◇	–	–	TQFP (PT), QFN (ML)	USB 2.0 (Full Speed), Peripheral Pin Select, Deep Sleep Mode, XLP
	PIC16F917	R	\$2.17	40	36	MR	14 KB 8 Kw	✓	–	352	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	96	Comp	2	–	8	–	2	2	–	2	1	1	–	1	1	–	–	–	BOR	✓	–	✓	PDIP (P), TQFP (PT), 8x8 QFN (ML)	–
	PIC18F46K20	R	\$2.24	40	36	PIC18	64 KB 32 Kw	✓	✓	3936	1024	1.8V-3.6V	64 MHz	16 MHz, 31 kHz	0	Comp	2	–	14	–	2	1	1	1	3	–	1	1	1	–	–	–	PBOR	✓	–	–	PDIP (P), TQFP (PT), 8x8 QFN (ML)	XLP
	PIC18F45J50	R	\$2.30	40	34	PIC18	32 KB 16 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	CTMU	13	–	13	–	2	–	2	2	3	–	2	2	2	–	1	–	BOR	SW ◇	–	–	TQFP (PT), QFN (ML)	USB 2.0 (Full Speed), Peripheral Pin Select, Deep Sleep Mode, XLP
	PIC18F46J11	R	\$2.37	40	34	PIC18	64 KB 32 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	CTMU	13	–	13	–	2	–	2	2	3	–	2	2	2	–	–	–	BOR	SW ◇	–	–	PDIP (P), TQFP (PT), QFN (ML)	Peripheral Pin Select, Deep Sleep Mode, XLP
	PIC18F4450	R	\$2.39	40	34	PIC18	16 KB 8 Kw	✓	✓	768	–	2V-5.5V	48 MHz	31 kHz	0	–	–	–	13	–	0	1	–	1	2	–	1	–	–	–	1	–	PBOR	SW ◇	–	–	PDIP (P), TQFP (PT), QFN (ML)	USB 2.0 (Full Speed)
	PIC18F46J50	R	\$2.58	40	34	PIC18	64 KB 32 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	–	CTMU	13	–	13	–	2	–	2	2	3	–	2	2	2	–	1	–	BOR	SW ◇	–	–	PDIP (P), TQFP (PT), QFN (ML)	USB 2.0 (Full Speed), Peripheral Pin Select, Deep Sleep Mode, XLP
	PIC18F4550	R	\$3.65	40	35	PIC18	32 KB 16 Kw	✓	✓	2048	256	2V-5.5V	48 MHz	8 MHz, 31 kHz	0	–	–	–	13	–	2	1	1	1	3	–	1	1	1	–	1	–	PBOR	SW ◇	–	–	PDIP (P), TQFP (PT), QFN (ML)	USB 2.0 (Full Speed)
	PIC18F4523	R	\$3.67	40	36	PIC18	32 KB 16 Kw	✓	✓	1536	256	2V-5.5V	40 MHz	8 MHz, 31 kHz	0	–	–	–	13	–	2	1	1	1	3	–	1	1	1	–	–	–	PBOR	SW ◇	–	–	PDIP (P), TQFP (PT), QFN (ML)	–

Products sorted by pin count followed by pricing.

† - Pricing subject to change; please contact your Microchip representative for most current pricing.

◇ - Software PLVD implemented via ADC.

8-bit PIC® Microcontrollers

Product		Released (R) Not Released (NR)	5 ku Pricing¹	Pins		Core	Memory					Voltage Range	Operating Speed		LCD Segments	mTouch™		Analog			Digital				Communication						Monitors		SR-Latch	Timer 1 Gate	Packages (Designator)	Special Features		
				Total	I/O		Program	Self-Read	Self-Write	Data RAM (B)	Data EE (B)		Maximum Speed	Internal Oscillator		Module	Channels	8-bit ADC	10-bit ADC	12-bit ADC	Comparators	CCP	ECCP	8-bit Timer	16-bit Timer	AUSART	EUSART	I²C™	SPI	Ethernet (MAC/PHY)	FS-USB	ECAN					BOR/PBOR	PLVD
40/44-Pin (Cont.)	PIC18F4480	R	\$3.93	40	36	PIC18	16 KB 8 Kw	✓	✓	768	256	2V-5.5V	40 MHz	8 MHz, 31 kHz	0	–	–	–	11	–	2	1	1	1	3	–	1	1	1	–	–	1	PBOR	SW ◇	–	–	PDIP (P), TQFP (PT), QFN (ML)	CAN 2.0
	PIC18F4553	R	\$4.33	40	35	PIC18	32 KB 16 Kw	✓	✓	2048	256	2V-5.5V	48 MHz	8 MHz, 31 kHz	0	–	–	–	13	2	1	1	1	3	–	1	1	1	–	1	–	PBOR	SW ◇	–	–	PDIP (P), TQFP (PT), QFN (ML)	USB 2.0 (Full Speed)	
	PIC18F4580	R	\$4.38	40	36	PIC18	32 KB 16 Kw	✓	✓	1536	256	2V-5.5V	40 MHz	8 MHz, 31 kHz	0	–	–	–	11	–	2	1	1	1	3	–	1	1	1	–	–	1	PBOR	SW ◇	–	–	PDIP (P), TQFP (PT), QFN (ML)	CAN 2.0
	PIC18F4680	R	\$5.26	40	36	PIC18	64 KB 32 Kw	✓	✓	3328	1024	2V-5.5V	40 MHz	8 MHz, 31 kHz	0	–	–	–	11	–	2	1	1	1	3	–	1	1	1	–	–	1	PBOR	SW ◇	–	–	PDIP (P), TQFP (PT), 8x8 QFN (ML)	CAN 2.0
64-Pin	PIC16F1946	NR	\$1.75	64	53	EMR	14 KB 8 Kw	✓	✓	512	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	184	CSM	17	–	17	–	3	2	3	4	1	–	2	2	2	–	–	–	BOR	SW ◇	✓	✓	TQFP (PT)	XLP
	PIC16F1947	NR	\$1.82	64	53	EMR	28 KB 16 Kw	✓	✓	1024	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	184	CSM	17	–	17	–	3	2	3	4	1	–	2	2	2	–	–	–	BOR	SW ◇	✓	✓	TQFP (PT)	XLP
	PIC18F63J11	R	\$2.20	64	54	PIC18	8 KB 4 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	8 MHz, 31 kHz	0	–	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	PBOR	SW ◇	–	–	TQFP (PT)	–
	PIC18F65J10	R	\$2.25	64	50	PIC18	32 KB 16 Kw	✓	✓	2048	–	2V-3.6V	40 MHz	31 kHz	0	–	–	–	11	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	TQFP (PT)	–
	PIC18F64J11	R	\$2.27	64	54	PIC18	16 KB 8 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	8 MHz, 31 kHz	0	–	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	SW ◇	–	–	TQFP (PT)	–
	PIC16F946	R	\$2.31	64	54	MR	14 KB 8 Kw	✓	–	336	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	168	Comp	2	–	8	–	2	2	–	2	1	1	–	1	1	–	–	–	BOR	✓	–	✓	TQFP (PT)	–
	PIC18F63J90	R	\$2.35	64	51	PIC18	8 KB 4 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	8 MHz, 31 kHz	132	–	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	TQFP (PT)	Integrated LCD Driver
	PIC18F65J11	R	\$2.37	64	54	PIC18	32 KB 16 Kw	✓	✓	2048	–	2V-3.6V	40 MHz	8 MHz, 31 kHz	0	–	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	SW ◇	–	–	TQFP (PT)	–
	PIC18F64J90	R	\$2.41	64	51	PIC18	16 KB 8 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	8 MHz, 31 kHz	132	–	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	TQFP (PT)	Integrated LCD Driver
	PIC18F66J10	R	\$2.49	64	50	PIC18	64 KB 32 Kw	✓	✓	2048	–	2V-3.6V	40 MHz	31 kHz	0	–	–	–	11	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	TQFP (PT)	–
	PIC18F65J90	R	\$2.52	64	50	PIC18	32 KB 16 Kw	✓	✓	2048	–	2V-3.6V	40 MHz	8 MHz, 31 kHz	132	–	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	TQFP (PT)	Integrated LCD Driver
	PIC18F65J50	R	\$2.63	64	49	PIC18	32 KB 16 Kw	✓	✓	3904	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	–	–	–	8	–	2	2	3	2	3	–	2	2	2	–	1	–	BOR	✓	–	–	TQFP (PT)	USB 2.0 (Full Speed)
	PIC18F66J11	R	\$2.63	64	50	PIC18	64 KB 32 Kw	✓	✓	3904	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	–	–	–	11	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	TQFP (PT)	–
	PIC18F66J90	R	\$2.70	64	51	PIC18	64 KB 32 Kw	✓	✓	3900	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	132	CTMU	12	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	TQFP (PT)	Integrated LCD Driver
	PIC18F67J10	R	\$2.77	64	50	PIC18	128 KB 64 Kw	✓	✓	3936	–	2V-3.6V	40 MHz	31 kHz	0	–	–	–	11	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	TQFP (PT)	–
	PIC18F66J50	R	\$2.90	64	49	PIC18	64 KB 32 Kw	✓	✓	3904	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	–	–	–	8	–	2	2	3	2	3	–	2	2	2	–	1	–	BOR	✓	–	–	TQFP (PT)	USB 2.0 (Full Speed)
	PIC18F67J11	R	\$2.93	64	50	PIC18	128 KB 64 Kw	✓	✓	3904	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	–	–	–	11	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	TQFP (PT)	–
	PIC18F67J90	R	\$3.00	64	51	PIC18	128 KB 64 Kw	✓	✓	3900	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	132	CTMU	12	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	TQFP (PT)	Integrated LCD Driver
	PIC18F67J50	R	\$3.19	64	49	PIC18	128 KB 64 Kw	✓	✓	3904	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	–	–	–	8	–	2	2	3	2	3	–	2	2	2	–	1	–	BOR	✓	–	–	TQFP (PT)	USB 2.0 (Full Speed)
	PIC18F6493	R	\$3.29	64	50	PIC18	16 KB 8 Kw	✓	–	768	–	2V-5.5V	32 MHz	8 MHz, 31 kHz	132	–	–	–	12	2	2	–	1	3	1	1	1	1	1	–	–	–	PBOR	SW ◇	–	–	TQFP (PT)	Integrated LCD Driver
	PIC18F66J60	R	\$3.36	64	39	PIC18	64 KB 32 Kw	✓	✓	3808	–	2V-3.6V	42 MHz	31 kHz	0	–	–	–	11	–	2	2	3	2	3	–	1	1	1	–	–	–	BOR	✓	–	–	TQFP (PT)	Integrated MAC, 10 Base T PHY
	PIC18F67J60	R	\$3.65	64	39	PIC18	128 KB 64 Kw	✓	✓	3808	–	2V-3.6V	42 MHz	31 kHz	0	–	–	–	11	–	2	2	3	2	3	–	1	1	1	1	–	–	BOR	✓	–	–	TQFP (PT)	Integrated MAC, 10 Base T PHY
	PIC18F6723	R	\$7.99	64	54	PIC18	128 KB 64 Kw	✓	✓	3936	1024	2V-5.5V	40 MHz	8 MHz, 31 kHz	0	–	–	–	–	12	2	2	3	2	3	–	2	2	2	–	–	–	PBOR	SW ◇	–	–	TQFP (PT)	–

Products sorted by pin count followed by pricing.

† - Pricing subject to change; please contact your Microchip representative for most current pricing.

◇ - Software PLVD implemented via ADC.

8-bit PIC® Microcontrollers

Product	Released (R) Not Released (NR)	5 yr Pricing†	Pins		Core	Memory					Voltage Range	Operating Speed		LCD Segments	mTouch™		Analog			Digital				Communication						Monitors		SR-Latch	Timer 1 Gate	Packages (Designator)	Special Features		
			Total	I/O		Program	Self-Read	Self-Write	Data RAM (B)	Data EE (B)		Maximum Speed	Internal Oscillator		Module	Channels	8-bit ADC	10-bit ADC	12-bit ADC	Comparators	CCP	ECPP	8-bit Timer	16-bit Timer	AUSART	EUSART	PC™	SPI	Ethernet (MAC/PHY)	FS-USB	ECAN					BOR/PBOR	PLVD
80-Pin	PIC18F83J11	R	\$2.46	80	70	PIC18	8 KB 4 Kw	✓	✓	1024	–	2V-3.6V	40 MHz 8 MHz, 31 kHz	0	–	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	SW ◇	–	–	TQFP (PT)	–
	PIC18F85J10	R	\$2.49	80	66	PIC18	32 KB 16 Kw	✓	✓	2048	–	2V-3.6V	40 MHz 31 kHz	0	–	–	–	15	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	TQFP (PT)	–
	PIC18F84J11	R	\$2.52	80	70	PIC18	16 KB 8 Kw	✓	✓	1024	–	2V-3.6V	40 MHz 8 MHz, 31 kHz	0	–	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	SW ◇	–	–	TQFP (PT)	–
	PIC18F83J90	R	\$2.60	80	66	PIC18	8 KB 4 Kw	✓	✓	1024	–	2V-3.6V	40 MHz 8 MHz, 31 kHz	192	–	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	TQFP (PT)	Integrated LCD Driver
	PIC18F85J11	R	\$2.63	80	70	PIC18	32 KB 16 Kw	✓	✓	2048	–	2V-3.6V	40 MHz 8 MHz, 31 kHz	0	–	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	SW ◇	–	–	TQFP (PT)	–
	PIC18F84J90	R	\$2.67	80	66	PIC18	16 KB 8 Kw	✓	✓	1024	–	2V-3.6V	40 MHz 8 MHz, 31 kHz	192	–	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	TQFP (PT)	Integrated LCD Driver
	PIC18F86J10	R	\$2.74	80	66	PIC18	64 KB 32 Kw	✓	✓	2048	–	2V-3.6V	40 MHz 31 kHz	0	–	–	–	15	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	TQFP (PT)	–
	PIC18F85J90	R	\$2.77	80	66	PIC18	32 KB 16 Kw	✓	✓	2048	–	2V-3.6V	40 MHz 8 MHz, 31 kHz	192	–	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	TQFP (PT), LQFP (PL)	Integrated LCD Driver
	PIC18F85J50	R	\$2.90	80	65	PIC18	32 KB 16 Kw	✓	✓	3904	–	2V-3.6V	48 MHz 8 MHz, 31 kHz	0	–	–	–	12	–	2	2	3	2	3	–	2	2	2	–	1	–	BOR	✓	–	–	TQFP (PT)	USB 2.0 (Full Speed)
	PIC18F86J11	R	\$2.90	80	66	PIC18	64 KB 32 Kw	✓	✓	3904	–	2V-3.6V	48 MHz 8 MHz, 31 kHz	0	–	–	–	15	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	TQFP (PT)	–
	PIC18F86J90	R	\$2.97	80	67	PIC18	64 KB 32 Kw	✓	✓	3900	–	2V-3.6V	48 MHz 8 MHz, 31 kHz	192	CTMU	12	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	TQFP (PT)	Integrated LCD Driver
	PIC18F87J10	R	\$3.02	80	66	PIC18	128 KB 64 Kw	✓	✓	3936	–	2V-3.6V	40 MHz 31 kHz	0	–	–	–	15	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	TQFP (PT), LQFP (PL)	–
	PIC18F86J50	R	\$3.15	80	65	PIC18	64 KB 32 Kw	✓	✓	3904	–	2V-3.6V	48 MHz 8 MHz, 31 kHz	0	–	–	–	12	–	2	2	3	2	3	–	2	2	2	–	1	–	BOR	✓	–	–	TQFP (PT)	USB 2.0 (Full Speed)
	PIC18F87J11	R	\$3.19	80	66	PIC18	128 KB 64 Kw	✓	✓	3904	–	2V-3.6V	48 MHz 8 MHz, 31 kHz	0	–	–	–	15	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	TQFP (PT)	–
	PIC18F87J90	R	\$3.26	80	67	PIC18	128 KB 64 Kw	✓	✓	3900	–	2V-3.6V	48 MHz 8 MHz, 31 kHz	192	CTMU	12	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	TQFP (PT)	Integrated LCD Driver
	PIC18F87J50	R	\$3.44	80	65	PIC18	128 KB 64 Kw	✓	✓	3904	–	2V-3.6V	48 MHz 8 MHz, 31 kHz	0	–	–	–	12	–	2	2	3	2	3	–	2	2	2	–	1	–	BOR	✓	–	–	TQFP (PT)	USB 2.0 (Full Speed)
	PIC18F86J60	R	\$3.63	80	55	PIC18	64 KB 32 Kw	✓	✓	3808	–	2V-3.6V	42 MHz 31 kHz	0	–	–	–	15	–	2	2	3	2	3	–	2	1	1	1	–	–	BOR	✓	–	–	TQFP (PT)	Integrated MAC, 10 Base T PHY
	PIC18F8493	R	\$3.78	80	66	PIC18	16 KB 8 Kw	✓	–	768	–	2V-5.5V	32 MHz 8 MHz, 31 kHz	192	–	–	–	12	2	2	–	1	3	1	1	1	1	–	–	–	PBOR	SW ◇	–	–	TQFP (PT)	Integrated LCD Driver	
PIC18F87J60	R	\$3.92	80	55	PIC18	128 KB 64 Kw	✓	✓	3808	–	2V-3.6V	42 MHz 32 kHz, 31 kHz	0	–	–	–	15	–	2	2	3	2	3	–	2	1	1	1	–	–	BOR	✓	–	–	TQFP (PT)	Integrated MAC, 10 Base T PHY	
PIC18F8723	R	\$8.44	80	70	PIC18	128 KB 64 Kw	✓	✓	3936	1024	2V-5.5V	40 MHz 8 MHz, 31 kHz	0	–	–	–	16	2	2	3	2	3	–	2	2	2	–	–	–	PBOR	SW ◇	–	–	TQFP (PT)	–		
100-Pin	PIC18F96J60	R	\$3.84	100	70	PIC18	64 KB 32 Kw	✓	✓	3808	–	2V-3.6V	42 MHz 31 kHz	0	–	–	–	16	–	2	2	3	2	3	–	2	2	2	1	–	–	BOR	✓	–	–	TQFP (PT)	Integrated MAC, 10 Base T PHY
	PIC18F97J60	R	\$4.13	100	70	PIC18	128 KB 64 Kw	✓	✓	3808	–	2V-3.6V	42 MHz 31 kHz	0	–	–	–	16	–	2	2	3	2	3	–	2	2	2	1	–	–	BOR	✓	–	–	TQFP (PT), LQFP (PL)	Integrated MAC, 10 Base T PHY

Products sorted by pin count followed by pricing.

† - Pricing subject to change; please contact your Microchip representative for most current pricing.

◇ - Software PLVD implemented via ADC.

16-bit PIC® Microcontrollers For 8-bit Applications

Product	Released (R) Not Released (NR)	5 ku Pricing [†]	Pins		Core	Memory			Voltage Range	Operating Speed		Analog			Capture/Compare/PWM Peripherals	Timers	Communication		Monitors	Packages (Designator)	
			Total	I/O		Program (KB)	Data RAM (B)	EEPROM		Maximum MIPS	Internal Oscillator	Charge Time Measurement Unit	10-bit ADC	Comparators			Digital Communication	FS-USB OTG	System Mgmt. Features		
20-Pin	PIC24F08KA101	R	\$1.44	20	18	PIC24F	8	1536	512	1.8V-3.6V	16	8 MHz, 32 kHz	√	9	2	1-Std. PWM, 16-bit PWM resolution, 1-Input Capture	3 x 16-bit	2-UART, 1-SPI, 1-PC	0	BOR, POR, WDT, Deep Sleep, XLP	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)
	PIC24F16KA101	R	\$1.51	20	18	PIC24F	16	1536	512	1.8V-3.6V	16	8 MHz, 32 kHz	√	9	2	1-Std. PWM, 16-bit PWM resolution, 1-Input Capture	3 x 16-bit	2-UART, 1-SPI, 1-PC	0	BOR, POR, WDT, Deep Sleep, XLP	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)
28-Pin	PIC24F08KA102	R	\$1.51	28	24	PIC24F	8	1536	512	1.8V-3.6V	16	8 MHz, 32 kHz	√	9	2	1-Std. PWM, 16-bit PWM resolution, 1-Input Capture	3 x 16-bit	2-UART, 1-SPI, 1-PC	0	BOR, POR, WDT, Deep Sleep, XLP	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)
	PIC24F16KA102	R	\$1.58	28	24	PIC24F	16	1536	512	1.8V-3.6V	16	8 MHz, 32 kHz	√	9	2	1-Std. PWM, 16-bit PWM resolution, 1-Input Capture	3 x 16-bit	2-UART, 1-SPI, 1-PC	0	BOR, POR, WDT, Deep Sleep, XLP	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)
	PIC24FJ16GA002	R	\$1.74	28	21	PIC24F	16	4096	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	–	10	2	5-Std. PWM, 16-bit PWM resolution, 5-Input Capture	5 x 16-bit	2-UART, 2-SPI, 2-PC	0	BOR, LVD, POR, WDT	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)
	PIC24FJ32GA002	R	\$2.06	28	21	PIC24F	32	8192	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	–	10	2	5-Std. PWM, 16-bit PWM resolution, 5-Input Capture	5 x 16-bit	2-UART, 2-SPI, 2-PC	0	BOR, LVD, POR, WDT	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)
	PIC24FJ48GA002	R	\$2.27	28	21	PIC24F	48	8192	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	–	10	2	5-Std. PWM, 16-bit PWM resolution, 5-Input Capture	5 x 16-bit	2-UART, 2-SPI, 2-PC	0	BOR, LVD, POR, WDT	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)
	PIC24FJ64GA002	R	\$2.48	28	21	PIC24F	64	8192	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	–	10	2	5-Std. PWM, 16-bit PWM resolution, 5-Input Capture	5 x 16-bit	2-UART, 2-SPI, 2-PC	0	BOR, LVD, POR, WDT	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)
40/44-Pin	PIC24FJ16GA004	R	\$1.93	44	35	PIC24F	16	4096	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	–	13	2	5-Std. PWM, 16-bit PWM resolution, 5-Input Capture	5 x 16-bit	2-UART, 2-SPI, 2-PC	0	BOR, LVD, POR, WDT	TQFP (PT), QFN (ML)
	PIC24FJ32GA004	R	\$2.30	44	35	PIC24F	32	8192	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	–	13	2	5-Std. PWM, 16-bit PWM resolution, 5-Input Capture	5 x 16-bit	2-UART, 2-SPI, 2-PC	0	BOR, LVD, POR, WDT	TQFP (PT), QFN (ML)
	PIC24FJ48GA004	R	\$2.51	44	35	PIC24F	48	8192	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	–	13	2	5-Std. PWM, 16-bit PWM resolution, 5-Input Capture	5 x 16-bit	2-UART, 2-SPI, 2-PC	0	BOR, LVD, POR, WDT	TQFP (PT), QFN (ML)
	PIC24FJ64GA004	R	\$2.72	44	35	PIC24F	64	8192	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	–	13	2	5-Std. PWM, 16-bit PWM resolution, 5-Input Capture	5 x 16-bit	2-UART, 2-SPI, 2-PC	0	BOR, LVD, POR, WDT	TQFP (PT), QFN (ML)
64-Pin	PIC24FJ64GA006	R	\$3.05	64	53	PIC24F	64	8192	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	–	16	2	5-Std. PWM, 16-bit PWM resolution, 5-Input Capture	5 x 16-bit	2-UART, 2-SPI, 2-PC	0	BOR, POR, WDT	TQFP (PT)
	PIC24FJ96GA006	R	\$3.16	64	53	PIC24F	96	8192	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	–	16	2	5-Std. PWM, 16-bit PWM resolution, 5-Input Capture	5 x 16-bit	2-UART, 2-SPI, 2-PC	0	BOR, POR, WDT	TQFP (PT)
	PIC24FJ128GA006	R	\$3.35	64	53	PIC24F	128	8192	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	–	16	2	5-Std. PWM, 16-bit PWM resolution, 5-Input Capture	5 x 16-bit	2-UART, 2-SPI, 2-PC	0	BOR, POR, WDT	TQFP (PT)
	PIC24FJ128GA106	R	\$3.56	64	53	PIC24F	128	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-PC	0	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ64GB106	R	\$3.64	64	52	PIC24F	64	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-PC	√	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ192GA106	R	\$3.77	64	53	PIC24F	192	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-PC	0	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ128GB106	R	\$3.93	64	52	PIC24F	128	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-PC	√	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ256GA106	R	\$3.98	64	53	PIC24F	256	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-PC	0	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ192GB106	R	\$4.14	64	52	PIC24F	192	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-PC	√	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ256GB106	R	\$4.35	64	52	PIC24F	256	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-PC	√	BOR, LVD, POR, WDT	TQFP (PT)

Products sorted by pin count followed by pricing.

† - Pricing subject to change; please contact your Microchip representative for most current pricing.

◊ - Software PLVD implemented via ADC.

(1)See Application Note "AN1095 - Emulating Data EEPROM".

16-bit PIC® Microcontrollers For 8-bit Applications

Product	Released (R) Not Released (NR)	5-ku Pricing†	Pins		Core	Memory			Voltage Range	Operating Speed		Analog			Capture/Compare/PWM Peripherals	Timers	Communication		Monitors	Packages (Designator)	
			Total	I/O		Program (KB)	Data RAM (B)	EEPROM		Maximum MIPS	Internal Oscillator	Charge Time Measurement Unit	10-bit ADC	Comparators			Digital Communication	FSUSB OTG	System Mgmt. Features		
80-Pin	PIC24FJ64GA008	R	\$3.30	80	69	PIC24F	64	8192	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz,32 kHz		16	2	5-Std. PWM, 16-bit PWM resolution, 5-Input Capture	5 x 16-bit	2-UART, 2-SPI, 2-FC	0	BOR, POR, WDT	TQFP (PT)
	PIC24FJ96GA008	R	\$3.43	80	69	PIC24F	96	8192	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz,32 kHz		16	2	5-Std. PWM, 16-bit PWM resolution, 5-Input Capture	5 x 16-bit	2-UART, 2-SPI, 2-FC	0	BOR, POR, WDT	TQFP (PT)
	PIC24FJ128GA008	R	\$3.60	80	69	PIC24F	128	8192	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz,32 kHz		16	2	5-Std. PWM, 16-bit PWM resolution, 5-Input Capture	5 x 16-bit	2-UART, 2-SPI, 2-FC	0	BOR, POR, WDT	TQFP (PT)
	PIC24FJ128GA108	R	\$3.82	80	69	PIC24F	128	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz,32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-FC	0	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ64GB108	R	\$3.91	80	68	PIC24F	64	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz,32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-FC	√	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ192GA108	R	\$4.03	80	69	PIC24F	192	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz,32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-FC	0	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ128GB108	R	\$4.20	80	68	PIC24F	128	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz,32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-FC	√	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ256GA108	R	\$4.24	80	69	PIC24F	256	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-FC	0	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ192GB108	R	\$4.41	80	68	PIC24F	192	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-FC	√	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ256GB108	R	\$4.62	80	68	PIC24F	256	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-FC	√	BOR, LVD, POR, WDT	TQFP (PT)
100-Pin	PIC24FJ64GA010	R	\$3.51	100	85	PIC24F	64	8192	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz		16	2	5-Std. PWM, 16-bit PWM resolution, 5-Input Capture	5 x 16-bit	2-UART, 2-SPI, 2-FC	0	BOR, POR, WDT	TQFP (PT)
	PIC24FJ96GA010	R	\$3.64	100	85	PIC24F	96	8192	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz		16	2	5-Std. PWM, 16-bit PWM resolution, 5-Input Capture	5 x 16-bit	2-UART, 2-SPI, 2-FC	0	BOR, POR, WDT	TQFP (PT)
	PIC24FJ128GA010	R	\$3.81	100	85	PIC24F	128	8192	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz		16	2	5-Std. PWM, 16-bit PWM resolution, 5-Input Capture	5 x 16-bit	2-UART, 2-SPI, 2-FC	0	BOR, POR, WDT	TQFP (PT)
	PIC24FJ128GA110	R	\$4.03	100	85	PIC24F	128	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-FC	0	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ64GB110	R	\$4.12	100	84	PIC24F	64	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-FC	√	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ192GA110	R	\$4.24	100	85	PIC24F	192	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-FC	0	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ128GB110	R	\$4.41	100	84	PIC24F	128	16384	AN1095 ⁽¹⁾	2V-3.6V	16	16 MHz, 32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-FC	√	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ256GA110	R	\$4.45	100	85	PIC24F	256	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-FC	0	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ192GB110	R	\$4.62	100	84	PIC24F	192	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-FC	√	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ256GB110	R	\$4.83	100	84	PIC24F	256	16384	AN1095 ⁽¹⁾	2V-3.6V	16	8 MHz, 32 kHz	√	16	3	9-Std. PWM, 16-bit PWM resolution, 9-Input Capture	5 x 16-bit	4-UART, 3-SPI, 3-FC	√	BOR, LVD, POR, WDT	TQFP (PT)

Products sorted by pin count followed by pricing.

† - Pricing subject to change; please contact your Microchip representative for most current pricing.

◊ - Software PLVD implemented via ADC.

⁽¹⁾See Application Note "AN1095 - Emulating Data EEPROM".

Terms and Definitions

Term	Definition
1 KB	1024 bytes
1 Kw	1024 words
18F/PIC18	16-bit instruction word – 75/83 instructions
ADC	Analog to Digital Converter
AUSART	Addressable Universal Synchronous Asynchronous Receiver Transceiver
BL/Baseline	12-bit instruction word – 33 instructions
BOR/PBOR	Brown Out Reset/Programmable Brown Out Reset
CCP/ECCP	Capture Compare PWM/Enhanced Capture Compare PWM
DSM	Data Signal Modulator
ECAN	Enhanced Controller Area Network
EEPROM	Electrically Erasable Programmable Read Only Memory
EFT	Electrical Fast Transient
EMC	Electromagnetic Compatibility
EMI	Electromagnetic Interference
EMR/Enhanced-MidRange	14 bit instruction word – 49 instructions (denoted as PIC1XF1XXX)
ESD	Electrostatic Discharge
EUSART	Enhanced Universal Synchronous Asynchronous Receiver Transceiver
EWDT/WDT	Extended Watch Dog Timer/Watch Dog Timer
HV	High Voltage
ICD	In-Circuit Debug
ICE	In-Circuit Emulation
ICSP	In-Circuit Serial Programming
IDE	Integrated Development Environment
LCD	Liquid Crystal Display
LDO	Low Drop-Out voltage regulator
LF	Low Power Flash
MI ² C/I ² C	Master Inter-Integrated Circuit bus/Inter-Integrated Circuit bus
MIPS	Million Instructions Per Second
MR/Mid-Range	14 bit instruction word – 35 instructions
MSSP/SSP	Master/Synchronous Serial Port (I ² C & SPI Peripheral)
mTouch	Proprietary Touch Sensing Technology
Comp	Capacitive Sensing implemented via Comparator
CSM	mTouch – Capacitive Sensing Module
CTMU	mTouch – Charge Time Measurement Unit
SR Latch	Capacitive Sensing implemented via SR Latch
PIC24F	16-bit Core
PLVD	Programmable Low Voltage Detect
POR/POOR	Power ON Reset/Power ON/OFF Reset
PWM	Pulse Width Modulation
RAM	Random Access Memory
Source/Sink Current	All Products Support 25 mA per I/O
SR Latch	Set Reset Latch
SPI	Serial Peripheral Interface
T1G	Timer 1 Gate
USART	Universal Synchronous Asynchronous Receiver Transceiver
USB	Universal Serial Bus
USB (Low Speed)	1.5 Mb/s Data Rate
USB (Full Speed)	12 Mb/s Data Rate
USB (Hi Speed)	480 Mb/s Data Rate
USB OTG	USB On-The-Go
XLP	nanoWatt XLP™ eXtreme Low Power Technology

Support

Microchip is committed to supporting its customers in developing products faster and more efficiently. We maintain a worldwide network of field applications engineers and technical support ready to provide product and system assistance. In addition, the following service areas are available at www.microchip.com:

- **Support** link provides a way to get questions answered fast: <http://support.microchip.com>
- **Sample** link offers evaluation samples of any Microchip device: <http://sample.microchip.com>
- **Forum** link provides access to knowledge base and peer help: <http://forum.microchip.com>
- **Buy** link provides locations of Microchip Sales Channel Partners: www.microchip.com/sales

Sales Office Listing

AMERICAS

Atlanta

Tel: 678-957-9614

Boston

Tel: 774-760-0087

Chicago

Tel: 630-285-0071

Cleveland

Tel: 216-447-0464

Dallas

Tel: 972-818-7423

Detroit

Tel: 248-538-2250

Kokomo

Tel: 765-864-8360

Los Angeles

Tel: 949-462-9523

Santa Clara

Tel: 408-961-6444

Toronto

Mississauga, Ontario

Tel: 905-673-0699

EUROPE

Austria - Wels

Tel: 43-7242-2244-39

Denmark - Copenhagen

Tel: 45-4450-2828

France - Paris

Tel: 33-1-69-53-63-20

Germany - Munich

Tel: 49-89-627-144-0

Italy - Milan

Tel: 39-0331-742611

Netherlands - Drunen

Tel: 31-416-690399

Spain - Madrid

Tel: 34-91-708-08-90

UK - Wokingham

Tel: 44-118-921-5869

Training

If additional training interests you, then Microchip can help. We continue to expand our technical training options, offering a growing list of courses and in-depth curriculum locally, as well as significant online resources – whenever you want to use them.

- Regional Training Centers: www.microchip.com/rtc
- MASTERS Conferences: www.microchip.com/masters
- Worldwide Seminars: www.microchip.com/seminars
- eLearning: www.microchip.com/webseminars
- Resources from our Distribution and Third Party Partners www.microchip.com/training

ASIA/PACIFIC

Australia - Sydney

Tel: 61-2-9868-6733

China - Beijing

Tel: 86-10-8528-2100

China - Chengdu

Tel: 86-28-8665-5511

China - Hong Kong SAR

Tel: 852-2401-1200

China - Nanjing

Tel: 86-25-8473-2460

China - Qingdao

Tel: 86-532-8502-7355

China - Shanghai

Tel: 86-21-5407-5533

China - Shenyang

Tel: 86-24-2334-2829

China - Shenzhen

Tel: 86-755-8203-2660

China - Wuhan

Tel: 86-27-5980-5300

China - Xiamen

Tel: 86-592-2388138

China - Xian

Tel: 86-29-8833-7252

China - Zhuhai

Tel: 86-756-3210040

ASIA/PACIFIC

India - Bangalore

Tel: 91-80-3090-4444

India - New Delhi

Tel: 91-11-4160-8631

India - Pune

Tel: 91-20-2566-1512

Japan - Yokohama

Tel: 81-45-471- 6166

Korea - Daegu

Tel: 82-53-744-4301

Korea - Seoul

Tel: 82-2-554-7200

Malaysia - Kuala Lumpur

Tel: 60-3-6201-9857

Malaysia - Penang

Tel: 60-4-227-8870

Philippines - Manila

Tel: 63-2-634-9065

Singapore

Tel: 65-6334-8870

Taiwan - Hsin Chu

Tel: 886-3-572-9526

Taiwan - Kaohsiung

Tel: 886-7-536-4818

Taiwan - Taipei

Tel: 886-2-2500-6610

Thailand - Bangkok

Tel: 66-2-694-1351

1/26/09

Microcontrollers • Digital Signal Controllers • Analog • Serial EEPROMs

Information subject to change. The Microchip name and logo, the Microchip logo, HI-TECH C and PIC are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries. mTouch is a trademark of Microchip Technology Incorporated in the U.S.A. and other countries. All other trademarks mentioned herein are property of their respective companies.

© 2009, Microchip Technology Incorporated. All Rights Reserved. Printed in the U.S.A. 4/09

DS41380B




MICROCHIP
www.microchip.com

Microchip Technology Inc.
2355 W. Chandler Blvd.
Chandler, AZ 85224-6199