



1 CABLE ASSEMBLY TESTED FOR OPENS, SHORTS AND HI-POT @ 300V.

2 LABEL INFORMATION:



- 3. PRODUCT AND PROCESSING MEETS REQUIREMENTS OF TE CONNECTIVITY STANDARD TEC-138-702.
- 4. PRODUCT MEETS THE REQUIREMENTS OF T10/2125-D, REVISION 04b [SAS-2.1].

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SMITH 24FEB2010	TE Connectivity																		
DIMENSIONS: mm		CHK J. HACKMAN 24FEB2010																			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. HACKMAN 24FEB2010	NAME CABLE ASSEMBLY, MINI-SAS, 4X, EXTERNAL 6 Gbps, PASSIVE																		
<table border="1"> <tr><td>0 PLC</td><td>±</td><td>-</td></tr> <tr><td>1 PLC</td><td>±</td><td>-</td></tr> <tr><td>2 PLC</td><td>±</td><td>-</td></tr> <tr><td>3 PLC</td><td>±</td><td>-</td></tr> <tr><td>4 PLC</td><td>±</td><td>-</td></tr> <tr><td>ANGLES</td><td>±</td><td>-</td></tr> </table>		0 PLC	±	-	1 PLC	±	-	2 PLC	±	-	3 PLC	±	-	4 PLC	±	-	ANGLES	±	-	APPLICATION SPEC	SIZE A1
0 PLC	±	-																			
1 PLC	±	-																			
2 PLC	±	-																			
3 PLC	±	-																			
4 PLC	±	-																			
ANGLES	±	-																			
MATERIAL		WEIGHT	CAGE CODE 00779																		
FINISH		DRAWING NO 2127833																			
BACKSHELL		CUSTOMER DRAWING																			
WIRING PATTERN		SCALE 1:1 SHEET 1 OF 2 REV B1																			



3	3	2-4-6	2-4-6	6 GBPS	24 AWG	10±0.15 METERS	2-2127833-6
3	3	2-4-6	2-4-6	6 GBPS	24 AWG	9±0.15 METERS	2-2127833-5
3	3	2-4-6	2-4-6	6 GBPS	24 AWG	8±0.125 METERS	2-2127833-4
3	3	2-4-6	2-4-6	6 GBPS	24 AWG	7±0.1 METERS	2-2127833-3
-	-	2-4-6	2-4-6	6 GBPS	24 AWG	6±0.075 METERS	2-2127833-2
-	-	2-4-6	2-4-6	6 GBPS	24 AWG	5±0.075 METERS	2-2127833-1
-	-	2-4-6	2-4-6	6 GBPS	26 AWG	4±0.075 METERS	2-2127833-0
-	-	2-4-6	2-4-6	6 GBPS	26 AWG	3±0.05 METERS	1-2127833-9
-	-	2-4-6	2-4-6	6 GBPS	28 AWG	2.5±0.05 METERS	1-2127833-8
-	-	2-4-6	2-4-6	6 GBPS	28 AWG	2±0.05 METERS	1-2127833-7
-	-	2-4-6	2-4-6	6 GBPS	28 AWG	1.5±0.04 METERS	1-2127833-6
-	-	2-4-6	2-4-6	6 GBPS	30 AWG	1±0.04 METERS	1-2127833-5
-	-	2-4-6	2-4-6	6 GBPS	30 AWG	0.5±0.025 METERS	1-2127833-4
3	3	2-4	4-6	6 GBPS	24 AWG	10±0.15 METERS	1-2127833-3
3	3	2-4	4-6	6 GBPS	24 AWG	9±0.15 METERS	1-2127833-2
3	3	2-4	4-6	6 GBPS	24 AWG	8±0.125 METERS	1-2127833-1
3	3	2-4	4-6	6 GBPS	24 AWG	7±0.1 METERS	1-2127833-0
-	-	2-4	4-6	6 GBPS	24 AWG	6±0.075 METERS	2127833-9
-	-	2-4	4-6	6 GBPS	24 AWG	5±0.075 METERS	2127833-8
-	-	2-4	4-6	6 GBPS	26 AWG	4±0.075 METERS	2127833-7
-	-	2-4	4-6	6 GBPS	26 AWG	3±0.05 METERS	2127833-6
-	-	2-4	4-6	6 GBPS	28 AWG	2.5±0.05 METERS	2127833-5
-	-	2-4	4-6	6 GBPS	28 AWG	2±0.05 METERS	2127833-4
-	-	2-4	4-6	6 GBPS	28 AWG	1.5±0.04 METERS	2127833-3
-	-	2-4	4-6	6 GBPS	30 AWG	1±0.04 METERS	2127833-2
-	-	2-4	4-6	6 GBPS	30 AWG	0.5±0.025 METERS	2127833-1
P1	P2	P1	P2	DATA RATE	WIRE GAGE	L	PART NO
KEY RIB		KEY SLOTS					

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN T. SMITH 24FEB2010	 TE Connectivity
 0. PLC ± - 1. PLC ± - 2. PLC ± - 3. PLC ± - 4. PLC ± - ANGLES ± -		CHK J. HACKMAN 24FEB2010 APVD J. HACKMAN 24FEB2010 PRODUCT SPEC APPLICATION SPEC SIZE CAGE CODE DRAWING NO WEIGHT A1 00779 C=2127833	
MATERIAL	FINISH	CUSTOMER DRAWING SCALE 1:1 SHEET 2 OF 2 REV B1	