



Butterfly Hanger for elliptical waveguide 17

Product Classification

Product Type Hanger kit

Ordering Note CommScope® non-standard product

General Specifications

Cable Type Elliptical waveguide

Cables per Hanger 1

Color Silver

Hanger Type Standard butterfly hanger

Mounting 3/8 in (M10) drilled cable ladder

Dimensions

Height 76.2 mm | 3 in

Waveguide Size EW17

Electrical Specifications

Return Loss Effect 0.1 dB

DTF Effect 0.1 dB

Material Specifications

Material Type Stainless steel

Mechanical Specifications

Vibration Survival \geq 4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Double cable weight

Packaging and Weights

Height, packed 47 cm | 18.504 in

Width, packed 10.8 cm | 4.252 in

Length, packed 10.8 cm | 4.252 in

Packaging quantity 10

Weight, gross 2.23 kg | 4.916 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

