

1.5KE Series Protection Diodes




Transient Voltage Suppressors



Features:

- Glass passivated chip junction in moulded plastic package
- 1,500 W surge capability at 1 ms
- Low zener impedance
- Excellent clamping capability
- Fast response time : Typically less than 1 ps from 0 volts to BV minimum
- Typical IR less than 1 μ A above 10 V
- High temperature soldering : 260°C / 10 seconds / .375 inches, (9.5 mm) lead length / 5 lbs. (2.3 kg) tension
- Low clamping voltages
- Wide voltage range
- High transient power dissipation
- No wear-out limitation
- Small physical size

1.5KE Series



Mechanical Data

Case	: JEDEC DO-201AE moulded plastic
Terminals	: Axial leads, solderable per MIL-STD-202, Method 208
Polarity	: Colour band denoted cathode except Bipolar
Mounting Position	: Any
Weight	: 0.045 ounce, 1.2 g

Dimensions : Inches (Millimetres)

Maximum Ratings and Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified

Ratings	Symbol	Value	Units
		1.5KE Series	
Peak Power Dissipation at $T_A = 25^\circ\text{C}$, $T_P = 1$ ms (Note 1)	P_{PK}	Minimum 1,500	Watts
Steady State Power Dissipation at $T_L = 75^\circ\text{C}$ Lead Lengths 5.8 to 7.6, 7.2 to 9.5 (Note 2)	PD	5	
Peak Forward Surge Current, 8.3 ms Single Half Sine-Wave Superimposed on Rated Load (JEDEC Method) (Note 3)	I_{FSM}	200	Amperes
Operating and Storage Temperature Range	T_J, T_{STG}	-65 to +175	°C

Notes

1. Non-repetitive current pulse, per Fig. 3 and derated above $T_A = 25^\circ\text{C}$ per Fig. 2
2. Mounted on copper Leaf area of 0.79in² (20 mm²)
3. 8.3 ms single half sine-wave, duty cycle = 4 pulses per minutes maximum

1.5KE Series Protection Diodes



Transient Voltage Suppressors

Rating and Characteristic Curves

1.5KE Series




Fig. 1-Peak Pulse Power Rating Curve




Fig. 3-Pulse Waveform




Fig. 5-Steady State Power Derating Curve




Fig. 2-Pulse Derating Curve




Fig. 4-Typical Junction Capacitance Unidirectional




Fig. 6-Maximum Non-Repetitive Peak Forward Surge Current Unidirectional

1.5KE Series Protection Diodes



Transient Voltage Suppressors

Uni-Directional 1,500 Watt Axial Lead TVS

Stand-off Voltage V_{rm} (V)	Breakdown Voltage V_{br} (V) Minimum	Breakdown Voltage V_{br} (V) Maximum	I_{test} (mA)	Clamping Voltage V_{clamp} A	Maximum Peak Pulse Current I_{pp} (A)	P_{tot} at $T_L = 75^\circ C$ (W)	Uni-Directional Part Number
5.5	6.45	7.14	10	10.5	143	5	1.5KE6.8A
9.4	10.5	11.6	1	15.6	96		1.5KE11A
13.6	15.2	16.8		22.5	67		1.5KE16A
15.3	17.1	18.9		25.2	59.5		1.5KE18A
18.8	20.9	23.1		30.6	49		1.5KE22A
23.1	25.7	28.4		37.5	40		1.5KE27A
25.6	28.5	31.5		41.4	36		1.5KE30A
28.2	31.4	34.7		45.7	33		1.5KE33A
30.8	34.2	37.8		49.9	30		1.5KE36A
40.2	44.7	49.4		64.8	23.2		1.5KE47A
136	152	162		219	6.8		1.5KE160A
342	380	420		548	4		1.5KE400A

Bi-Directional 1,500 Watt Axial Lead TVS

Stand-off Voltage V_{rm} (V)	Breakdown Voltage V_{br} (V) Minimum	Breakdown Voltage V_{br} (V) Maximum	I_{test} (mA)	Clamping Voltage V_{clamp} A	Maximum Peak Pulse Current I_{pp} (A)	P_{tot} at $T_L = 75^\circ C$ (W)	Bi-Directional Part Number
5.8	6.45	7.14	10	10.5	143	5	1.5KE6.8CA
9.4	10.5	11.6	1	15.6	96		1.5KE11CA
13.6	15.2	16.8		22.5	67		1.5KE16CA
15.3	17.1	18.9		25.2	59.5		1.5KE18CA
18.8	20.9	23.1		30.6	49		1.5KE22CA
23.1	25.7	28.4		37.5	40		1.5KE27CA
25.6	28.5	31.5		41.4	36		1.5KE30CA
28.2	31.4	34.7		45.7	33		1.5KE33CA
30.8	34.2	37.8		49.9	30		1.5KE36CA
40.2	44.7	49.4		64.8	23.2		1.5KE47CA
136	152	168		219	6.8		1.5KE160CA
342	380	420		548	4		1.5KE400CA

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.