






PROJECT NO. EGATN07138		LOC A1	DIST -	REVISIONS					
				P	LTR	DESCRIPTION	DATE	DWN	APVO
					A1	SEE E-08-012925	27MAY2008	CA	VB
					A2	SEE E-12-013952	03AUG2012	SK	AK



- NOTES
BEMERKUNGEN
- NV

NOTE NOT VALID
Bemerkung nicht verwendet
- 1

ORDER NUMBER
BESTELL-NUMMER
- 2

REVISION NUMBER
WERKZEUGÄNDERUNGSINDEX
- 3

MATERIAL MARKING
WERKSTOFFKENNZEICHNUNG
- NV

GM LOGO
GM Logo
- 5

PRODUCTION DATE
PRODUKTIONSdatum
- 6

CONTACT CAVITY NUMBER
KONTAKTKAMMERNUMMER
- 7


TE LOGO
TE Logo
- 8

PACKAGING: BULK MATERIAL IN CARDBOARD BOX
VERPACKUNG: SCHÜTTGUT IN KARTON
- 9


TOOL CAVITY MARKING
NESTMARKIERUNG
- 10

SLOT FOR GM 13257300 (ZUH 360)
Aufnahme fuer GM 13257300 (ZUH 360)



B-B



CODING A



CODING B



-	0-1563190-2	A	2 Pos. TAB 1.6x0.6. TAB-Hsg. CODB	Hsd	PBT-GF20	1.3	1
19179872	0-1563190-1	A	2 Pos. TAB 1.6x0.6. TAB-Hsg. CODA	BLACK	PBT-GF20	1.3	1
CUSTOMER PART NO	PART NO	REV	DESCRIPTION	COLOR	MATERIAL	WEIGHT [g]	ITEM NO

A1	0-1452140-3	2 Pos. MT2, Rec-Hsg.
	1-0962580-1	2 Pos. MT2, Rec-Hsg.
	0-1563189-1	2 Pos. MT2, Rec-Hsg.
TE BESTELL-NR. TE ORDER NO.	BENENNUNG DESCRIPTION	
COUNTERPARTS GEGENSTECKER		

A2	0-1241846-2	1.5	CuFe 2	PRETINNED
	0-0964267-2	0.5-1.0	CuFe 2	PRETINNED
	0-0964265-2	0.35-0.5	CuFe 2	PRETINNED
TE ORDER NO STRIP FORM	WIRE RANGE MM ²	MATERIAL	FINISH	

RRECOMMENDED CONTACT SYSTEM: MICRO TIMER 2 TYPE A; UNSEALED
FOR CABLE INSULATION TYPE FLR ACC. DIN 72551 / ISO 6722 MAX. WIRE SIZE 1.5mm²
MAX. CABLE ISOLATION CRIMP DIAMETER 2.9mm
FOR CABLE INSULATION TYPE TXL ACC. SAE J1128 MAX. WIRE SIZE 1.0mm² OR MAX AWG 18
THE USE OF OTHER CABLE TYPES MUST BE CHECKED IN ANY INDIVIDUAL CASE!

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN C. Anghel	29 JUN 2007	 TE Connectivity		
DIMENSIONS: mm			CHK A. Ketteler	29 JUN 2007			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -		NAME 2 Pos. 1.6x0.6. TAB Hsg.		
	0 PL/C	±0.3	PRODUCT SPEC		-		
	1 PL/C	±0.3	108-94118		-		
	2 PL/C	±0.3	APPLICATION SPEC		-		
	3 PL/C	±-	116-18901		-		
ANGLES		±-	WEIGHT		SIZE		
FINISH		±*	CUSTOMER DRAWING		CAGE CODE		
MATERIAL		-	SCALE		DRAWING NO		
-		-	5:1		A 1 00779 C=1563190		
-		-	SHEET		RESTRICTED TO		
-		-	1 OF 1		-		
-		-	REV A2				