






FCIconnect.com

Copyright FCI

PRODUCT NO

SEE TABLE



mat'l. code				surface		tolerance	projection	product family	
-				ISO 1302		ISO 406 ISO 1101		MOD JACK	
ltr	ecn	no	dr	date	tolerances unless otherwise specified		MM/INCH	title	
A	V91847	RHG		1/5/98	angles	linear		NET JACK II RJ45 SINGLE	
B	V91920	BKB		8/24/99				PORT ASS'Y DIAMOND PEG	
C	V92060	LP		10/20/99	0'±2'			sheet 1 of 3 size	
D	V00462	CEK		02/01/00	dr	R. GRAPE	1/5/98	dwg no	
E	V12718	LP		1/22/02	enr	B. MARSHALL	1/5/98	74262	
F	M05-0074	ERE		04/22/05	chr	B. MARSHALL	1/5/98	A3	
G	M06-0224	ERE		6/12/06	app	B. MARSHALL	1/5/98	type	
sheet		revision	G	G	G			Product Customer Drawing	
index		sheet	1	2	3				


form: A3

PRODUCT NO


SEE TABLE

SPRING TAB CONFIGURATIONS


OPTION Y




OPTION 1




OPTION 2



OPTION 3



OPTION 4



OPTION 5

mat'l. code				surface	tolerance	projection	product family
-				ISO 1302	ISO 406		MOD JACK
				tolerances unless otherwise specified			title
ltr	ecn	no	dr	date	angles	linear	NET JACK II RJ45 SINGLE
G							PORT ASS'Y DIAMOND PEG
							dwg no
							sheet 3 of 3 size
							A3
							type
							Product Customer Drawing
sheet	revision						
index	sheet						

form: A3