


202K142 - 100 - 01/180 - 0

Product Details

Share

Print

Email



Molded Parts

Always EU RoHS/ELV Compliant

(

Statement of Compliance

)

Product Highlights:

- ? Molded Part Type = Molded Boot
- ? Family Name = 202K1
- ? Straight
- ? Marine Application, Military Application, Rail Application
- ? Entry Size, Braided or Magneform Adapter = 10, 11

View all Features

Quick Links

- ?

Check Pricing & Availability
- ?

Search for Tooling
- ?

Product Feature Selector
- ?

Contact Us About This Product

202K142 - 100 - 01/180 - 0

TE Internal Number: 171047 - 000

Active

Add to My Part List

Request Sample

Find Similar Products

Buy Product

Documentation & Additional Information	
Product Drawings: ? Customer Drawing (PDF, English) Catalog Pages/Data Sheets: ? None Available Product Specifications: ? None Available Application Specifications: ? None Available Instruction Sheets: ? None Available CAD Files: ? None Available List all Documents	Additional Information: ? Product Line Information Related Products: ? Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: ? Molded Part Type = Molded Boot ? Size = 42 ? Material = Low Fire Hazard Material Electrical Characteristics: ? Angle = Straight Body Features: ? Cable Diameter Range (mm [in]) = 7.10 - 16.00 [0.280 - 0.630] Contact Features: ? Family Name = 202K1 ? Entry Size, Braided or Magneform Adapter = 10, 11 Housing Features: ? Entry Size, Tinel -Lock Adapter = 7, 8, 10 ? Entry Size - Solid or Fixed Adapter = 6 ? Entry Size - Spin Coupling Adapter = 8 - 10 ? Adapter Entry Size Outside Diameter (Min -Max) (mm [in]) = 18.00 - 24.00 [0.709 - 0.945] ? Material Systems Code = 100 ? Adhesive Pre -Coating = With ? Adhesive Description = Good Water Blocking Pre -Coat Adhesive	Configuration Features: ? Material Code = 100 ? Adhesive Code = 180 Industry Standards: ? RoHS/ELV Compliance = RoHS compliant, ELV compliant ? Lead Free Solder Processes = Not relevant for lead free process ? RoHS/ELV Compliance History = Always was RoHS compliant Environmental: ? Operating Temperature (°C) = -30 - +80 Operation/Application: ? Application = Marine, Military, Rail Other: ? Brand = Raychem ? Comment = Adhesive not used with Transitions. Cut -off boot length; contact Raychem for details.

Corporate Information

- Who We Are

Investors

News Room

Supplier Portal

Careers

Quick Links

- Check Distributor Inventory

Cross Reference

Find Documents & Drawings

Product Compliance Support Center

Site Map

Customer Support

- Email or Chat With Us

Find a Phone Number

Search Knowledge Base

Manage your Account

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

