

Customer Information Sheet

DRAWING No.: M20-611XX05

SHEET 2 OF 2


IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



NOTES:

1. ALL TOLERANCES ARE
±0.20 UNLESS OTHERWISE
STATED.

SPECIFICATION:

MATERIALS:

MOULDING - GLASS-FILLED POLYESTER UL94V-0 BLACK
CONTACTS - PHOSPHOR BRONZE

FINISH:

CONTACTS - 008μ GOLD OVER NICKEL

ELECTRICAL:

CURRENT RATING - 3A MAX

CONTACT RESISTANCE - 10 MILLIOHMS MAX

INSULATION RESISTANCE - 5,000 MEGOHMS MIN

VOLTAGE PROOF - 1,000V AC

MECHANICAL:

INSERTION FORCE (PER CONTACT) - 1.1N AVERAGE

WITHDRAWAL FORCE (PER CONTACT) - 0.7N AVERAGE




ENVIRONMENTAL:

TEMPERATURE RANGE - -55° TO +105°C

PACKING:

TUBE

RECOMMENDED PCB LAYOUT



No. OF WAYS PER ROW	DIM 'A'	DIM 'B'
20	51.46	48.26
32	81.94	78.74

ORDER CODE:

M20-611XX05

No. OF WAYS PER ROW —
20, 32

JAE	5	0107.02	6779
NAME	ISS.	DATE	C/NOTE
APPROVED:			
CHECKED:			
DRAWN:		W. J. BOURNE	
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

HARWIN INC
U.S.A.
TEL: (812) 285 0055
FAX: (812) 285 0056

HARWIN PLC
U.K.
TEL: 023 9237 0451
FAX: 023 9231 4590

HARWIN PTE
SINGAPORE
TEL: 65 7794909
FAX: 65 7793868

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES

X. - ±1mm
X.X - ±0.25mm
X.XX - ±0.10mm
X.XXX - ±0.01mm
ANGLES - ±5°
UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH:

SEE ABOVE

S/AREA:

mm²

TITLE:

PC104 CONNECTOR
(NON-STACKTHROUGH)

DRAWING NUMBER:

M20-611XX05

SHT
2
OF
2