



Power PCB Transformer
Horizontal Split Bobbin

[Home](#) | [Who We Are](#) | [How To Reach Us](#) | [Product Finder](#) | [Distributor Finder](#) | [Sales Rep Finder](#) | [Press Releases](#) | [Other Products: Relays & LCDs, LEDs](#) | [More Info](#) | [Employment Opportunities](#) | [Business Opportunities](#) | [Magnetics Online Store](#)



Features


- Is UL recognized for use in the US and Canada
- UL approved Class B (130° C) Insulation System
- Split Bobbin Design
- Dielectric Strength 2500 Vrms
- Single 115V and dual 115/230V primaries at 50/60Hz are offered as standard
- Standard Dual Secondaries for a Variety of Applications
- Precision Molded-in Terminals
- Available in 6 Standard Sizes for a Variety of Power Requirements

Outline Dimensions


Inches .xxx ± 0.010
mm .xx ± 0.25



SIZE	VA	L	W	H	M	A	B	C	WT. (lbs.)
2	1.1	1.375 34.93	1.125 28.58	0.930 23.62	—	0.250 6.35	0.250 6.35	1.220 30.99	0.17
3	2.4	1.375 34.93	1.125 28.58	1.170 29.72	—	0.250 6.35	0.250 6.35	1.220 30.99	0.25
4	6.0	1.625 41.28	1.313 33.35	1.290 32.77	1.063 26.99	0.250 6.35	0.350 8.89	1.280 32.51	0.44
5	12.0	1.875 47.63	1.563 39.69	1.410 35.81	1.250 31.75	0.300 7.62	0.400 10.16	1.400 35.56	0.70
6	20.0	2.250 57.15	1.875 47.63	1.410 35.81	1.500 38.10	0.300 7.62	0.400 10.16	1.590 40.39	0.80
7	36.0	2.625 66.68	2.188 55.56	1.560 39.62	—	0.400 10.16	0.400 10.16	1.840 46.74	1.1



To order click on part number below		Secondary RMS Rating	
Single 115V 6 PIN	Dual 115V/230V 8 PIN	Series	Parallel
AH20010	ADH20010	10VCT @ 0.110A	5V @ 0.220A
AH30010	ADH30010	10VCT @ 0.250A	5V @ 0.500A
AH40010	ADH40010	10VCT @ 0.600A	5V @ 1.200A
AH50010	ADH50010	10VCT @ 1.200A	5V @ 2.400A
AH60010	ADH60010	10VCT @ 2.000A	5V @ 4.000A
AH20012	ADH20012	12.6VCT @ 0.090A	6.3V @ 0.180A
AH30012	ADH30012	12.6VCT @ 0.200A	6.3V @ 0.400A
AH40012	ADH40012	12.6VCT @ 0.500A	6.3V @ 1.000A
AH50012	ADH50012	12.6VCT @ 1.000A	6.3V @ 2.000A
AH60012	ADH60012	12.6VCT @ 1.600A	6.3V @ 3.020A
AH20016	ADH20016	16VCT @ 0.070A	8V @ 0.140A
AH30016	ADH30016	16VCT @ 0.150A	8V @ 0.300A
AH40016	ADH40016	16VCT @ 0.400A	8V @ 0.800A
AH50016	ADH50016	16VCT @ 0.800A	8V @ 1.600A
AH60016	ADH60016	16VCT @ 1.250A	8V @ 2.500A
AH20020	ADH20020	20VCT @ 0.050A	10V @ 0.110A
AH30020	ADH30020	20VCT @ 0.120A	10V @ 0.240A
AH40020	ADH40020	20VCT @ 0.300A	10V @ 0.600A
AH50020	ADH50020	20VCT @ 0.600A	10V @ 1.200A
AH60020	ADH60020	20VCT @ 1.000A	10V @ 2.000A
AH20024	ADH20024	24VCT @ 0.045A	12V @ 0.090A
AH30024	ADH30024	24VCT @ 0.100A	12V @ 0.200A
AH40024	ADH40024	24VCT @ 0.250A	12V @ 0.500A
AH50024	ADH50024	24VCT @ 0.500A	12V @ 1.000A
AH60024	ADH60024	24VCT @ 0.800A	12V @ 1.600A
AH20028	ADH20028	28VCT @ 0.040A	14V @ 0.080A
AH30028	ADH30028	28VCT @ 0.085A	14V @ 0.170A
AH40028	ADH40028	28VCT @ 0.200A	14V @ 0.400A
AH50028	ADH50028	28VCT @ 0.420A	14V @ 0.840A
AH60028	ADH60028	28VCT @ 0.700A	14V @ 1.400A
AH20036	ADH20036	36VCT @ 0.030A	18V @ 0.060A
AH30036	ADH30036	36VCT @ 0.065A	18V @ 0.130A
AH40036	ADH40036	36VCT @ 0.170A	18V @ 0.340A
AH50036	ADH50036	36VCT @ 0.350A	18V @ 0.700A
AH60036	ADH60036	36VCT @ 0.550A	18V @ 1.100A
AH20048	ADH20048	48VCT @ 0.023A	24V @ 0.046A
AH30048	ADH30048	48VCT @ 0.050A	24V @ 0.100A
AH40048	ADH40048	48VCT @ 0.125A	24V @ 0.250A
AH50048	ADH50048	48VCT @ 0.250A	24V @ 0.500A
AH60048	ADH60048	48VCT @ 0.400A	24V @ 0.800A
AH20056	ADH20056	56VCT @ 0.020A	28V @ 0.040A
AH30056	ADH30056	56VCT @ 0.045A	28V @ 0.090A
AH40056	ADH40056	56VCT @ 0.110A	28V @ 0.220A
AH50056	ADH50056	56VCT @ 0.220A	28V @ 0.440A
AH60056	ADH60056	56VCT @ 0.350A	28V @ 0.700A
AH200120	ADH200120	120VCT @ 0.010A	60V @ 0.020A
AH300120	ADH300120	120VCT @ 0.020A	60V @ 0.040A
AH400120	ADH400120	120VCT @ 0.050A	60V @ 0.100A
AH500120	ADH500120	120VCT @ 0.100A	60V @ 0.200A
AH600120	ADH600120	120VCT @ 0.160A	60V @ 0.320A



Copyright © 1999 ZETTLER, Magnetics, Inc., a Zettler Components Company

All rights reserved.

Tel: (949) 360-5838 Fax: (949) 360-5839

Email: sales@zettlermagnetics.com | Web: www.zettlermagnetics.com

Website-Design by MWS-Internet 1999-2001